

# IP Flex 5 Chrome 14IAU7

## PERFORMANCE

### Processor

Intel® Core™ i3-1215U, 6C (2P + 4E) / 8T, P-core 1.2 / 4.4GHz, E-core 0.9 / 3.3GHz, 10MB

### Graphics

Integrated Intel® UHD Graphics

### Chipset

Intel® SoC Platform

### Memory

8GB Soldered LPDDR4x-4266

### Memory Slots

Memory soldered to systemboard, no slots, dual-channel (8GB models)

### Max Memory

8GB soldered memory, not upgradable

### Storage

128GB eMMC 5.1

### Storage Support<sup>[1]</sup>

One drive, up to 128GB eMMC 5.1 storage card

### Storage Slot

One M.2 2242 PCIe® 4.0 x4 slot, supports M.2 2242 SSD or eMMC storage card (PCIe® 1x1)

### Card Reader

microSD Card Reader

### Audio Chip

High Definition (HD) Audio, Realtek® ALC5682I-VD codec

### Speakers

Stereo speakers, 2W x2, optimized with Waves MaxxAudio®

### Camera

FHD 1080p with Privacy Shutter

### Microphone

2x, Array

### Battery

Integrated 51Wh

### Power Adapter

45W USB-C® (3-pin)

## DESIGN

### Display<sup>[2]</sup>

14" WUXGA (1920x1200) IPS 300nits Glossy, 45% NTSC, 60Hz, Touch

### Touchscreen

10-point Multi-touch

### Keyboard

Backlit, French / English

### Touchpad

Buttonless Mylar® surface multi-touch touchpad, 75 x 120 mm (2.95 x 4.72 inches)

### Case Color

Stone Blue

### Surface Treatment

Aluminium Stamping (Anodized)

### Case Material

Aluminium (Top), PC-ABS (Bottom)

### Pen<sup>[3]</sup>

Pen Upgradable (Purchase Separately)

### Dimensions (WxDxH)<sup>[4]</sup>

315.5 x 229 x 19.8 mm (12.42 x 9.02 x 0.78 inches)

### Weight<sup>[5]</sup>

Starting at 1.58 kg (3.48 lbs)

## SOFTWARE

### Operating System

ChromeOS

### Bundled Software

None

## CONNECTIVITY

### Ethernet

No Onboard Ethernet

### WLAN + Bluetooth®<sup>[6]</sup>

Wi-Fi® 6E, 802.11ax 2x2 + BT5.3

### WWAN

Non-WWAN

### NFC

None

### Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 2x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 3.0 and DisplayPort™ 1.4
- 1x Headphone / microphone combo jack (3.5mm)
- 1x microSD card reader

## SECURITY & PRIVACY

### Security Chip

Google Security Chip H1

### Fingerprint Reader

Touch Style, on Palm Rest

### Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

### Other Security

Camera privacy shutter

## SERVICE

### Base Warranty

1-year, Courier or Carry-in

## PSREF

Product Specifications  
Reference

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories<sup>[7]</sup>

None

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- EPEAT™ Silver Registered
- ErP Lot 6/26
- RoHS compliant

## MODEL

TopSeller : No

EAN / UPC / JAN : 196380225130

Announce Date : 2022-04-23

End of Support : 2028-05-30



Product image is a sample, it may not match the real color of this model

### Note:

[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[2] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[3] IP Flex 5 Chrome 14IAU7 is only compatible with USI 1.0 stylus pens.

[4] The system dimensions may vary depending on configurations.

[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[6] Wi-Fi 6E full features might be limited by country-level restrictions.

6GHz Wi-Fi 6E operation is dependent on the support of the operating system, routers/APs/Gateways that support Wi-Fi 6E, and the regional regulatory certifications & spectrum allocation.

Bluetooth 5.3 operation requires Windows 11. For more information please visit [General Bluetooth Support Information on Microsoft](#).

[7] For more compatible accessory solutions, please visit [Lenovo accessories](#).

Lenovo reserves the right to change specifications without notice.

To see more note information, please link to

<https://psref.lenovo.com/Detail/1998?M=82T50000CF>

## Premium Care - Advanced Support from Real People. Real Fast.

### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Recommended Accessories

### Lenovo USI Pen

Lenovo USI Pen is great for extended notetaking and writing, fine art or graphic design. The pen with USI protocol supported Chrome OS and provides an industry-leading 4096 levels of pressure sensitivity for natural w...

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Services

GOOD

3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WSOK75704)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**PSREF**

Product Specifications  
Reference