

HP 965 4K Streaming Webcam (695J5AA)



Overview

Look Great, Automatically

Stream your most authentic self with an AI-enhanced[1], HDR webcam[1] in up to 4K resolution[2] on your favorite streaming platforms. This webcam automatically color corrects, so you look true-to-life, day or night, while it also automatically keeps you center stage. All you need is one webcam to stream, automate, and create what you care about.

UHD 4K

Stream the Real You

Get studio-quality without the studio with this streaming webcam. Film in up to 4K[2] 30fps or 1080p 60 fps with the cutting-edge image sensor, so your audience can enjoy smooth, superb video on your chosen streaming platforms. Fine-tuned to you, the dual-microphones pick up the audio you want to share while reducing the noise you don't.



An AI-Enhanced Production

You don't need a film crew when you have an AI-enabled webcam[1]. During your livestream, Auto Framing keeps you and any guests centerstage.



Always Show your True Colors

Stream in stunning color at any time or on any set. Color correction and HDR automatically adjust to keep you and your content vibrant, day or night, and the 18 mm F2.0 large lens takes everything in for an excellent image, even in low light.



Set your Stage

Customize your set exactly the way you want it. Mount it almost anywhere with the stand or a tripod[3] and still find the perfect angle with 360° swivel and 90° tilt. Adjust your field-of-view to capture the entire set or bring it in for a tighter focus[1].

Features



Auto Focus

While you focus on your stream, this webcam automatically adjusts the focus on you. Feel confident knowing your image is crystal clear throughout your streams.



Only Share When you Want To

When you're done streaming or conferencing, simply attach the magnetic privacy cover for worry-free privacy.



Digital Zoom

Need to get a closer look? Use digital zoom to zoom in and out, so you can show what you want--all available on Poly Lens.^[1]



Conference Seamlessly

Certified for Zoom and compatible with other popular conferencing applications, you can be sure our hardware works seamlessly with Zoom and most other conferencing platforms to deliver an stunning conferencing experience every time.



Thoughtful Product Packaging

HP is committed to reducing plastic in landfills by using recyclable packaging that meets recycling requirements, so it can stay out of the landfill.^[4,5]

[1] Requires downloadable software on [Poly.com/lens](https://poly.com/lens). Host PC requires Windows 10 or higher.

[2] Streaming apps with 3840 x 2160 and minimum 25Mbps network required.

[3] Compatible with standard 1/4" screw tripods and mounts. Tripod not included.

[4] 100% outer box/corrugate cushion packaging made from sustainably sourced certified and recycled fibers. Fiber cushions made from 100% recycled wood fiber and organic material. Any plastic cushions are made from >90% recycled plastic. Excludes plastic bags and plastic foam sheeting.

[5] Recycling facilities not available in all locations.

Specifications

Minimum dimensions (W x D x H)	4.14 x 4.34 x 8.67 cm
Minimum dimensions (W x D x H)	1.63 x 1.71 x 3.41 in
Weight	0.225 kg
Weight	0.5 lb
Package dimensions (W x D x H)	13.9 x 11 x 7.3 cm
Package weight	0.412 kg
Special features	HDR support; Tripod support; Sony STARVIS™ CMOS sensor technology
Sustainable impact specifications	Outside box and corrugated cushions are 100% sustainably sourced and recyclable; 85% post-consumer recycled plastic
Minimum System Requirements	USB 3.0 Type-A
UPC number	(ABB) 196548637850; (ABL) 196548527274; (AC3) 196548527281; (UUF) 196548527298
What's in the box	Webcam; Quick start guide; Warranty card; USB Type-A cable; Privacy cap

Additional specifications

Cable length	1.5 m
Cable length (imperial)	4.92 ft
Camera resolution	2160p, 4K UHD (3840 x 2160), 30 fps; 1080p, FHD (1920 x 1080), 30 fps; 1080p, FHD (1920 x 1080), 60 fps; 720p, HD (1280 x 720), 30 fps; 720p, HD (1280 x 720), 60 fps
Certified collaboration software	Zoom
Color	Black
Compatible Operating Systems	Windows 10; Windows 11; mac OS 10.10 or later; Chrome OS™
Connection type	Wired USB Type-A
Country of origin	Made in China
Datasheet photo 1	AHID/9cdf79a801879abb70f96300aafb81de40781f78
Datasheet photo 2	AHID/df14f48f28da42a8eb3b6cfc676f3ff2ce10410a
Datasheet photo 3	AHID/2d6a834a7e5a00e3036add42957ae2b66f491b3a
Datasheet photo 4	AHID/bf1836d9f29bf88b955c863defda88dbfdd4c840
Diagonal field of view (dFoV)	100°/90°/78°
Focus type	Auto focus
Framing type	Auto framing
Lens cover capabilities	Attachable
Management Software	Poly lens
Microphone type	Dual noise-reducing microphone
Package dimensions (W x D x H)	5.47 x 4.33 x 2.87 in
Package weight	0.908 lb
Technology logo 1	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08373057.png
Technology logo 2	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08737444.png
Technology logo 3	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08737446.png
Technology logo 4	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08737445.png
Tilt	90°
Total camera resolution (megapixels)	8 MP
UNSPSC code	45121520
UVC-compliant applications	Microsoft Teams; Zoom; BlueJeans; Cisco Webex; Google Meet; GoToMeeting; Vidy; OBS; Xspilt; Twitch; YouTube; Fuze
Zoom capability	4x
swivel	360°

Disclaimer — Copyright

Microsoft, Encarta, MSN, and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Mac® is a trademark of Apple Inc., registered in the U.S. and other countries and regions. Chrome is a trademark of Google LLC.

Actual product may vary from image shown.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 13, 2024 9:29 PM UTC+0000