

# AXIS Camera Station S1264 Rack Recording Server

## Flexible and scalable recording server

Featuring powerful components, this secure, scalable recording server offers high performance and support for powerful applications and features. It includes AXIS Camera Station licenses and multiple RAID configurations for flexible storage and multiple redundancy configuration. And, a Trusted Platform Module (FIPS 140-2 level 2 certified) ensures secure storage of all cryptographic keys and certificates. Available in three variants with a choice of storage, it comes preloaded with preconfigured software. Plus, all supported products are available in one price list for a one-stop-shop experience. Furthermore, it offers services such as Keep Your Hard Drive, Next Business Day Onsite Support, and a 5-year warranty.

- > **Scalable and powerful solution**
- > **Flexible storage options including RAID**
- > **Available in 3 variants: 24 TB, 64 TB, and 144 TB**
- > **64 AXIS Camera Station licenses included**
- > **Extensive support and 5-year warranty**



# AXIS Camera Station S1264 Rack Recording Server

<b>Models</b>	S1264 Rack 24 TB S1264 Rack 64 TB S1264 Rack 144 TB	2x RJ45 1 Gbps
<b>Licenses</b>	64 AXIS Camera Station core licenses included and tied to the hardware. Can be upgraded with additional licenses (sold separately).	<b>Video</b> <b>Video streaming</b> Not intended for local viewing of video. Recommended to use Axis workstations.
<b>System scalability</b>	Qualified for 192 doors and a recording bitrate up to 850 Mbit/s, 96 video channels at 4 MP, 30 fps in a retail scenario. Check AXIS Site Designer for storage estimates. Tested with: 20 live view clients 3 clients performing heavy playback or scrubbing operations For systems with over 80 video channels or a recording bitrate over 750 Mbit/s, we recommend setting the size allocated for recording to 95%.	<b>Cybersecurity</b> <b>Documentation</b> <i>AXIS Camera Station Hardening Guide</i> <i>Axis Vulnerability Management Policy</i> <i>Axis Security Development Model</i> To download documents, go to <a href="https://axis.com/support/cybersecurity/resources">axis.com/support/cybersecurity/resources</a> To read more about Axis cybersecurity support, go to <a href="https://axis.com/cybersecurity">axis.com/cybersecurity</a>
<b>Hardware</b>		
<b>Processor</b>	Intel® Xeon® Silver	<b>General</b> <b>Operating system</b> Microsoft® Windows® 10 IoT Enterprise LTSC 2021 Built-in operating system recovery: yes Operating system drive: 240 GB SSD
<b>Memory</b>	S1264 Rack 24 TB 2x 8 GB S1264 Rack 64 TB 2x 8 GB S1264 Rack 144 TB 2x 16 GB	<b>Remote server management</b> iDRAC 9 express license
<b>Storage</b>	<b>S1264 Rack 24 TB</b> Hot swappable Enterprise Class HDD Total HDD slot: 12 Free HDD slot: 6 Out-of-the-box storage: 20 TB after RAID 5 Out-of-the-box capacity without RAID: 24 TB (6x4 TB) <b>S1264 Rack 64 TB</b> Hot swappable Enterprise Class HDD Total HDD slot: 12 Free HDD slot: 4 Out-of-the-box storage: 56 TB after RAID 5 Out-of-the-box capacity without RAID: 64 TB (8x8 TB) <b>S1264 Rack 144 TB</b> Hot swappable Enterprise Class HDD Total HDD slot: 12 Free HDD slot: 0 Out-of-the-box storage: 120 TB after RAID 6 Out-of-the-box capacity without RAID: 144 TB (12x12 TB)	<b>Security</b> Support for encrypted operating system drive and recording drive FIPS 140-2 level 2 certified Trusted Platform Module (TPM 2.0) <b>Operating conditions</b> 10 °C to 35 °C (50 °F to 95 °F) Humidity 20–80% RH (non-condensing) <b>Storage conditions</b> -40 °C to 65 °C (-40 °F to 149 °F)
<b>RAID</b>	<b>S1264 Rack 24 TB</b> Factory RAID level: 5 Supported RAID levels: 0, 1, 5, 6, 10 <b>S1264 Rack 64 TB</b> Factory RAID level: 5 Supported RAID levels: 0, 1, 5, 6, 10 <b>S1264 Rack 144 TB</b> Factory RAID level: 6 Supported RAID levels: 0, 1, 5, 6, 10	<b>Approvals</b> EMC EN 55032 Class A, EN 55024, EN 55035, EN 61000-3-2, EN 61000-3-3, FCC Part 2 and 15 Class A, ISED ICES-003 Class A, RCM AS/NZS CISPR 32 Class A, KS C 9832 Class A, KS C 9835, VCCI 32-1 Class A, BSMI <b>Safety</b> IEC/EN/UL 60950-1, IEC/EN/UL 62368-1, EN 62311, NOM-019-SCFI-1998
<b>Power</b>	2 x 800 W hot-plug redundant power supplies (included) (100–240 V AC, 9.2–4.7 A, 50/60 Hz)	<b>Compliance</b> TAA (Trade Agreements Act)
<b>Connectors</b>	<b>Front side:</b> 1x USB 2.0 1x VGA 1x iDRAC direct port <b>Rear side:</b> 1x USB 2.0 1x USB 3.0 1x VGA 1x iDRAC dedicated Ethernet port	<b>Dimensions</b> 721.62 x 482 x 87 mm (28.42 x 19 x 3.43 in), 2U chassis <b>Rail sizing:</b> Type: sliding Minimum rail mounting depth: 719 mm (28.31 in) Square-hole rack adjustment range: 631–868 mm (24.85–34.18 in) For more information, see the Dell EMC Enterprise Systems Rail Sizing and Rack Compatibility Matrix
		<b>Weight</b> S1264 Rack 24 TB 20.8 kg (45.86 lb) S1264 Rack 64 TB 22.9 kg (50.49 lb) S1264 Rack 144 TB 25.6 kg (56.44 lb)
		<b>Included accessories</b> Dell Ready Rails 2U Sliding Rails, 2x C13 to C14 power cords for rack PDU (Wall plug power cords are not included)
		<b>Optional accessories</b> Axis workstations Enterprise hard drives For more accessories, see <a href="https://axis.com">axis.com</a>
		<b>Services</b> Next Business Day Onsite Support Keep Your Hard Drive
		<b>Warranty</b> 5-year warranty, see <a href="https://axis.com/warranty">axis.com/warranty</a>

## AXIS Camera Station

For details about AXIS Camera Station features and functions, see the AXIS Camera Station datasheet on [axis.com](https://axis.com)