




LATITUDE 3120 FOR EDUCATION

## Boundless, hands-on learning



### DESIGNED KID-TOUGH TO ENDURE THE LONG SCHOOL DAY AND BEYOND

With a brand new chassis design, the Dell Latitude 3120 raises the bar on durability and serviceability. Laser etching on the front and back covers provides enhanced grip to help prevent drops and slipping. It comes with a spill-resistant keyboard and captive keys, and its rubberized edges and rounded corners minimize drop impacts. The palmrest-mounted keyboard adds extra strength and rigidity to the overall product, while remaining easily removable for improved access to internal components. On the 3120 2-in-1, the Dragontrail Pro glass provides scratch resistance, as well as better protection if the system is dropped on its corners.



### STAY CONNECTED AND PRODUCTIVE FOR UNLIMITED LEARNING

Built with Intel® Celeron Quad-Core and Pentium Quad-Core Processors, students can confidently power through the day on the Dell Latitude 3120. Lessons are uninterrupted with extended battery life, and the system will charge up to 80% in about an hour with ExpressCharge. Connect better than ever with USB Type-C™ (Pentium only) for greater flexibility, including charging, display support, and data transfer. Engage students with the optional world-facing camera, which provides dual camera support that enables flipped viewing and recording angles. Improve performance with optional WiFi 6 for faster speed, increased capacity, and better power efficiency. The 3120 2-in-1 provides support for the optional Dell Active Pen as well as pencil support, so students can write, take notes, or draw diagrams from any angle or mode - flat, tent, tablet or laptop.



### RIGOROUSLY TESTED TO WITHSTAND THE DEMANDS OF STUDENT USE

Dell's testing of its education devices is based on real-world evaluation and an understanding of the cumulative effects of impacts over time. The Dell Latitude 3120 has been tested more rigorously than ever for maximum endurance. In addition to passing 17 MIL-STD 810G tests, it survives tens of thousands of hinge-cycle tests (the opening and closing of the device), as well as 12-ounce liquid spills on its spill-resistant keyboard. Additionally, it endures thousands of micro-drops, 4-inch drops from multiple angles that simulate every day student use over a period of 3 to 5 years.



### READY FOR EVERY LEARNING ENVIRONMENT

As learning models continue to shift and evolve, mobile education devices are being put to the test more than ever before. Designed with durability and mobility top of mind, the Dell Latitude 3120 is more than up to the challenge. Compact and strong, it provides the right balance of performance and productivity for students on the move, and delivers everything learners need – whether in the classroom, at home, or anywhere that learning takes them.

# Recommended Accessories

LATITUDE 3120 FOR EDUCATION

## ULTIMATE CLASSROOM SOLUTIONS



DELL 24 MONITOR |  
E2420HS

This 23.8" monitor features a height-adjustable stand, Full HD resolution, and integrated speakers, all in a space-saving design.



WALTOP EDUCATION  
ACTIVE PEN

Enable personalized learning with your Latitude 3120 2-in-1 and the Waltop Education Active Pen. Provides a natural pen-on-paper writing experience for drawing diagrams or taking notes.



DELL 75 4K INTERACTIVE TOUCH  
MONITOR | C7520QT

Experience natural touch functionality that allows you to annotate with your fingers, write with a stylus, or even erase written content with the palm of your hand with virtually no lag. Includes our exclusive Dell Screen Drop feature for users of different heights.

## LEARNING ON-THE-GO



DELL ESSENTIAL BACKPACK 15 | ES1520P

This lightweight yet roomy backpack is perfect for carrying and protecting student essentials, including laptop, study materials, bottled drink, and umbrella.




DELL STEREO HEADSET | UC150

Students will experience great audio clarity with the Dell Pro Stereo Headset UC150 and can get started right away with plug and play technology.



DELL MOBILE WIRELESS MOUSE | MS3320W

Work seamlessly with dual mode connectivity (2.4GHz wireless or bluetooth) and 36 months\* battery life.



DELL ADAPTER - USB-C TO HDMI/VGA/ETHERNET/  
USB 3.0 - DA200

Use this compact USB-C adapter to connect to any external display which supports VGA or HDMI inputs.

# Features & Technical Specifications

## LATITUDE 3120 FOR EDUCATION

Feature	Latitude 3120 Technical Specifications <sup>1</sup>
Processor Options <sup>1</sup>	Intel® Celeron QC & Pentium QC Processors
Operating System <sup>1</sup>	Microsoft® Windows 10 Pro 64 bit Microsoft® Windows 10 Home 64 bit
Memory Options <sup>1,2,3</sup>	DDR4 2933MHz; Single Channel, supporting 4GB (Celeron) LPDDR4 2933MHz; Single Channel, supporting 4GB; Dual Channel, supporting 8GB & 16GB (Pentium)
Chipset <sup>1</sup>	Integrated with the Processor
Graphics <sup>1,10</sup>	Intel® HD Graphics
Display <sup>1</sup>	11.6" HD (1366 x 768) Anti-glare (16:9) 11.6" HD (1366 x 768) Touch, Dragontrail Pro glass, Pen Support (16:9)
Storage Options <sup>1,3</sup>	64GB eMMC (Celeron only) 128GB SSD 256GB SSD
Security <sup>1</sup>	Intel PTT
Docking <sup>1</sup>	Optional USB Dock available
Optical Drive Options	External Options Only
Multimedia <sup>1</sup>	High Quality Speakers Headset/mic combo jack Integrated webcam with microphone Optional World Facing Camera (2-in-1 only)
Battery Options <sup>1,5</sup>	3-Cell, 40 WHr Polymer, ExpressCharge™ capable 4-Cell, 53 WHr Polymer, ExpressCharge™ capable
Power Options <sup>1</sup>	65W adapter, 7.4mm barrel 65W adapter, USB Type-C
Connectivity Options	<b>Wireless LAN:</b> Intel® Dual Band Wireless AC 9560 (802.11ac) 2x2 + Bluetooth 5.1 (Celeron) Intel® Dual Band Wireless AX 201 (802.11ax) 2x2 + Bluetooth 5.1 (Pentium)
Ports, Slots & Chassis <sup>1</sup>	2 USB 3.2 Gen 1 1 USB Type-C (Pentium) HDMI Headset/mic combo jack Wedge-shaped lock slot
Dimensions & Weight <sup>1,11</sup>	Width: 11.8" / 300.8mm Depth: 8.1" / 204.8mm Height: 0.82" / 20.9mm (Laptop) Height: 0.82" / 21.4mm (2-in-1)  Starting weight: 2.97lbs/1.35Kg (Laptop) Starting weight: 3.12lbs/1.42Kg (2-in-1)
Regulatory and Environmental Compliance <sup>1</sup>	Regulatory Model: P32T/P33T Regulatory Type: P32T001/P33T001 ENERGY STAR 8.0 <sup>1</sup> EPEAT Silver Registered. For specific country participation and rating, please see <a href="http://www.epeat.net">www.epeat.net</a> BFR/PVC free <sup>7</sup> TCO NB 8.0
Input <sup>1</sup>	Spill and Pick resistant keyboard Multi-touch Touchpad Dell Active Pen (2-in-1) No. 2 Pencil (2-in-1)
Systems Management <sup>1</sup>	
Warranty and Service <sup>1</sup>	Limited Hardware Warranty <sup>4</sup> Standard 1 year Mail-in Service after Remote Diagnosis <sup>8</sup> optional 3, 4 and 5 year hardware warranty extensions and 3-5 year Dell ProSupport contracts available <sup>9</sup>
Peripheral Ecosystem <sup>1</sup>	Purpose built ecosystem to enable productivity on the go or in the classroom. Includes Dell Cases, Dell Mobile Carts, and other accessories





## LATITUDE 3120 FOR EDUCATION

# Boundless, hands-on learning

1 Offering may vary by country and by configuration

2 A 64-bit operating system is required to support 4GB or more of system memory.

3 GB means 1 billion bytes and TB equals 1 trillion bytes; actual capacity varies with preloaded material and operating environment and will be less.

4 Limited Hardware Warranty: For copy of Limited Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see [www.dell.com/warranty](http://www.dell.com/warranty)

5 Battery support is dependent upon graphics support. Check technical guides for detailed support

6 COMPUTRACE Not a Dell offer. Certain conditions apply. For full details, see terms and conditions at [www.absolute.com/en/about/legal/agreements](http://www.absolute.com/en/about/legal/agreements).

7 Dell Education Series are brominated flame retardant free (BFR-free) and polyvinyl chloride free (PVC-free); meeting the definition of BFR-/PVC-free as set forth in the iNEMI Position Statement on the 'Definition of Low-Halogen Electronics (BFR-/CFR-/PVC-free)'. Plastic parts contain less than 1,000 ppm (0.1%) of bromine (if the Br source is from BFRs) and less than 1,000 ppm (0.1%) of chlorine (if the Cl source is from CFRs or PVC or PVC copolymers). All printed circuit board (PCB) and substrate laminates contain bromine/chlorine total less than 1,500 ppm (0.15%) with a maximum chlorine of 900 ppm (0.09%) and maximum bromine being 900 ppm (0.09%).

8 Onsite Service after Remote Diagnosis: Remote Diagnosis is determination by online/phone technician of cause of issue; may involve customer access to inside of system and multiple or extended sessions. If issue is covered by Limited Hardware Warranty ([www.dell.com/warranty](http://www.dell.com/warranty)) and not resolved remotely, technician and/or part will be dispatched, usually within 1 business day following completion of Remote Diagnosis. Availability varies. Other conditions apply.

9 Dell Services: Availability and terms of Dell Services vary by region. For more information, visit [www.dell.com/servicedescriptions](http://www.dell.com/servicedescriptions).

10 GB means 1 billion bytes and TB equals 1 trillion bytes; significant system memory may be used to support graphics, depending on system memory size and other factors.

11 Weights vary depending on configuration and manufacturing variability.