



Hewlett Packard
Enterprise

HPE STOREEASY 1660 STORAGE WITH MICROSOFT WINDOWS SERVER IOT 2019 (R7G24B)

Flexible File and Application Storage



WHAT'S NEW

- The new HPE StoreEasy 1660 and HPE StoreEasy1860 models are built from HPE ProLiant DL380 Gen10 Plus technologies including Broadcom® MegaRAID Gen10+ Controllers and Intel Xeon 4309Y processor.

OVERVIEW

Every day, your organization faces challenges. Why should file storage be one of them?

HPE StoreEasy 1000 Storage with the HPE StoreEasy Management Console provides easy-to-manage centralized network attached storage for securely storing documents,

- The new affordable HPE StoreEasy 1460 and StoreEasy 1560 models use software RAID. The existing HPE StoreEasy 1460 and HPE StoreEasy 1560 use hardware RAID and deliver the highest performance.
- Support for new 18 TB hard drives (on select models), for a maximum of 504 TB of raw internal capacity on the HPE StoreEasy 1660 expanded storage.
- HPE StoreEasy Management Console adds simplified storage provisioning and more intelligent consumption monitoring.

images, audio, and video files. HPE StoreEasy 1000 Storage offers flexible, efficient, and reliable file storage, right-sized for your organization's needs and budget, without compromising on quality or capabilities. It is available in a diverse range of form factors, capacities, and performance options, and can help you get more out of your investment while you protect your indispensable digital assets in an evolving threat landscape. With that in mind, the HPE StoreEasy Management Console provides a simplified management experience developed by HPE that consolidates multiple interfaces, automates storage tasks, and centralizes monitoring. Now you can spend less time on your file storage and more time on your business.

FEATURES

Customized and Tailored for File Storage

HPE StoreEasy 1000 Storage is built on industry-leading HPE ProLiant Gen10 DNA and comes with pre-configured hardware and a Microsoft® Windows® Server for Storage operating system. Get your NAS out of the box and online fast with tools that simplify installation and curb common configuration errors.

The HPE StoreEasy Management Console makes file sharing twice as simple to manage [1], enabling administrators with any level of storage expertise to simplify core operations, including management of volumes, file shares, quotas, snapshots, network services, and external enclosures.

Leverage the HPE StoreEasy Management Console's data-driven insights on storage usage and performance to simplify planning. Quickly configure low-capacity email alerts to reduce disruption caused by capacity limitations, and easily identify maintenance windows to plan for capacity expansion.

Simplified provisioning through the HPE StoreEasy Management Console allows admins to quickly input desired usable capacity and provision based on best practices, while economical hard disk drive (HDD) bundles make it easier for you to buy and deploy additional capacity over time.

Efficiency Saves you Time and Money

Spend less time on storage by leveraging the HPE StoreEasy Management Console to manage and monitor your HPE StoreEasy appliance instead of numerous, disparate Windows utilities.

Save storage space with built-in granular file deduplication and compression - even for very large files and volumes. Define and apply quotas in StoreEasy Management Console to control consumption and alert admins to low capacity.

Built-in file sync and share enables employees, mobile workers and distributed teams to access their work files from any internet-connected desktop, smartphone, or tablet. Organizations can apply policies to wipe devices remotely and enforce lock screen passwords to protect data on employee devices.

Advanced data management capabilities automatically improve use of resources, comply with data retention policies, and enhance protection of sensitive files, even if they're downloaded from HPE StoreEasy and emailed to unauthorized recipients.



File Classification Infrastructure can dynamically identify files based on sensitivity and implement sophisticated access controls based on your organization's requirements using Active Directory Rights Management Services.

Multi-dimensional Protection for Your Data

Built from the world's most secure industry-standard servers [2] the sixth generation of HPE StoreEasy 1000 Storage provides expanded security capabilities to help you protect your employees, customers, and organization in an evolving threat landscape.

HPE StoreEasy 1000 Storage protects data at rest with file system encryption and Microsoft BitLocker® drive encryption, as well as data in flight through SMB encryption and signing, and at the physical level with a lockable bezel.

Install and run endpoint protection such as antivirus on the system itself, reducing the cost and complexity of connecting an external endpoint protection server. Prevent against data loss with Volume Shadow Copy Service online snapshots and simple cloud backup to Microsoft Azure.

Highly Resilient to Prevent Disruption to Your Business and Users

HPE StoreEasy 1000 Storage increases uptime with standard features including nearly continuous health monitoring with HPE Active Health System, redundant components, file system online self-healing, online verification, and rapid repair that reduces downtime from file corruption to minutes.

Protect up to 100TB of data from simple errors or massive failures using built-in Microsoft Distributed File System Replication (DFS-R).

Get comprehensive system support from HPE file storage experts with onsite parts and labor warranty for the system and telephone support for pre-installed software. Expand or enhance your base support coverage through optional services from HPE Pointnext for HPE StoreEasy 1000 Storage.

Use advanced diagnostics and near-continuous monitoring, enabled by the HPE Integrated Lights-Out (iLO) Management Engine, to deliver greater stability and shorter downtimes.



Technical specifications

HPE StoreEasy 1660 Storage with Microsoft Windows Server IoT 2019

Product Number	R7G24B
Capacity	Depends on configuration (288 TB raw maximum)
Host interface	Option to choose
Protocol supported	SMB, NFS, iSCSI over Ethernet, FTP/S, HTTP/S
Replication support	Microsoft Distributed File System Replication (DFS-R) for data sets up to 100 TB
Storage expansion options	All HPE StoreEasy models support external expansion using HPE MSA SAN Storage or D3X10, D6020, and D8000 Disk Enclosure product families. A Fibre Channel, SAS, or iSCSI connection must be added to support MSA SAN Storage (note that high-availability clustering is not supported) while a Smart Array controller with external ports must be added to support external Disk Enclosures.
Compatible operating systems	Microsoft® Windows® Server IoT 2019 for Storage Standard Edition is pre-installed. Client operating systems supported include Microsoft® Windows®, Mac OS, Linux®, and Unix.
Management features	HPE StoreEasy Management Console version; HPE iLO5; HPE MR Storage Administrator; HPE Smart Storage Administrator; Windows Server® Manager and utilities
Drive description	Does not include data drives standard. 12 x LFF (3.5") hot-plug front drive bays standard 4 x LFF hot-plug mid-chassis drive cage is optional
Clustering support	Not supported on HPE StoreEasy 1000 Storage appliances
HD type	Hot-plug SATA or SAS, LFF (3.5")
Snapshot support	Microsoft Volume Shadow Copy Service (VSS)
Form factor (fully configured)	2U rack mount
Product Dimensions (metric)	8.73 x 44.54 x 74.9 cm (without bezel)
Weight	33.9 kg maximum (without rear drives)
Warranty	3/3/3 system warranty includes three years of parts, three years of labor, three years of onsite support coverage, next business day response. Software media is warranted to be free of physical defect for a period of 90 days from delivery. Additional information regarding worldwide limited warranty and technical support is available at: https://support.hpe.com/hpsc/wc/public/home



For additional technical information, available models and options, please reference the [QuickSpecs](#)

HPE POINTNEXT SERVICES

[HPE Pointnext Services](#) brings together technology and expertise to help you drive your business forward and prepare for whatever is next.

Operational Services from HPE Pointnext Services

[HPE Pointnext Tech Care](#) provides fast access to product-specific experts, an AI-driven digital experience, and general technical guidance to help enable constant innovation. We have reimagined IT support from the ground up to deliver faster answers and greater value. By continuously searching for better ways to do things—as opposed to just fixing things that break—HPE Pointnext Tech Care helps you focus on achieving your business goals.

[HPE Pointnext Complete Care](#) is a modular, edge-to-cloud IT environment service that provides a holistic approach to optimizing your entire IT environment, and achieving agreed upon IT outcomes and business goals through a personalized and customer-centric experience. All delivered by an assigned team of HPE Pointnext Services experts.

HPE Integration and Performance Services help you customize your experience at any stage of your product lifecycle with a menu of services based on individual needs, workloads, and technologies.

- Advise, design, and transform
- Deploy
- Integrate and migrate
- Operate and improve
- Financial Services
- GreenLake Management Services
- Retire and sanitize
- IT Training and personal development

Other related services

[HPE Education Services](#) delivers a comprehensive range of services to support your people as they expand their skills required for a digital transformation. Consult your HPE Sales Representative or Authorized Channel Partner of choice for any additional questions and support options.

Defective Media Retention is optional and allows you to retain Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

HPE GREENLAKE

[HPE GreenLake](#) is HPE's market-leading IT as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model. HPE GreenLake delivers public cloud services and infrastructure for workloads on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

[1] Based on HPE internal testing with 50% fewer tools and fewer actions for key NAS administrative tasks

[2] Based on results of external, third-party penetration testing of servers from different manufacturers

Make the right purchase decision.
Contact our presales specialists.

[Call for availability](#)



Chat now (sales)



Call now



Buy now



Share now



Get updates



Hewlett Packard
Enterprise

© Copyright 2022 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Broadcom is a registered trademark of Broadcom, Inc.; Microsoft, Windows, and Windows Server are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. UNIX is a registered trademark of The Open Group. Linux is the registered trademark of Linus Torvalds in the U.S. and other countries. All other third-party trademark(s) is/are property of their respective owner(s).

Image may differ from the actual product
[PSN1014678387IEEN](#), November, 2022.