

### PERFORMANCE

#### Display Size

49"

#### View Area

1198.1x337.0 mm

#### Panel

In-Plane Switching

#### Backlight

WLED

#### Aspect Ratio

32:9

#### Resolution

5120x1440

#### Pixel Pitch

0.234x0.234 mm

#### Dot / Pixel Per Inch

109 dpi

#### View Angle (H / V)

178° / 178°

#### Response Time

4ms (Extreme mode) / 6ms (Normal mode)

#### Color Support

1.07 Billion

#### Refresh Rate

60Hz

#### Brightness

350 nits

#### Contrast Ratio

2000:1

#### Color Gamut

98% DCI-P3

#### Screen Surface Treatment

Anti-glare

#### Curvature

3800R

#### Camera

Modular Camera Support

#### Microphone

None

#### Speakers

5Wx2

#### Power Consumption (Typical / Maximum)

58W / 265W

#### Power Adapter

Integrated

#### Touchscreen

None

#### Smart System

None

### DESIGN

#### Stand

Tilt, Swivel, Height Adjust Stand

#### Case Color

Raven Black

#### Side Bezel Width

2.1 mm

#### Dimensions with Stand (HxWxD)

576.3 x 1215.1 x 253.9 mm / 22.69 x 47.84 x 9.99 inches

#### Weight (Including Stand)

15.8 kg / 34.8 lbs.

#### Mounting

Supports VESA mount 100 x 100 mm & 200 x 100 mm

#### ThinkCentre® M Series Support

Tiny Support

### CONNECTIVITY

#### USB Port

4x USB 3.2 Gen 1, 1x USB-C® 3.2 Gen 1, 1x USB-B 3.2 Gen 1, 1x Thunderbolt™ 4 Out, 1x Thunderbolt 4 In

#### Video Connector

2x HDMI® 2.1, 1x DP 1.4, 1x Thunderbolt 4 in, 1x Thunderbolt 4 out

#### Network Connectivity

1x RJ45, Ethernet (10M/100M/1000M)

### SERVICE

#### Base Warranty

3-year

### CERTIFICATIONS

#### Environmental Certification

ENERGY STAR® Certified, TCO 9.0, TCO edge 2.0, EPEAT™ Gold, RoHS

#### Ergonomic Certification

Eyesafe® Display 2.0, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Eye Comfort

#### Sync Technology

None

### Special Features

- Factory Calibration: Avg. Delta E<2
- Picture In Picture (PIP) / Picture By Picture (PBP) Support
- True Split
- KVM Switch
- Natural Low Blue Light
- Lenovo® ThinkColour (Lenovo Display Control Center) Support  
ThinkColour can only be used with Windows® 10 and Windows 11
- Smart Power  
The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device

### SOFTWARE

#### Operating System

Support Windows 10, Windows 11

### ACCESSORIES

#### Video Cables

DP cable (NA & LA only), USB-A to USB-B cable, Thunderbolt™ cable

### MODEL

Announce Date : 2023-05-11  
EAN / UPC : 0196802297486 / 196802297486 / None  
JAN



Product image is a sample, it may not match the real color of this model

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.


## Recommended Accessories



### Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...



### Lenovo Security Cable Lock

57Y4303

The Lenovo Security Cable Lock allows customers to manage physical security access within the enterprise, offices, schools, libraries, or in other public spaces. Cable locks help reduce theft, and increase physical as...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference