

PERFORMANCE

Processor

Intel® Core™ i7-1185G7 (4C / 8T, 3.0 / 4.8GHz, 12MB)

Graphics

Integrated Intel Iris® Xe Graphics

Chipset

Intel SoC Platform

Memory

16GB Soldered LPDDR4x-4266

Memory Slots

Memory soldered to systemboard, no slots, 8-channel

Max Memory

16GB soldered memory, not upgradable

Storage

512GB SSD M.2 2280 PCIe® x4 NVMe® Opal 2.0

Storage Support

One drive, up to 2TB M.2 2280 SSD

Storage Slot

One M.2 2280 PCIe 4.0 x4 slot

Audio Chip

High Definition (HD) Audio, Realtek® ALC3306 codec

Speakers

Stereo speakers, 2W x2 woofers and 0.8W x2 tweeters, Dolby® Atmos®

Camera

HD 720p + IR Hybrid with Privacy Shutter

Microphone

4x, Array

Battery

Integrated 57Wh

Max Battery Life

MobileMark® 2014: 21.0 hr

MobileMark 2018: 16.1 hr

JEITA 2.0: 23.9 hr

Power Adapter

65W USB-C® (2-pin)

DESIGN

Display

14" WUXGA (1920x1200) IPS 400nits Anti-glare, 100% sRGB, Low Power, Touch

Touchscreen

OGS, 10-point Multi-touch

Keyboard

Backlit, English

Case Color

Storm Grey

Case Material

Aluminium (Top), Aluminium (Bottom)

Pen

Lenovo® Integrated Pen

Dimensions (WxDxH)

314.4 x 223 x 14.99 mm (12.38 x 8.78 x 0.59 inches)

Weight

Starting at 1.399 kg (3 lbs)

SOFTWARE

Operating System

Windows® 11 DG Windows 10 Pro 64, English

CONNECTIVITY

Ethernet

100/1000M (Mini RJ-45)

WLAN + Bluetooth®

Intel Wi-Fi® 6 AX201, 11ax 2x2 + BT5.1

Standard Ports

- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 2x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4a)
- 1x HDMI® 2.0
- 1x Headphone / microphone combo jack (3.5mm)

Docking

Various docking solutions supported via Thunderbolt / USB-C.

For more compatible docking solutions, please visit [Docking for ThinkPad® X1 Yoga® Gen 6](#)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Physical Locks

Kensington® Nano Security Slot™

Other Security

- Human Presence Detection
- IR camera for Windows® Hello
- Camera privacy shutter

MANAGEABILITY

System Management

Intel® vPro®

SERVICE

Base Warranty

3-year, Courier or Carry-in

CERTIFICATIONS

Green Certifications

- EPEAT™ Gold
- ENERGY STAR® 8.0
- TCO Certified
- RoHS compliant

Other Certifications

- Intel Evo™ Platform
- TÜV Rheinland® Low Blue Light

Mil-Spec Test

MIL-STD-810H military test passed

MODEL

TopSeller : Yes

Announce Date : 2022-12-09

EAN / UPC / JAN : 196803865394

End of Support : 2027-10-02



intel

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo 65W USB-C AC Travel Adapter

40AW0065WW

STREAMLINE YOUR LIFE WITH A 65W USB-C AC TRAVEL ADAPTER. Changing the way you travel for business or pleasure, the Lenovo 65W USB-C AC Travel Adapter eliminates the need for multiple chargers. Power your USB-C devices...

Recommended Services

BEST	4Y Lenovo Protect (Premier Support + Accidental Damage Protection + Keep Your Drive + 3Y Sealed Battery + International Upg) (5PSON73238)
BETTER	3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + Sealed Battery + International Upg) (5PSON73216)
GOOD	3Y Lenovo Support (Premier Support + Keep Your Drive + Sealed Battery + International Upg) (5PSON73159)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference