

PERFORMANCE

Processor

Intel® Core™ i7-12700H, 14C (6P + 8E) / 20T, P-core 2.3 / 4.7GHz, E-core 1.7 / 3.5GHz, 24MB

Graphics

Intel Arc™ A370M 4GB GDDR6

Chipset

Intel SoC Platform

Memory

32GB Soldered LPDDR5-4800

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

32GB soldered memory, not upgradable

Storage

1TB SSD M.2 2280 PCIe® 3.0x4 NVMe®

Storage Support

One drive, up to 512GB M.2 2242 SSD or 1TB M.2 2280 SSD

Storage Slot

One M.2 2280 PCIe 4.0 x4 slot

Card Reader

4-in-1 Card Reader

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, optimized with Dolby® Atmos®

Camera

HD 720p + IR, ToF Sensor

Microphone

2x, Array

Battery

Integrated 75Wh

Max Battery Life

MobileMark® 2018@200nits: 6.98 hr
Local video (1080p) playback@150nits: 12.83 hr

Power Adapter

135W Slim Tip (3-pin)

DESIGN

Display

16" 2.5K (2560x1600) IPS 500nits Glossy, 100% sRGB, 120Hz, DisplayHDR™ 400, Dolby Vision™, Eyesafe®, Glass, Touch

Touchscreen

OGS, 10-point Multi-touch

Keyboard

Backlit, English (US)

Case Color

Storm Grey

Surface Treatment

Aluminium Stamping (Anodized)

Case Material

Aluminium (Top), Aluminium (Bottom)

Dimensions (WxDxH)

356.81 x 247.42 x 17.4 mm (14.05 x 9.74 x 0.69 inches)

Weight^[1]

Around 2.08 kg (4.59 lbs)

SOFTWARE

Operating System

Windows® 11 Home, English

Bundled Software

Office Trial

CONNECTIVITY

Ethernet

No Onboard Ethernet

WLAN + Bluetooth®

Wi-Fi® 6, 11ax 2x2 + BT5.1

Standard Ports

- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 1x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)
- 1x HDMI® 2.0
- 1x Card reader
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

Monitor Cable

None

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0

Fingerprint Reader

None

Other Security

IR camera for Windows Hello

SERVICE

Base Warranty

1-year, Courier or Carry-in

Included Upgrade

1Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WSOT73712)

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 6
- ErP Lot 26
- RoHS compliant

Other Certifications

- Intel® Evo™ Platform
- Eyesafe® Certified
- TÜV Rheinland® Low Blue Light (Hardware Solution)

MODEL

TopSeller : No Announce Date : 2022-05-07

EAN / UPC / JAN : 196379855652 End of Support : 2028-06-13



intel

To see more note information, please link to https://psref.lenovo.com/Detail/Lenovo_Slim_7_16IAH7?M=82VB0000US

· Lenovo reserves the right to change specifications or other product information without notice.
· Battery life is an estimated maximum. Actual battery life may vary by hardware or system settings, active applications, battery conditioning, etc.
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad X1 Active Noise Cancellation Headphones

4XD0U47635

The ThinkPad X1 Active Noise Cancellation headphones provide rich, first-class listening and calling in any noise environment. Lenovo has partnered with Synaptics AudioSmartto create industry-leading headphones with H...



ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

The ThinkPad Hybrid USB-C with USB-A Dock expands the capabilities of most any laptop, new or old, making it perfect for enterprise customers with mixed-PC or shared-desk environments. Featuring enterprise-class manag...

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference