

# Topaz 3

13<sup>th</sup> Gen Simply NUC Consumer NUC – NUC13TZi5



Simply NUC<sup>®</sup>

# Topaz 3 i5

13<sup>th</sup> Gen Simply NUC Consumer NUC – NUC13TZi5

## Evolve your Mini PC Experience

The Topaz 3 NUC harnesses Intel's latest 13th Gen Raptor Lake 1340P Processor with Iris Xe graphics to provide the most crisp computing experience to date. With up to 64GB of DDR4-3200 memory and up to 10TB of M.2 storage, Topaz 3 has the capabilities you need to evolve your mini PC experience or corporate infrastructure to the latest and greatest technology available. Intel's 13th Gen 1340P processor ushers a host of new and improved features including increased core counts and an upgraded Intel® Thread Director to increase both your efficiency and your productivity.

## Crystal Clear, Clean & Secure Computing

From a home theater to a digital signage kiosk, the Intel® Iris Xe Graphics in Topaz 3 have you covered. With support for up to four 4K displays, you can enjoy crisp visuals from every angle.

Take advantage of super-fast networking with dual 2.5Gb LAN ports and onboard TPM 2.0, giving you a robust and secure connection to your home or office network, or ditch the cabling and go wireless with Wi-Fi 6E and Bluetooth 5.3 for that sleek setup look, without sacrificing performance and reliability.

## The Number One Choice for your Next Mini PC

Topaz 3 offers a plethora of customization options while maintaining that 4x4 footprint people love. From Gen4 PCIe drives, to I/O options like additional USB ports and serial adapters via the replaceable lid, you have the versatility you need to meet your use case. The Topaz 3 NUC with a 13th Gen Intel® Core 1340P Processor is the number one choice for your mini PC needs for both the home and the office, so get yours, today.

## Features

- 13th Gen Intel® Core™ i5-1340P
- Intel® Iris® Xe Graphics
- 2x DDR4-3200 SO-DIMM Sockets
- 1x M.2 22x80 M-key PCIe x4 socket supporting up to Gen4 NVMe SSDs
- 1x M.2 22x80 socket supporting SATA SSDs
- 2x Intel® 2.5Gb LAN
- Intel® Wi-Fi 6E + Bluetooth 5.3
- 1x HDMI 2.0b
- 1x DisplayPort 1.4
- 4x USB 3.2 Gen 2 Type-A Ports
- 2x USB 3.2 Gen 2 Type-C Ports (Alt-DP1.4)
- 3.5mm stereo headset jack
- TPM 2.0
- Kensington Lock support
- VESA Mount included
- 19v 90W power supply included
- 3-yr Warranty and Support Service



## Customization

- Primary storage socket supporting up to NVMe Gen4 available up to 4TB, up to 8TB Gen3
- Secondary storage socket supporting SATA SSD up to 2TB
- Memory up to 64GB
- OS options including Windows 10/11 & Ubuntu

Intel® Partner Alliance  
Titanium Partner



THINK BIG, go mini

## Technical Specification

<b>Processor</b>	Intel® 13th Gen Core™ i5-1340P   4P+8E/16T   P-Cores: up to 4.6GHz - E-Cores: up to 3.4GHz   12MB Intel® Smart Cache   28W Base Power
<b>Graphics</b>	Intel® Iris Xe Graphics up to 1.45GHz   Up to 4x displays   1x HDMI 2.0b   2x Alt-DP 1.4a++ via USB-C   1x DisplayPort 1.4a++
<b>Memory</b>	Dual DDR4 SODIMMs 1.2V   64GB Max   Up to 3200MHz
<b>Storage</b>	1x M.2 22x80 M-Key x4 PCIe supporting NVMe Gen4 (512GB to 4TB), Gen3 (128GB to 8TB)   1x M.2 22x80 M-Key supporting SATA SSD (128GB to 2TB)
<b>Peripherals</b>	Intel® Wi-Fi 6E AX210   Bluetooth 5.3   2x 2.5Gb LAN (i225-LM)   2x USB 3.2 Gen2 Type-C   4x USB 3.2 Gen2 Type-A
<b>Chassis</b>	115 x 115 x 49mm   Kensington Lock   VESA Mount Kit Support
<b>Expansion</b>	2x USB 2.0 header   1x COM Header   Replaceable Lid
<b>Audio</b>	3.5mm front stereo headset jack
<b>Power</b>	12-19V <sub>DC</sub> Input Range   19V <sub>DC</sub> 90W Power supply included

## Certifications and Regulations

<b>Safety Regulations and Standards</b>	IEC 62368-1   EN 62368-1   CAN/CSA 62368-1
<b>EMC/RF Regulations &amp; Standards</b>	FCC CFR Title 47, Chapter I, Part 15, Subpart B   EN 55024   EN 55032   EN 55035   CISPR 32   ICES-003   ETSI EN.301 489-1   ETSI EN.301 489-17
<b>Environmental Regulations</b>	RoHS Compliant   REACH Compliant
<b>Certified Operating Systems</b>	Windows 10 64-bit (Pro, Home and IoT)   Windows 11 64-bit (Pro, Home and IoT)   Linux (Ubuntu)
<b>Environmental Operating Temp</b>	0°C to +60°C