

HP Elite Mini 600 G9 Desktop PC

Ready for hybrid workstyles

The HP Elite Mini 600 Desktop PC delivers the performance needed to for your enterprise workload, while still being small enough to allow you to take it with you between the home and the office. Equipped with a powerful Intel® Processor², DDR5 memory, and smart deployment options, this is the right PC for desktop users needing flexibility in where they work.

Power for the enterprise

Power through your work with the latest Intel® processor² and fast DDR5 memory that provides the speed and responsiveness needed by multi-taskers. Enjoy the experience on up to four monitors.³

Take your work with you

Your work must continue whether you're in the office or at home. The ultrasmall HP Elite Mini 600 fits easily into most small bags so it's easily moved between your office and home. Mount it behind a compatible HP monitor.⁴

Protected by HP Wolf Security

HP Wolf Security for Business creates a hardware-enforced, always-on, resilient defense. From the BIOS to the browser, above, in, and below the OS, these constantly evolving solutions help protect your PC from modern threats.⁵



*Product image may differ from actual product

Sustainability in action

Help protect our shared future

At least 50 percent of all plastic used in this PC is post-consumer recycled plastic.⁶ The outer box packaging is 100 percent sustainably sourced.⁷ This PC is ENERGY STAR® certified and EPEAT® registered in 23 countries.⁸



HP Elite Mini 600 G9 Desktop PC

Featuring

Power for the enterprise

Power through your work with the latest Intel® processor² and fast DDR5 memory that provides the speed and responsiveness needed by multi-taskers. Enjoy the experience on up to four monitors.³

Take your work with you

Your work must continue whether you're in the office or at home. The ultrasmall HP Elite Mini 600 fits easily into most small bags so it's easily moved between your office and home. Mount it behind a compatible HP monitor.⁴

Protected by HP Wolf Security

HP Wolf Security for Business creates a hardware-enforced, always-on, resilient defense. From the BIOS to the browser, above, in, and below the OS, these constantly evolving solutions help protect your PC from modern threats.⁵

Help protect our shared future

At least 50 percent of all plastic used in this PC is post-consumer recycled plastic.⁶ The outer box packaging is 100 percent sustainably sourced.⁷ This PC is ENERGY STAR® certified and EPEAT® registered in 23 countries.⁸

Handle data with agility

Quickly access and transfer data to keep up with today's changing business requirements with PCIe Gen4 SSDs.

Automatic recovery from firmware attacks

Firmware attacks can completely devastate your PC. Stay protected with HP Sure Start Gen7, the self-healing BIOS that automatically recovers itself from attacks or corruption.

Keep your PC's security protections in place

Stop unwanted changes to security settings and help limit the spread of malware with HP Sure Run Gen5 which identifies, quarantines, and provides reporting on attackers trying to kill processes.

Browse confidently

Help protect your PC from websites and read and edit Microsoft Word files and read-only PDF attachments with malware, ransomware, or viruses with hardware-enforced security from HP Sure Click.

Built-in durability

Rest easy with a PC that undergoes 120,000 hours of HP's Total Test Process and MIL-STD 810 testing. Help extend protection with an optional removable dust filter.

Work hard without sounding like it

Focus on work while enjoying whisper quiet operation. The HP Elite Mini 600 utilizes HP Run Quiet Design that finely tunes the fans to keep systems running quiet and cool.



HP Elite Mini 600 G9 Desktop PC

Technical specifications

Available Operating Systems	Windows 11 Pro ¹ Windows 11 Pro Education ¹ Windows 11 Home – HP recommends Windows 11 Pro for business ¹ Windows 11 Home Single Language – HP recommends Windows 11 Pro for business ¹ Windows 11 Pro (preinstalled with Windows 10 Pro Downgrade) ^{1,2} FreeDOS
Processor family	Intel® Pentium® processor Intel® Celeron® processor 13th Generation Intel® Core™ i7 processor 13th Generation Intel® Core™ i5 processor 13th Generation Intel® Core™ i3 processor 12th Generation Intel® Core™ i7 processor 12th Generation Intel® Core™ i5 processor 12th Generation Intel® Core™ i3 processor
Available Processors ^{3,28}	Intel® Core™ i5-12500T with Intel® UHD Graphics (2.0 GHz P-core base frequency, up to 4.4 GHz P-core Max Turbo frequency, 18 MB L3 cache, 6 P-cores, 12 threads), supports Intel® vPro® Technology Intel® Core™ i5-12400T with Intel® UHD Graphics (1.8 GHz P-core base frequency, up to 4.2 GHz P-core Max Turbo frequency, 18 MB L3 cache, 6 P-cores, 12 threads) Intel® Core™ i3-12300T with Intel® UHD Graphics (2.3 GHz P-core base frequency, up to 4.2 GHz P-core Max Turbo frequency, 12 MB L3 cache, 4 P-cores, 8 threads) Intel® Core™ i3-12100T with Intel® UHD Graphics (2.2 GHz P-core base frequency, up to 4.1 GHz P-core Max Turbo frequency, 12 MB L3 cache, 4 P-cores, 8 threads) Intel® Pentium® Gold G7400 with Intel® UHD Graphics (3.7 GHz P-core base frequency, 6 MB L3 cache, 2 P-cores, 4 threads) Intel® Celeron® G6900 with Intel® UHD Graphics (3.4 GHz P-core base frequency, 4 MB L3 cache, 2 P-cores, 2 threads) Intel® Core™ i5-12600 with Intel® UHD Graphics (3.3 GHz P-core base frequency, up to 4.8 GHz P-core Max Turbo frequency, 18 MB L3 cache, 6 P-cores, 12 threads), supports Intel® vPro® Technology Intel® Core™ i5-12500 with Intel® UHD Graphics (3.0 GHz P-core base frequency, up to 4.6 GHz P-core Max Turbo frequency, 18 MB L3 cache, 6 P-cores, 12 threads), supports Intel® vPro® Technology Intel® Core™ i5-12400 with Intel® UHD Graphics (2.5 GHz P-core base frequency, up to 4.4 GHz P-core Max Turbo frequency, 18 MB L3 cache, 6 P-cores, 12 threads) Intel® Core™ i3-12300 with Intel® UHD Graphics (3.5 GHz P-core base frequency, up to 4.4 GHz P-core Max Turbo frequency, 12 MB L3 cache, 4 P-cores, 8 threads) Intel® Core™ i3-12100 with Intel® UHD Graphics (3.3 GHz P-core base frequency, up to 4.3 GHz P-core Max Turbo frequency, 12 MB L3 cache, 4 P-cores, 8 threads) Intel® Pentium® Gold G7400T with Intel® UHD Graphics (3.1 GHz P-core base frequency, 6 MB L3 cache, 2 P-cores, 4 threads) Intel® Celeron® G6900T with Intel® UHD Graphics (2.8 GHz P-core base frequency, 4 MB L3 cache, 2 P-cores, 2 threads) Intel® Core™ i5-12600T with Intel® UHD Graphics (2.1 GHz P-core base frequency, up to 4.6 GHz P-core Max Turbo frequency, 18 MB L3 cache, 6 P-cores, 12 threads), supports Intel® vPro® Technology Intel® Core™ i7-12700T with Intel® UHD Graphics (1.0 GHz E-core base frequency, 1.4 GHz P-core base frequency, up to 3.4 GHz E-core Max Turbo frequency, up to 4.6 GHz P-core Max Turbo frequency, up to 4.7 GHz with Intel® Turbo Boost Technology, 25 MB L3 cache, 8 P-cores and 4 E-cores, 20 threads), supports Intel® vPro® Technology Intel® Core™ i7-12700 with Intel® UHD Graphics (1.6 GHz E-core base frequency, 2.1 GHz P-core base frequency, up to 3.6 GHz E-core Max Turbo frequency, up to 4.8 GHz P-core Max Turbo frequency, up to 4.9 GHz with Intel® Turbo Boost Technology, 25 MB L3 cache, 8 P-cores and 4 E-cores, 20 threads), supports Intel® vPro® Technology
Chipset ³	Intel® Q670 (vPro®)
Form factor	Mini
Maximum memory	16 GB DDR4-3200 SDRAM; 64 GB DDR5-4800 SDRAM ^{4,5,6} Transfer rates up to 3200 MT/s; Transfer rates up to 4800 MT/s.
Memory slots	2 SODIMM
Internal storage	500 GB up to 2 TB SATA HDD ^{7,32} up to 500 GB SATA SED Opal 2 HDD ^{7,32} 256 GB up to 1 TB PCIe® NVMe™ M.2 SSD ^{7,32} 128 GB up to 2 TB PCIe® NVMe™ TLC M.2 SSD ^{7,32} 256 GB up to 512 GB PCIe® NVMe™ SED Opal 2 TLC M.2 SSD ^{7,32}
Available Graphics	Integrated: Intel® UHD Graphics 730; Intel® UHD Graphics 770; Intel® UHD Graphics 710 (Integrated graphics will depend on processor.)
Audio	Realtek ALC3252 codec, universal audio jack with CTIA and OMTP headset support
Expansion slots	1 M.2 2230; 2 M.2 2280 (1 M.2 slot for WLAN and 2 M.2 2280 slots for storage.)
Ports and connectors	Front: 1 headset connector; 1 SuperSpeed USB Type-A 10Gbps signaling rate; 1 SuperSpeed USB Type-A 10Gbps signaling rate (charging); 1 SuperSpeed USB Type-C® 20Gbps signaling rate; Rear: 1 power connector; 1 RJ-45; 3 SuperSpeed USB Type-A 10Gbps signaling rate; 2 DisplayPort™ 1.4; 1 HDMI 2.1; Optional Ports: Flex IO port 2 – choose one of the following options: 2 USB 2.0 Type-A 480Mbps signaling rate, 1 serial, 1 second external antenna port; Flex IO port 1 – choose one of the following options: 1 VGA, 1 DisplayPort™ 1.4, 1 HDMI 2.1, 1 SuperSpeed USB Type-C® 10Gbps signaling rate (100W Power Intake, Alt Mode DisplayPort™), 2 SuperSpeed USB Type-A 5Gbps signaling rate, HP Fiber NIC Port (1Gbps), Intel® I225-LM 2.5 Gigabit Network Connection LOM, 1 Thunderbolt™ 3 with USB 4.0, 1 serial ³¹
Input devices	HP USB Business Slim SmartCard CCID Keyboard; HP 125 Wired Keyboard; HP 125 Antimicrobial Wired Keyboard; HP 655 Wireless Keyboard and mouse combo; HP USB 320K Keyboard ²⁵ ; HP Wired Desktop 320M mouse; HP 125 Wired Mouse; HP 128 Laser Wired Mouse; HP 125 Antimicrobial Wired Mouse ²⁹
Communications	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card, vPro®; Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card, non-vPro®; Realtek Wi-Fi 6 RTL8852BE 802.11a/b/g/n/ax (2x2) and Bluetooth® 5.3 wireless card ^{26,27}
Drive Bays	One 2.5" ⁸
Environmental	Operating temperature: 10 to 35°C; Operating humidity: 10 to 90% RH
Software	HP Notifications; HP PC Hardware Diagnostics UEFI; HP Support Assistant; HP Connection Optimizer; HP Privacy Settings; HP PC Hardware Diagnostics Windows; HP Desktop Support Utilities; HP Easy Clean; Touchpoint Customizer for Commercial; HP Easy Clean Keyboard Driver; HSA Fusion for Commercial; HSA Telemetry for Commercial; HPX for CMIT ^{12,14}
Available software	HP Smart Support ¹⁵
Security management	Trusted Platform Module TPM 2.0 Embedded Security Chip shipped with Windows 10 (Common Criteria EAL4+ Certified)(FIPS 140-2 Level 2 Certified); HP Secure Erase; HP Sure Click; HP Sure Sense; Absolute Persistence module; HP Sure Admin; HP BIOSphere Gen6; HP Client Security Manager Gen7; HP Tamper Lock; HP Sure Start Gen7; HP Sure Run Gen5; HP Sure Recover Gen5 ^{16,17,18,19,20,21,22,23,24,25}
Security Software Licenses	HP Wolf Pro Security Edition ⁵⁶



HP Elite Mini 600 G9 Desktop PC

Technical specifications

Management features	HP Client Catalog (download); HP Driver Packs (download); HP Image Assistant (download); HP Client Management Script Library (download); HP Connect for Microsoft Endpoint Manager; HP Manageability Integration Kit (download); HP Patch Assistant (download) ^{9,10,11}
Power	90 W external power adapter, up to 89% efficiency; 120 W external power adapter, up to 89% efficiency, active PFC
Dimensions	6.97 x 6.89 x 1.34 in 17.7 x 17.5 x 3.4 cm 19.61 x 9.25 x 5.20 in 49.8 x 23.5 x 13.2 cm (Package)
Weight	3.13 lb 1.42 kg (Exact weight depends on configuration.)
Ecolabels	EPEAT® registered ³⁰
Energy star certified (series fixed)	ENERGY STAR® certified



HP Elite Mini 600 G9 Desktop PC

Footnotes

Key Selling Points Footnotes

- ² Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.
- ³ Four displays sold separately and only supported on with configurable flex port for a fourth display.
- ⁴ Monitor and mounting hardware sold separately or as an optional feature.
- ⁵ HP Wolf Security for Business requires Windows 10 and higher, includes various HP security features and is available on HP Pro, Elite, Workstation, and RPOS products. See product details for included security features and OS requirements.
- ⁶ Recycled plastic content percentage is based on the definition set in the IEEE 16801-2018 standard.
- ⁷ 100% outer box packaging made from sustainably sourced certified and recycled fibers. Fiber cushions made from 100% recycled wood fiber and organic material. Any plastic cushions are made from >90% recycled plastic.
- ⁸ Based on US EPEAT® registration according to IEEE 16801-2018 EPEAT®. EPEAT® status varies by country. Visit www.epeat.net for more information.
- ¹⁰ HP Sure Start Gen7 is available on select HP PCs and requires Windows 10 and higher.
- ¹¹ HP Sure Run Gen5 is available on select HP PCs and requires Windows 10 and higher.
- ¹² HP Sure Click requires Windows 10 and higher. See https://bit.ly/2PrLT6A_SureClick for complete details.

Technical Specifications Footnotes

- ¹ Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.
- ² This system is preinstalled with Windows 10 Pro software and also comes with a license for Windows 11 Pro software and provision for recovery software. You may only use one version of the Windows software at a time. Switching between versions will require you to uninstall one version and install the other version. You must back up all data (files, photos, etc.) before uninstalling and installing operating systems to avoid loss of your data.
- ³ For full Intel® vPro® functionality, Windows 10 Pro 64 bit, vPro supported processor, vPro enabled chipset, vPro enabled wired LAN and/or WLAN card and TPM 2.0 are required. Some functionality requires additional 3rd party software in order to run. See <http://intel.com/vpro>
- ⁴ For systems configured with more than 3 GB of memory and a 32-bit operating system, all memory may not be available due to system resource requirements. Addressing memory above 4 GB requires a 64-bit operating system. Memory modules support data transfer rates up to 3200MT/s for DDR4 and support up to 4800 MT/s for DDR5; actual data rate is determined by the system's configured processor. See processor specifications for supported memory data rate.
- ⁵ All memory slots are customer accessible / upgradeable.
- ⁶ Actual data rate is determined by both the system's configured processor and memory module installed.
- ⁷ For storage drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 30 GB (for Windows) of disk is reserved for system recovery software.
- ⁸ The 2.5" SATA drive bay can be both HDD and SSD.
- ⁹ HP Connect for Microsoft Endpoint Manager is available from the Azure Market Place for HP Pro, Elite, Z and Point-of-Sale PCs managed with Microsoft Endpoint Manager. Subscription to Microsoft Endpoint Manager required and sold separately. Network connection required.
- ¹⁰ HP Patch Assistant available on select HP PCs with the HP Manageability Kit that are managed through Microsoft System Center Configuration Manager. HP Manageability Integration Kit can be downloaded from <http://www8.hp.com/us/en/ads/clientmanagement/overview.html>.
- ¹¹ HP Manageability Integration Kit can be downloaded from <http://www.hp.com/go/clientmanagement>.
- ¹² myHP requires Windows OS.
- ¹⁴ HP Support Assistant. Requires Windows and Internet access.
- ¹⁵ HP Smart Support requires HP TechPulse to be installed. For more information about how to enable or to download HP Smart Support, please visit <http://www.hp.com/smart-support>.
- ¹⁶ HP Sure Click requires Windows 10 Pro or higher or Enterprise. See https://bit.ly/2PrLT6A_SureClick for complete details.
- ¹⁷ HP Sure Sense is available on select HP PCs with Windows 10 Pro, Windows 10 Enterprise, Windows 11 Pro, or Windows 11 Enterprise OS.
- ¹⁸ HP Sure Run Gen5 is available on select HP PCs and requires Windows 10 and higher.
- ¹⁹ HP Sure Recover Gen5 with Embedded Reimaging is an optional feature which requires Windows 10 and higher must be configured at purchase. You must back up important files, data, photos, videos, etc. before use to avoid loss of data. Network based recovery using Wi-Fi is only available on PCs with Intel Wi-Fi Module.
- ²⁰ HP Sure Start Gen7 is available on select HP PCs and requires Windows 10 and higher.
- ²¹ HP Sure Admin requires Windows 10 or higher, HP BIOS, HP Manageability Integration Kit from <http://www.hp.com/go/clientmanagement> and HP Sure Admin Local Access Authenticator smartphone app from the Android or Apple store.
- ²² HP Client Security Manager Gen7 requires Windows and is available on the select HP Elite and Pro PCs.
- ²³ HP BIOSphere Gen6 features may vary depending on the platform and configuration.
- ²⁴ HP Secure Erase for the methods outlined in the National Institute of Standards and Technology Special Publication 800-88 "Clear" sanitation method. HP Secure Erase does not support platforms with Intel® Optane™.
- ²⁵ Absolute firmware module is shipped turned off and can only be activated with the purchase a license subscription and full activation of the software agent. License subscriptions can be purchased for terms ranging multiple years. Service is limited, check with Absolute for availability outside the U.S. Certain conditions apply. For full details visit: <https://www.absolute.com/about/legal/agreements/absolute/>.
- ²⁶ Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 is backwards compatible with prior 802.11 specs.
- ²⁷ Wi-Fi 6E requires a Wi-Fi 6E router, sold separately, to function in the 6GHz band. Availability of public wireless access points limited. Wi-Fi 6E is backwards compatible with prior 802.11 specs. And available in countries where Wi-Fi 6E is supported.
- ²⁸ Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See www.intel.com/technology/turboboost for more information.
- ²⁹ Availability may vary by country (Antimicrobial China only)
- ³⁰ Based on US EPEAT® registration according to IEEE 16801-2018 EPEAT®. Status varies by country. Visit www.epeat.net for more information.
- ³¹ Platform power consumption varies per configuration, for the best user experience, please connect PC power cord while using USB-C® cable via Super Speed USB Type-C® port in the rear side of the platform.
- ³² Starting from November 1st 2023, all shipments will require Windows to be installed on SSD to provide users a better experience. HDD can only be configured as additional data drives and not the boot drive.
- ⁵⁶ HP Wolf Pro Security Edition (including HP Sure Click Pro and HP Sure Sense Pro) is available preloaded on select SKUs and, depending on the HP product purchased, includes a paid 1-year or 3-year license. The HP Wolf Pro Security Edition software is licensed under the license terms of the HP Wolf Security Software - End-User license Agreement (EULA) that can be found at: https://support.hp.com/us-en/document/ish_3875769-3873014-16 as that EULA is modified by the following: "7. Term. Unless otherwise terminated earlier pursuant to the terms contained in this EULA, the license for the HP Wolf Pro Security Edition (HP Sure Sense Pro and HP Sure Click Pro) is effective upon activation and will continue for either a twelve (12) month or thirty-six (36) month license term ("Initial Term"). At the end of the Initial Term you may either (a) purchase a renewal license for the HP Wolf Pro Security Edition from HP.com, HP Sales or an HP Channel Partner, or (b) continue using the standard versions of HP Sure Click and HP Sure Sense at no additional cost with no future software updates or HP Support.

