



Professional machines for advanced users

ThinkStation P3 Series workstations provide affordable power-computing with a choice of processor technologies, expansion bays and support for multiple storage drives.

ThinkStation PX

Powered by up to two 4th Gen Intel Xeon scalable processors, this workstation comes with high processing power helping business professionals to handle most extreme workflows. Combined with up to four NVIDIA RTXTM 6000 Ada Generation GPUs, this workstation runs the most complex computing workloads seamlessly. Moreover, the discrete TPM 2.0 chipset ensures that no unintended users gain access to confidential data and the Kensington security slot protects the device from thefts.



Configured with up to 2TB DDR5 memory, this workstation offers portable power and enables specialists to power through compute-intensive workflows and multi-user collaboration.

To view and compare detailed spreadsheets, the workstation offers easy upgrades to professionals by helping them connect to multiple displays via discrete graphics.

Optional EPEAT Gold and ENERGY STAR 8.0 certification makes it an energy-efficient device.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service



If a problem can't be fixed remotely, we will visit your location
Normally next business day service
Agreed appointment times

Accessories

Lenovo Essential Wired Keyboard & Mouse

USB wired keyboard & mouse combo. Low profile island style keys, LED indicators & adjustable feet
Spill-resistant keyboard with waterproof membrane to protect from accidental spills
Mouse with 1000 DPI optical sensor and scroll wheel for precise control



PN: 4X30179883

Lenovo Essential USB Mouse

Convenient and easy plug-and-play connection to PCs via a USB cable
Ergonomic full-size design provides a comfortable grip for all day comfort
Ambidextrous design, high-resolution 1600 DPI optical sensor experience smooth movement



PN: 4Y50R20863

ThinkStation PX

Performance

Processor

Up to two 4th Gen Intel Xeon Scalable family processors, Silver, Gold, or Platinum.

Operating System

Windows 11 Pro for Workstations
Windows 11 DG Windows 10 Pro 64 for Workstations
Red Hat Enterprise Linux (certified only)

Graphics

Supports up to four NVIDIA RTX 6000 Ada Generation

Chipset

Intel C741 chipset

Memory ¹

Up to 2TB, 16 DDR5 DIMM slots

¹The max memory is based on the test results with current Lenovo memory offerings. The system may support more memory as the technology develops.

Storage ²

Up to 7 drives (4x 3.5" SATA HDD + 3x M.2 SSD) or 9 drives (2x 3.5" SATA HDD + 7x M.2 SSD)
• 3.5" HDD supports hot-swap
• 3.5" HDD up to 12TB each
• M.2 SSD up to 4TB each
• RAID 0/1/10/5 support for 3.5" HDD / M.2 SSD

²The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Design

Dimensions ³

220 x 575 x 440.4mm (8.7 x 22.6 x 17.3 inches, with feet)

³The system dimensions may vary depending on configurations.

Weight ⁴

35.6 kg (78.5 lbs, maximum configuration)

⁴The system weight is approximate and may vary depending on configurations

Connectivity

Ethernet

Two onboard Ethernet, GbE and 10GbE
Additional Ethernet options via PCIe adapter

WLAN + Bluetooth ⁵

Up to Intel Wi-Fi 6E AX210, Bluetooth 5.1, vPro

⁵Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

Security & Privacy

Discrete TPM 2.0

Access Panel Lock Kit with Common Key*

Access Panel Lock Kit with Unique Key*

Chassis intrusion switch

Kensington Security Slot, 3x 7 mm

Manageability

Intel vPro Enterprise with Intel AMT16.0

⁶Intel vPro offers a superset of DASH's defined capabilities.

Certifications

EPEAT Gold Registered*

ENERGY STAR 8.0

RoHS compliant

⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁸EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.