newline

NT+ Series

Superior Image Quality

Seamless Wireless Casting

Access to the Cloud

Non-Touch Display

Impressive Embedded OS

Remote Management

Control by Remote

Compatible with all Devices

STREAMLINE YOUR SUCCESS

The NT+ Series is a non-touch display that brings your lessons to life in vivid Ultra-High Definition (4K) resolution. Focus on just the tools you need to get your students engaged in class without paying more for features you won't use.

Wirelessly cast to the screen from any mobile device, tablet, desktop, or laptop. Whether you use Windows, Mac, or Chrome, the NT+ Series lets you share your screen through a wireless connection or through the multiple I/O ports built into the panel. Access your files on your preferred Cloud storage system right on the display. The built-in file viewer lets you easily navigate through local files, Cloud storage, and files from connected USB thumb drives.

Rediscover the simplicity of real innovation with the new NT+ Series.

Newline NT+ Series includes the following software solutions

CAST   **BROADCAST**   **DISPLAY MANAGEMENT PLUS**

NT+ Series

Model	TT-5523NT-PLUS	TT-6523NT-PLUS	TT-7523NT-PLUS	TT-8623NT-PLUS	TT-9823NT-PLUS
Display					
Screen Size	55"	65"	75"	86"	98"
Landscape/Portrait Mode	Both	Both	Landscape Only	Landscape Only	Landscape Only
Backlight	LED	LED	LED	LED	LED
Display Area (in)	47.6 x 26.8 in	56.3 x 31.7 in	65 x 36.6 in	74.6 x 41.9 in	85 x 47.8 in
Display Ratio	16:9	16:9	16:9	16:9	16:9
Resolution	3840 x 2160 pixels	3840 x 2160 pixels	3840 x 2160 pixels	3840 x 2160 pixels	3840 x 2160 pixels
Display Colors	1.07 billion (8 bit + FRC)	1.07 billion (8 bit + FRC)	1.07 billion (8 bit + FRC)	1.07 billion (8 bit + FRC)	1.07 billion (8 bit + FRC)
Brightness Center Brightness	Without cover glass 400 cd/m²	Without cover glass 400 cd/m²	Without cover glass 400 cd/m²	Without cover glass 400 cd/m²	Without cover glass 400 cd/m²
Contrast	Dynamic 5000:1 Static 1200:1	Dynamic 5000:1 Static 1200:1	Dynamic 5000:1 Static 1200:1	Dynamic 5000:1 Static 1200:1	Dynamic 5000:1 Static 1200:1
Response Time	8 ms	8 ms	8 ms	8 ms	8 ms
Viewing Angle	178°	178°	178°	178°	178°
Lifetime Hours	≥ 50,000 hours	≥ 50,000 hours	≥ 50,000 hours	≥ 50,000 hours	≥ 50,000 hours
Continuous Run Time	24/7	24/7	24/7	24/7	24/7
Power					
Max Power Consumption	≤250W (Standby ≤0.5W)	≤300W (Standby ≤0.5W)	≤300W (Standby ≤0.5W)	≤350W (Standby ≤0.5W)	≤550W (Standby ≤0.5W)
Working Voltage	AC100-240V Max. 2.5A	AC100-240V Max. 3.0A	AC100-240V Max. 3.0A	AC100-240V Max. 3.5A	AC100-240V Max. 5.5A
Speakers					
Position	Downward	Downward	Downward	Downward	Downward
Max Power Output	(2) 15W	(2) 20W	(2) 20W	(2) 20W	(2) 20W
Transportation/Storage					
Outline Dimension	50 x 29 x 3 in	58 x 34 x 4 in	67 x 39 x 4 in	77 x 44 x 4 in	87 x 51 x 4 in
Packing Dimension	55 x 33 x 8 in	63 x 39 x 8 in	72 x 43 x 9 in	82 x 49 x 10 in	93 x 58 x 14 in
Net Weight	40 lbs	53 lbs	73 lbs	93 lbs	161 lbs
Gross Weight	56 lbs	75 lbs	101 lbs	130 lbs	205 lbs
VESA Mount installation position	400 x 400 mm	600 x 400 mm	800 x 400 mm	800 x 400 mm	800 x 600 mm
Installation Method					
Mounting Options	Wall-mounted, Mobile Stand				
Small form factor Computer VESA	No	Yes	Yes	Yes	Yes
Embedded Operating System					
RAM	4GB	4GB	4GB	4GB	4GB
ROM	32GB	32GB	32GB	32GB	32GB
Android Version	11.0	11.0	11.0	11.0	11.0
Speciality					
Wi-Fi Module (Optional)	Pluggable Wi-Fi module, Wi-Fi 6 and BlueTooth 5.2 capable				
Firmware update	USB, OTA				
Back Button	(1) Power Button Rocker switch for power; Up, Down, Left, Right, OK, Return, Menu				
Continuous Use Time	24/7				
Ports					
Front Port	n/a				
Ports	(3) HDMI; (1) HDMI Out; (2) USB A embedded; (1) USB C; (1) Display Port; (1) RS232; (1) SPDIF out; (1) Headphones out; (1) LAN IN; (1) LAN OUT				

newline

950 W Bethany Drive, Suite 330
Allen, TX 75013

Toll-Free: 888-233-0868
Local: 972-468-9728

sales@newline-interactive.com
www.newline-interactive.com