




UX10 FULLY RUGGED TABLET

- 12th Generation Intel® Core™ i5/i7 Processor.
- 10.1" FHD Luminbond® display with Getac sunlight readable technology (1,000 nits) and capacitive touchscreen.
- Enhanced enterprise security with optional Intel® vPro®, Windows Hello face-authentication camera and multifactor authentication options.
- Versatile I/Os connectivity including Thunderbolt™ 4.
- Enhanced Wi-Fi, GPS and LTE performance.



SPECIFICATIONS

Generation

G3

Operating System

Windows 11 Pro

Mobile Computing Platform

Intel® Core™ i5-1235U Processor

Max. 4.4GHz with Intel® Turbo Boost Technology
- 12MB Intel® Smart Cache

Platform options:

Intel® Core™ i5-1245U vPro® Processor

Max. 4.4GHz with Intel® Turbo Boost Technology

- 12MB Intel® Smart Cache

Intel® Core™ i7-1255U Processor

Max. 4.7GHz with Intel® Turbo Boost Technology

- 12MB Intel® Smart Cache

Intel® Core™ i7-1265U vPro® Processor

Max. 4.8GHz with Intel® Turbo Boost Technology

- 12MB Intel® Smart Cache

Intel® Pentium™ 8505 Processor

Max. 4.4GHz with Intel® Turbo Boost Technology

- 8MB Intel® Smart Cache

VGA Controller

Intel® UHD Graphics

Display

10.1" Wide Viewing Angle TFT LCD WUXGA (1920 x 1200)

Protection film

1,000 nits LumiBond® display with Getac sunlight readable

technology

Capacitive multi-touch screen

Storage & Memory

8GB DDR4

Optional: 16GB / 32GB DDR4

256GB PCIe NVMe SSD

Optional: 512GB / 1TB PCIe NVMe SSD

Keyboard

Power button

5 tablet programmable buttons

Pointing Device

Touchscreen

- Capacitive multi-touch screen

- Optional: Dual mode touchscreen (multi-touch and digitizer)

Expansion Slots

Optional (top side): 1D/2D imager barcode reader, or Serial port, or USB 3.2 Gen 1 Type-A port, or LAN port (RJ45) , or micro-SD or HF RFID reader¹, or HDMI 2.0.ⁱⁱ

Optional (right side): LAN port (RJ45) or Fingerprint readerⁱⁱⁱ

Optional (back side): Smart card reader, or Bridge battery, or Bridge battery + Smart card reader^{iv}

I/O Interface

FHD webcam x 1^v

8M pixels auto focus rear camera x 1

Audio in/out combo x 1

DC in Jack x 1

USB 3.2 Gen 2 Type-A x 1

Docking connector x 1

Thunderbolt™ 4 Type-C x 1

Optional: Windows Hello face-authentication camera (front-facing) x 1^v

Optional: RF antenna pass-through for GPS, WWAN and WLAN

Optional: HDMI 2.0 x 1ⁱⁱ

Communication Interface

Intel® Wi-Fi 6E AX211, 802.11ax

Bluetooth (v5.3)^{vi}

Dual SIM (Micro-SIM 3FF and e-SIM)^{vii,viii}

Optional: Dedicated GPS^x

Optional: 4G LTE mobile broadband with integrated GPS^{ix,x}

Optional: 10/100/1000 base-T Ethernet

Security Features

TPM 2.0

Kensington lock

Optional: Intel® vPro® Technology

Optional: HF RFID readerⁱⁱ

Optional: Fingerprint reader^{iv}

Optional: Smart card reader^{iv}

Optional: Windows Hello face-authentication camera (front-facing)^v

Power

AC adapter (65W, 100-240VAC, 50/60 Hz)

Li-ion battery (11.1V, typical 4200mAh; min. 4080mAh) x 1

Optional: High capacity Li-ion battery (10.8V, 9240mAh) x 1

Optional: Bridge battery^{iv}

Dimension (W x D x H) & Weight

279 x 194.5 x 23.5mm (10.98" x 7.65" x 0.92")^{xi}

1.22kg (2.68lbs)^{xi}

Rugged Feature

MIL-STD-810H certified

IP66 certified

MIL-STD-461G certified^{xii}

Vibration & 6ft (1.8m) drop resistant^{xiii}

Optional: ANSI/UL 12101, CSA C22.2 NO. 213 (Class I, Division 2, Groups A, B, C, D)^{xiv}

Environmental Specification

Temperature^{xv}

- Operating: -29°C to 63°C / -20°F to 145°F

- Storage: -51°C to 71°C / -60°F to 160°F

Humidity:

- 95% RH, non-condensing

Pre-installed Software

Getac Utility

Getac Camera

Getac Geolocation

Getac Barcode Manager^{xvi}

Getac Driving Safety Utility (trial version)

Getac KeyWedge Barcode Reader Utility (trial version)

Optional: Absolute Persistence^g

Optional Software

Getac Driving Safety Utility

Getac KeyWedge Barcode Reader Utility

Getac Device Monitoring System (GDMS)

Getac VGPS Utility^{xvii}

Accessories

Battery (11.1V, typical 4200mAh; min. 4080mAh)

AC adapter (65W, 100-240VAC)

Capacitive stylus with tether

Optional:

Carry bag

Folio case

Battery (11.1V, typical 4200mAh; min. 4080mAh)

High capacity Li-ion battery (10.8V, 9240 mAh)

Multi-Bay charger (Dual-Bay)

Multi-Bay charger (Eight-Bay)

AC adapter (65W, 100-240VAC)

Office dock AC adapter (90W, 100-240VAC)

MIL-STD-461 AC adapter (90W, 100-240VAC)

DC-DC vehicle adapter (120W, 11-32VDC)

Digitizer pen

Capacitive stylus with tether

Protection film

Hand strap

Shoulder strap (2-point)

Shoulder harness (4-point; handsfree)

Detachable keyboard

Vehicle cradle^{xviii}

Keyboard dock

Vehicle dock^{xix}

Office dock

100W Type-C adapter

Getac rugged keyboard

UX10 FULLY RUGGED TABLET

Bumper-to-Bumper warranty

Accidents can take your equipment out of service when you least expect it, especially in a rugged environment, which can cause costly equipment downtime. That is why Getac has introduced accidental damage as standard under our Bumper-to-Bumper warranty, to help minimize your enterprise IT costs. Bumper-to-Bumper is your hassle-free guarantee. That means you can depend on us to have your unit back in service within days.

Standard

3 years Bumper-to-Bumper

- I. 13.56MHz contactless HF RFID reader (ISO 15693, 14443 A/B, Mifare and Felica™ compliant).
- II. 1D/2D imager barcode reader, Serial port, USB 3.2 Gen 1 Type-A port, LAN port (RJ45), HF RFID reader, MicroSD and HDMI 2.0 are mutually exclusive options.
- III. Fingerprint reader and LAN Port are mutually exclusive options.
- IV. Smart card reader, Bridge battery and Bridge battery + Smart card reader are mutually exclusive options.
- V. FHD webcam and optional Windows Hello face-authentication camera (front-facing) are mutually exclusive options.
- VI. Bluetooth performance and connectable distance may be subject to interference with the environments and performance on client devices, users may be able to reduce effects of interference by minimizing the number of active Bluetooth wireless devices that is operating in the area.
- VII. One physical SIM card slot and one eSIM.
- VIII. Network service may vary depending on local telecommunication providers.
- IX. Supports GPS and Glonass.
- X. Units with 4G LTE option come with an embedded SIM card slot.
- XI. Weight and dimensions vary from configurations and optional accessories.
- XII. MIL-STD-461 90W AC adapter sold separately.
- XIII. Drop test results vary from configurations and optional accessories.
- XIV. Available with limited configurations and environment conditions.
- XV. Tested by an independent third-party test lab following MIL-STD-810H.
- XVI. Available when barcode reader option is selected.
- XVII. Models require either embedded or standalone GPS module.
- XVIII. Gamber Johnson and Havis vehicle docks are e-mark certified.

Information provided herewith is for reference only, available specification shall be subjected to quotation by request.

Getac

GETAC TECHNOLOGY CORPORATION

5F, Building A, No. 209, Section 1,
Nangang Rd., Nangang Dist., Taipei City,
115018, Taiwan, R.O.C. Tel : +886 2 2785
7888 globalmarketing@getac.com |
www.getac.com Copyright © 2023 Getac
Technology Corporation and/or any of its affiliates.
All Rights Reserved. Information provided herewith
is for reference only, available specification shall be
subjected to quotation by request.

	Vehicle Dock	Office Dock
Serial Port	1	1
External VGA	-	1
Microphone	-	1
Audio Output	-	1
DC in Jack	1	1
USB	USB 2.0 x 2 USB 3.2 Gen 1 x 2	USB 2.0 x 2 USB 3.2 Gen 1 x 2
LAN	1	1
HDMI 1.4	-	1
RF Antenna Connector	3 (WWAN, WLAN, GPS)	-
Kensington Lock	1	1