

PERFORMANCE

Processor

Intel® Core™ i7-8665UE (4C / 8T, 1.7 / 4.4GHz, 8MB)

Graphics

Integrated Intel UHD Graphics 620

Chipset

Intel SoC Platform

Memory

2x 16GB SO-DIMM DDR4-2400

Max Memory

Up to 64GB DDR4-2400

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Storage

512GB SSD M.2 2280 PCIe® 3.0x4 NVMe® Opal

Storage Support

Up to two drives, 1x 2.5" HDD/SSD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- 2.5" SSD up to 256GB
- M.2 SSD up to 1TB

Power Supply

65W 89% Adapter

DESIGN

Keyboard

None

Mouse

None

Case Color

Black

Dust Filter

None

Mounting

None

Dimensions (WxDxH)^[1]

179 x 182.9 x 72 mm (7.05 x 7.20 x 2.83 inches)

Weight^[2]

Around 2.985 kg (6.58 lbs)

CONNECTIVITY

Ethernet

Integrated 100/1000M, 2x RJ45

WLAN + Bluetooth®

None

Front Ports

- 1x USB 3.2 Gen 1
- 1x headphone (3.5mm)
- 1x headphone / microphone combo jack (3.5mm)
- 1x power connector

Optional Front Ports (configured)

None

Rear Ports

- 1x HDMI®
- 1x DisplayPort™
- 2x USB 2.0
- 1x USB 3.2 Gen 1
- 2x serial (RS232)
- 2x Ethernet (RJ-45)

Optional Rear Ports (configured)

None

Monitor Cable

None

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified

MANAGEABILITY

SERVICE

Base Warranty

3-year, Onsite

Included Upgrade

None

ENVIRONMENTAL

Operating Temperature

Standard Temperature 0° to 35° (32° to 95°)

CERTIFICATIONS

Green Certifications

- Low Halogen
- RoHS compliant
- REACH
- TED (ECO-declaration)
- WEEE

SOFTWARE

Operating System

Windows® 10 IoT Enterprise 64, English

ACCESSORIES

MODEL

TopSeller : Yes

Announce Date : 2022-08-25

EAN / UPC / JAN : 196802904834

End of Support : N/A



To see more note information, please link to https://psref.lenovo.com/Detail/ThinkEdge_SE50?M=11RJ006FUS.

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Professional Wireless Combo Keyboard & Mouse (US English)

4X30H56796

This sleek and stylish full-size keyboard and mouse combo offers exceptional quality in a modern wireless solution. The slim 3-zone keyboard with number pad has responsive quiet keys and a premium typing experience. O...

Recommended Services

GOOD

3Y Premier Support Upgrade from 3Y Onsite (5WS0U26647)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference