




B360 PRO FULLY RUGGED NOTEBOOK

- MIL-STD 810H, 6ft operating drop rating, IP66 certified and optional salt fog resistant
- 10th Generation Intel® Core™ Processor
- 13.3" FHD LumiBond® display with Getac sunlight readable technology (1,400 nits) and capacitive touchscreen
- Optional NVIDIA® GeForce® GTX1050 4GB discrete graphic controller
- Enhanced enterprise security with optional dual user replaceable storage, Windows Hello face-authentication camera, integrated 1D/2D imager barcode reader and multi-factor authentication options
- LifeSupport™ battery swappable technology



B360 PRO FULLY RUGGED NOTEBOOK

SPECIFICATIONS

Generation	G1
Operating System	Windows 10 Pro Windows 11 Pro
Mobile Computing Platform	Intel® Core™ i5-10210U Processor 1.6GHz Max. 4.2GHz with Intel® Turbo Boost Technology - 6MB Intel® Smart Cache Platform options: Intel® Core™ i5-10310U vPro™ Processor 1.7GHz Max. 4.4GHz with Intel® Turbo Boost Technology - 6MB Intel® Smart Cache Intel® Core™ i7-10510U Processor 1.8GHz Max. 4.9GHz with Intel® Turbo Boost Technology - 8MB Intel® Smart Cache Intel® Core™ i7-10610U vPro™ Processor 1.8GHz Max. 4.9GHz with Intel® Turbo Boost Technology - 8MB Intel® Smart Cache Intel® Core™ i7-10710U Processor 1.1GHz Max. 4.7GHz with Intel® Turbo Boost Technology 12MB Intel® Smart Cache
VGA Controller	Intel® UHD Graphics Optional: NVIDIA® GeForce® GTX1050 4GB discrete graphics controller ^{i,viii}
Display	13.3" IPS TFT LCD FHD (1920 x 1080) Protection film 1,400 nits LumiBond® display with Getac sunlight readable technology
Storage & Memory	8GB DDR4 Optional: 16GB / 32GB / 64GB DDR4 256GB PCIe NVMe SSD Optional: 512GB / 1TB PCIe NVMe SSD Optional 2 nd Storage ⁱⁱ : 256GB / 512GB / 1TB SATA SSD
Keyboard	LED backlit membrane keyboard Optional: LED backlit rubber keyboard

B360 PRO FULLY RUGGED NOTEBOOK

Pointing Device	Touchscreen - Capacitive multi-touch screen Touchpad - Touchpad with two buttons
Expansion Slots	Smart card reader x 1 Optional: Discrete graphics controller, or PCMCIA Type II, or ExpressCard/54 ⁱ Optional: 1D/2D imager barcode reader
Multimedia Bay	Optional: DVD super multi drive / Blu-Ray super multi drive ⁱⁱⁱ
I/O Interface	FHD webcam x 1 Audio in/out combo x 1 DC in Jack x 1 PowerShare USB 2.0 x 1 USB 3.2 Gen 2 Type-A x 2 LAN (RJ45) x 1 HDMI 1.4 x 1 Docking connector x 1 Optional: SIM card slot x 1 (Mini-SIM, 2FF) Optional: Windows Hello face-authentication camera (front-facing) x 1 Optional: RF antenna pass-through for GPS, WWAN and WLAN Configurable I/O options ^{iv} : 1. Serial port (9-pin; D-sub) x 1 + External VGA (15-pin; D-sub) x 1 2. Serial port (9-pin; D-sub) x 1 + USB 3.2 Gen 2 Type-C x 1 3. Serial port (9-pin; D-sub) x 1 + Display port x 1 4. Serial port (9-pin; D-sub) x 2 + External VGA (15-pin; D-sub) x 1 5. Serial port (9-pin; D-sub) x 2 + USB 3.2 Gen 2 Type-C x 1 6. Serial port (9-pin; D-sub) x 2 + Display port x 1 7. Serial port (9-pin; D-sub) x 1 + External VGA (15-pin; D-sub) x 1 + 2nd LAN (RJ45) x 1 8. Serial port (9-pin; D-sub) x 1 + Display Port x 1 + 2nd LAN (RJ45) x 1 9. Serial port (9-pin; D-sub) x 2 + External VGA (15-pin; D-sub) x 1 + 2nd LAN (RJ45) x 1 10. Serial port (9-pin; D-sub) x 2 + Display Port x 1 + 2nd LAN (RJ45) x 1
Communication Interface	10 / 100 / 1000 base-T Ethernet Intel® Wi-Fi 6 AX200, 802.11ax Bluetooth (v5.2) ^v Optional dedicated GPS ^{vi} Optional: 4G LTE mobile broadband with integrated GPS ^{vi,vii}

B360 PRO FULLY RUGGED NOTEBOOK

Security Features

TPM 2.0
Kensington lock
Optional: Fingerprint reader ^{xv}
Optional: HF RFID reader ^{viii, xv}
Smart card reader

Power

AC adapter (90W, 100-240VAC, 50/60Hz)
AC adapter (120W, 100-240VAC, 50/60Hz) ^{ix}
High capacity Li-ion battery (10.8V, typical 6900mAh; min. 6600mAh) x 2
LifeSupport™ battery swappable technology

Dimension (W x D x H) & Weigh

342 x 281 x 53.5mm (13.46" x 11.06" x 2.11")
3.08Kg (6.79lbs) ^x

Rugged Feature

MIL-STD-810H certified
IP66 certified
MIL-STD-461G certified ^{xi}
Vibration & 6ft (1.8m) drop resistant
Optional: ANSI/UL 121201, CSA C22.2 NO. 213 (Class I, Division 2, Groups A, B, C, D) ^{xvii}
Optional: Salt fog certified

Environmental Specification

Temperature ^{xii} :
- Operating: -29°C to 63°C / -20°F to 145°F
- Storage: -51°C to 71°C / -60°F to 160°F
Humidity:
- 95% RH, non-condensing

Pre-installed software

Getac Utility
Getac Geolocation
Getac Barcode Manager ^{xiii}
Optional: Absolute Persistence®

Optional software

Getac Driving Safety Utility
Getac KeyWedge Barcode Reader Utility
Getac Device Monitoring System (GDMS)
Getac VGPS Utility ^{xvi}

B360 PRO FULLY RUGGED NOTEBOOK

Accessories

High capacity Li-ion battery (10.8V, typical 6900mAh; min. 6600mAh)
AC adapter (90W, 100-240VAC)
Capacitive stylus with tether

Optional:

Backpack
High Capacity Li-ion Battery (10.8V, typical 6900mAh; min. 6600mAh)
Multi-Bay charger (Dual-Bay)
Multi-Bay charger (Eight-Bay)
AC adapter (90W, 100-240VAC)
AC adapter^{ix} (120W, 100-240VAC)
MIL-STD-461 AC adapter (90W, 100-240VAC)
DC-DC vehicle adapter (120W, 11-32VDC)
Capacitive stylus with tether
Protection film
Vehicle cradle
Vehicle dock
Office dock
Spare SSD kit
100W Type-C adapter^{xiv}

Bumper-to-Bumper warranty

Accidents can take your equipment out of service when you least expect it, especially in a rugged environment, which can cause costly equipment downtime.

That is why Getac has introduced accidental damage as standard under our Bumper-to-Bumper warranty, to help minimize your enterprise IT costs.

Bumper-to-Bumper is your hassle-free guarantee. That means you can depend on us to have your unit back in service within days.

Standard

3 years Bumper-to-Bumper

- I. Discrete graphics card, PCMCIA slot, and Expresscard slot are mutually exclusive.
- II. Second storage is optional and will be fitted with a removable cover when not chosen at point of purchase.
- III. DVD super multi drive and Blu-Ray super multi drive are mutually exclusive.
- IV. External VGA, USB 3.2 Gen 2 Type-C port and Display port are mutually exclusive.
- V. Bluetooth performance and connectable distance may be subject to interference with the environments and performance on client devices, users may be able to reduce effects of interference by minimizing the number of active Bluetooth wireless devices that is operating in the area.
- VI. Dedicated GPS is mutually exclusive with 4G LTE mobile broadband.
- VII. Units with 4G LTE option comes with an embedded SIM card slot.
- VIII. HF(13.56MHz) combo HF RFID/NFC reader (iClass, HID Prox , ISO 15693, 14443 A/B, Mifare, and FeliCa™ compliant).
- IX. 120W AC adapter is used for office dock and for device configured with discrete graphics card.
 - X. Weight and dimensions vary from configurations and optional accessories.
 - XI. MIL-STD-461 90W AC adapter sold separately.
 - XII. Tested by an independent third-party test lab following MIL-STD-810H.
 - XIII. Available when barcode reader option is selected.
 - XIV. Do not support the configurations with discrete graphics card.
 - XV. Fingerprint reader and HF RFID reader are mutually exclusive.
 - XVI. Models require either embedded or standalone GPS module.
 - XVII. Available with limited configurations and environment conditions.

Information provided herewith is for reference only, available specification shall be subjected to quotation by request.

B360 PRO FULLY RUGGED NOTEBOOK

	Vehicle Dock	Office Dock
Serial Port	2	2
External VGA	1	1
Microphone	1	1
Audio Output	1	1
DC in Jack	1	1
USB	6	5
LAN	2	2
HDMI 1.3	1	1
RF Antenna Connector	3 (GPS, WWAN, WLAN)	-

Getac (UK) Ltd.

Getac House, Stafford Park 12,
Telford, Shropshire TF3 3BJ, United Kingdom
Tel : +44 (0) 1952 207 222

Sales-Getac-UK@getac.com | www.getac.com/en/

Copyright © 2022 Getac Technology Corporation and/or any of its affiliates. All Rights Reserved.

Information provided herewith is for reference only,
available specification shall be subjected to quotation by request.