

**PERFORMANCE****Processor**

Intel® Core™ i7-1360P, 12C (4P + 8E) / 16T, P-core 2.2 / 5.0GHz, E-core 1.6 / 3.7GHz, 18MB

**Graphics**

NVIDIA® RTX A500 4GB GDDR6

**Chipset**

Intel SoC Platform

**Memory**

32GB Soldered LPDDR5x-7500 Non-ECC

**Memory Slots**

Models with LPDDR5x memory: memory soldered to systemboard, no slots, dual-channel

**Max Memory**

Models with 32GB LPDDR5x: 32GB soldered memory, not upgradable

**Storage**

1TB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

**Storage Support<sup>[7]</sup>**

One drive, up to 2TB M.2 2280 SSD

**Storage Slot**

One M.2 2280 PCIe 4.0 x4 slot

**Card Reader**

No card reader

**Audio Chip**

High Definition (HD) Audio, Realtek® ALC3287 codec

**Speakers**

Stereo speakers, 2W x2, Dolby® Audio™

**Camera**

5.0MP + IR Discrete with Privacy Shutter and Human Presence Detection

**Microphone**

2x, Array

**Battery**

Integrated 86Wh

**Power Adapter**

135W USB-C® Slim (3-pin)

**DESIGN****Display<sup>[8][9]</sup>**

16" WUXGA (1920x1200) IPS 300nits Anti-glare, 45% NTSC, Touch

**Touchscreen**

On-cell, 10-point Multi-touch

**Keyboard**

Backlit, French

**Case Color**

Villi Black

**Case Material**

PC + 20% CF + 50% GF (Top), PPS (Bottom)

**Dimensions (WxDxH)<sup>[10]</sup>**

361.9 x 255.5 x 21.1 mm (14.25 x 10.06 x 0.83 inches)

**Weight<sup>[11]</sup>**

Starting at 1.70 kg (3.77 lbs)

**SOFTWARE****Operating System**

Windows® 11 Pro, French

**CONNECTIVITY****Ethernet**

100/1000M (RJ-45)

**WLAN + Bluetooth®<sup>[12]</sup>**

Intel Wi-Fi® 6E AX211, 11ax 2x2 + BT5.1

**WWAN**

WWAN Upgradable to 4G

**Standard Ports**

- 2x USB 3.2 Gen 1 (one Always On)
- 2x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 2.0)
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Security keyhole

**Optional Ports (configured)**

1x Nano-SIM Card Slot

**Docking**

Various docking solutions supported via Thunderbolt or USB-C.

For more compatible docking solutions, please visit [Docking for ThinkPad® P16s Gen 2 \(Intel\)](#)**SECURITY & PRIVACY****Security Chip**

Discrete TPM 2.0 Enabled

**Fingerprint Reader**

Touch Style, Match-on-Chip, Integrated in Power Button

**Physical Locks**

Kensington® Nano Security Slot™, 2.5 x 6 mm

**Other Security**

- Ultrasonic Human Presence Detection for IR camera
- Ultrasonic Human Presence Detection for IR camera
- Camera privacy shutter
- Bottom cover tamper detection
- IR camera for Windows® Hello

**MANAGEABILITY****System Management**

Non-vPro®

**SERVICE****Base Warranty**

3-year, Courier or Carry-in

**Included Upgrade**

3Y Sealed Battery Add On, 3Y Premier Support Upgrade from 3Y Courier/CCI

**CERTIFICATIONS****Green Certifications<sup>[13][14]</sup>**

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- TCO Certified 9.0
- RoHS compliant

**Mil-Spec Test**

MIL-STD-810H military test passed

**ISV Certifications**Please visit [ISV certifications for Lenovo® Workstations](#)**MODEL**

TopSeller : Yes

EAN / UPC / JAN : 197528672519

Announce Date : 2023-06-13

End of Support : 2029-11-25



To see more note information, please link to

[https://psref.lenovo.com/Detail/ThinkPad\\_P16s\\_Gen\\_2\\_Intel?M=21HK003MCA](https://psref.lenovo.com/Detail/ThinkPad_P16s_Gen_2_Intel?M=21HK003MCA)

· Lenovo reserves the right to change specifications or other product information without notice.

· Product image on this page is a sample, it may not match the real color of this model

· Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad USB-C Dock Gen 2

40AS0090US

- Lenovo understands that modern business depends on a wide variety of PC's and even brands to meet their business needs. To make this easier Lenovo USB-C dock is compatible with Lenovo notebooks as well as note...

## Recommended Services

BEST	5Y Lenovo Protect (Premier Support + ADP + KYD + International Service Entitlement) For Embedded MTM (5PS1K54547)
BETTER	4Y Lenovo Support (Premier Support + KYD + International Service Entitlement) For Embedded MTM (5PS1K54545)
GOOD	3Y Lenovo Protect (ADP + KYD + International Service Entitlement) For Embedded MTM (5PS1K54544)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference