

**PERFORMANCE****Processor**

MediaTek Helio G80 (8C, 2x A75 @2.0GHz + 6x A55 @1.8GHz)

**Graphics**

Integrated ARM Mali-G52 MC2 GPU

**Chipset**

MediaTek SoC Platform

**Memory**

4GB Soldered LPDDR4x

**Storage**

64GB eMMC 5.1

**Card Reader**

microSD Card Slot

**Storage Support**

- 64GB eMMC 5.1 on systemboard
- microSD card, supports FAT32 up to 128GB, exFAT up to 2TB

**Speakers**

Dual speaker optimized with Dolby® Atmos®

**Microphone**

Mono

**Camera**

Front 2.0MP / Rear 8.0MP

**VoiceCall**

No

**Sensors**

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Coulomb counter
- Hall sensor

**Vibration Motor**

Eccentric Rotating Mass (ERM)

**Battery**

Integrated 5100mAh (Typ.)

**Power Adapter**

5V / 2A

**DESIGN****Display<sup>[1]</sup>**

9" HD (1340x800) IPS 400nits Anti-fingerprint, Touch

**Touchscreen**

In-cell, 10-point Multi-touch

**Case Material**

Metal (Back Cover)

**Keyboard**

None

**Pen**

No Support

**Dimensions (WxDxH)<sup>[2]</sup>**

215.43 x 136.76 x 7.99 mm (8.48 x 5.38 x 0.31 inches)

**Weight<sup>[3]</sup>**

Around 344 g (0.76 lbs)

**Case Color**

Arctic Grey

**SOFTWARE****Operating System<sup>[4]</sup>**

Android™ 12 or Later

**CONNECTIVITY****WLAN + Bluetooth®**

11ac 1x1 + BT5.1

**WWAN**

None

**Location Services**

GPS + GLONASS + Galileo

**Standard Ports**

- 1x USB-C® 2.0 (support data transfer, charging, USB-C® digital headset)
- 1x 3.5mm headphone jack
- 1x Card slot

**SERVICE****Base Warranty<sup>[5]</sup>**

1-year, Customer Replaceable Unit (CRU) with 1-year Battery

**ACCESSORIES****Bundled Accessories<sup>[6]</sup>**

None

**CERTIFICATIONS****Green Certifications**

- ENERGY STAR® 8.0 (only available for TB310FU)
- ErP Lot 3
- RoHS compliant

**Other Certifications**

TÜV Rheinland® Low Blue Light (Software Solution)

**MODEL**

Product : TB310FU

TopSeller : No

Announce Date : 2022-12-06

EAN / UPC / JAN : 196802847674



Product image is a sample, it may not match the real color of this model

**Note:**

<sup>[1]</sup> IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

<sup>[2]</sup> The system dimensions may vary depending on configurations.

<sup>[3]</sup> The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

<sup>[4]</sup> The operating system at launch is Android 12. Expect one OS upgrade and 3 years security patches in the field. For the latest software upgrade information, please visit <https://support.lenovo.com/solutions/ht501098>.

<sup>[5]</sup> For warranty upgrade service, please go to <https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access <https://bcsupport.lenovo.com/warranty>.

<sup>[6]</sup> For more compatible accessories, please check the file "Lenovo Android Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>.

Lenovo reserves the right to change specifications without notice.  
California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to <https://psref.lenovo.com/Detail/2127?M=ZAC30053US>

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

## Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

## Base Warranty - Included with the system you purchase with default 1-year coverage window.

## Lenovo Warranty Extensions & Upgrades (up to 3 years duration)

**- Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.**

- Pick up & return courier / Depot support
- Replaceable unit service\*

\*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo Folio Case for Tab M9

ZG38C04869

This folio case is designed to protect your tablet with modern material finish and brimless style. The folio case comes with the stand mode, allowing you to watch rich videos in convenient and comfortable positions. A...



### Lenovo Folio Case for Tab M9

ZG38C04874

This folio case is designed to protect your tablet with modern material finish and brimless style. The folio case comes with the stand mode, allowing you to watch rich videos in convenient and comfortable positions. A...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference