

**PERFORMANCE****Processor**

MediaTek Helio G99 (8C, 2x A76 @2.2GHz + 6x A55 @2.0GHz)

**Graphics**

Integrated ARM Mali-G57 MC2 GPU

**Chipset**

MediaTek SoC Platform

**Memory**

4GB Soldered LPDDR4x

**Storage**

128GB UFS 2.2 (uMCP)

**Card Reader**

microSD Card Slot

**Storage Support**

- 128GB uMCP (UFS-Based MCP, UFS 2.2)
- microSD card, supports up to 1TB (exFAT)

**Speakers**

4 speakers, 1W x4, optimized with Dolby® Atmos®

**Microphone**

2x, Array

**Camera**

Front 8.0MP / Rear 13.0MP

**VoiceCall**

No

**Sensors**

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Coulomb counter
- Gyroscope sensor
- Hall sensor
- Proximity (P) sensor

**Vibration Motor**

Eccentric Rotating Mass (ERM)

**Battery**

Integrated 7500mAh (Min.) / 7700mAh (Typ.)

**Power Adapter**

10V / 2A

**DESIGN****Display**<sup>[1][2]</sup>

11.5" 2K (2000x1200) IPS 400nits Anti-fingerprint, 97.5% DCI-P3, 120Hz, Corning® Gorilla® Glass 3, Touch

**Touchscreen**

10-point Multi-touch

**Case Material**

Metal + Plastic

**Keyboard**

None

**Pen**<sup>[3]</sup>

Pen Upgradable (Purchase Separately)

**Dust and Water Resistant**

IP52

**Dimensions (WxDxH)**<sup>[4]</sup>

269.1 x 169.4 x 7.4 mm without camera deco (10.59 x 6.67 x 0.29 inches)

**Weight**<sup>[5]</sup>

Around 520 g (1.15 lbs)

**Case Color**

Storm Grey

**SOFTWARE****Operating System**<sup>[6]</sup>

Android™ 12L or Later

**CONNECTIVITY****WLAN + Bluetooth**<sup>[7]</sup>

Wi-Fi® 6E, 11ax 1x1 + BT5.2

**WWAN**

None

**Location Services**

No location service

**Standard Ports**<sup>[8]</sup>

- 1x USB-C® 2.0 (support data transfer and charging)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Card slot
- 1x Pogo pin connector (4-point)

**Docking**

Smart Charging Station 2 Support (Purchase Separately)

**SERVICE****Base Warranty**<sup>[9]</sup>

1-year, Mail-in with 1-year Battery

**ACCESSORIES****Bundled Accessories**<sup>[10]</sup>

None

**CERTIFICATIONS****Green Certifications**

- ENERGY STAR® 8.0 (only available for TB350FU)
- ErP Lot 3
- RoHS compliant

**Other Certifications**

TÜV Rheinland® Full Care Display Certification

**MODEL**

Product : TB350FU

TopSeller : No

Announce Date : 2022-08-02

EAN / UPC / JAN : 196801871274



Product image is a sample, it may not match the real color of this model

**Note:**

<sup>[1]</sup> IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

<sup>[2]</sup> The screen supports a maximum refresh rate of 120Hz. The value varies according to applications and scenarios.

<sup>[3]</sup> For details upon pen compatibility, please check the file "Lenovo Android Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>.

<sup>[4]</sup> The system dimensions may vary depending on configurations.

<sup>[5]</sup> The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

<sup>[6]</sup> The operating system at launch is Android 12L. Two major OS upgrades (up to Android 14) will be made following launch during the product's lifecycle and it will receive three years of security upgrades. For the latest software upgrade information, please visit <https://support.lenovo.com/solutions/h501098>.

<sup>[7]</sup> Wi-Fi 6E full features might be limited by country-level restrictions. 6GHz Wi-Fi 6E operation is dependent on the support of routers/APs/Gateways that support Wi-Fi 6E, and the regional regulatory certifications & spectrum allocation.

<sup>[8]</sup> 4-point pogo pin connector is used to connect

Lenovo reserves the right to change specifications without notice. California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to <https://psref.lenovo.com/Detail/2067?M=ZABF006OUS>

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

## Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

## Base Warranty - Included with the system you purchase with default 1-year coverage window.

## Lenovo Warranty Extensions & Upgrades (up to 3 years duration)


**- Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.**

- Pick up & return courier / Depot support
- Replaceable unit service\*

\*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo Precision Pen 2 (2023)

ZG38C04470

With 4,096 levels of pressure and tilt detection, the Lenovo Precision affords users the highest level of precision and control as they sketch or just take notes.



### Lenovo Folio Case for Tab P11 (2nd Gen)

ZG38C04535

Offering all-around protection in a comfy and resilient microfiber polyurethane finish, the Folio Case builds in a convertible stand for both landscape and portrait viewing. Featuring fully and easy access to all your...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference