

PERFORMANCE

Processor

Intel® Atom x6425RE (4C / 4T, 1.9GHz, 1.5MB)

Graphics

Integrated Intel UHD Graphics

Chipset

Intel SoC Platform

Memory

1x 8GB SO-DIMM DDR4-3200

Max Memory

Up to 32GB DDR4-3200

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Storage

256GB SSD M.2 2230 PCIe® 3.0x4 NVMe®

Storage Support

SE10-I:

Up to two drives, 64GB eMMC 5.1 on systemboard + 1x M.2 SSD

- M.2 SSD up to 1TB
- 64GB eMMC 5.1, for SE10-I (-20-60°C) only

Power Supply

9-36V WDC

DESIGN

Keyboard

None

Mouse

None

Case Color

Black (SE10-I)

Mounting

1x DIN Rail Mount

Dimensions (WxDxH)^[1]

179 x 135 x 60 mm (7.04 x 5.31 x 1.45 inches)

Weight^[2]

2.6 kg (5.73 lb)

CONNECTIVITY

Ethernet

2x 2.5 Gigabit Ethernet (2x RJ-45)

WLAN + Bluetooth^[3]

Intel AX210, 11ax 2x2 + BT5.1

WWAN^[4]

None

Left Ports^[5]

- 1x Nano SIM slot
- 1x SD card slot

Front Ports

- 2x USB 3.2 Gen 2
- 1x line-out (3.5mm)
- 1x microphone (3.5mm)
- 3x LED (LED1: storage / LED2: Wireless / LED3: User defined or WWAN)
- 2x Serial (RS232 / RS422 / RS485, BIOS selectable)

Optional Front Ports (configured)^[6]

None

Rear Ports

- 1x HDMI® 1.4b
- 1x DisplayPort™ 1.4
- 2x USB 2.0
- 2x 2.5GbE Ethernet (RJ-45)
- 1x Slim Tip power connector (SE10 only)
- 1x DC-in 3pin Phoenix connector for 9-36V WDC (SE10-I only)
- 1x 2pin remote power switch (SE10-I only)

Optional Rear Ports (configured)

2x RP-SMA Female, Wi-Fi® antenna

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified

Other Security

- NITS SP800-147B compliant
- ThinkShield

MANAGEABILITY

System Management

XClarity In-Band manageability

SERVICE

Base Warranty

3-year, Onsite

Included Upgrade

None

ENVIRONMENTAL

Operating Temperature

Wide Temperature -20℥ to 60℥ (-4℥ to 140℥)

CERTIFICATIONS

Green Certifications

- ErP Lot 6
- Low Halogen
- RoHS compliant
- REACH
- TED (ECO-declaration)
- WEEE

Other Certifications

- Microsoft® Azure IoT Edge Certified
- AWS IoT Greengrass Certified
- Ubuntu Core™ Certified
- Ubuntu Server Certified
- Red Hat Enterprise Linux Certified

SOFTWARE

Operating System

Windows® 10 IoT Enterprise LTSC 2021, English

ACCESSORIES

Bundled Accessories

IP50 Dust Cover Kits

MODEL

TopSeller	: Yes	Announce Date	: 2023-07-07
EAN / UPC / JAN	: 197528819693	End of Support	: 2030-01-19



SE 10-I

Product image is a sample, it may not match the real color of this model
Note:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to <https://psref.lenovo.com/Detail/2269?M=12NK000VCM>

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Professional Wireless Combo Keyboard & Mouse (US English)

4X30H56796

This sleek and stylish full-size keyboard and mouse combo offers exceptional quality in a modern wireless solution. The slim 3-zone keyboard with number pad has responsive quiet keys and a premium typing experience. O...

Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Onsite (5WSIL39202)
BETTER	3Y Premier Support Plus upgrade from 3Y Onsite (5WSIL39468)
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WS0U26647)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference