



SPECIFICATION SHEET

All Purpose Cleaner

Lysol® Advanced Deep Clean All Purpose Cleaner – 32 fl. oz.

Superior* grease cutting performance with 3x faster cleaning power* while killing 99.9% of viruses and bacteria.** An advanced formula that powers through your toughest cleaning jobs.



Product Information

Lysol® Advanced Deep Clean All Purpose Cleaner	Units/Case	Unit Size	Reckitt Item #
Lemon Breeze® Scent	12	32 fl. oz.	19200-00351

Shipping Specifications

Reckitt Item #	19200-00351
Package Size	32 fl. oz.
Case Pack	12
Pallet Cases	36
Tie/High	9/4
Case Weight	30.60
Case Cube	1.38
Case L x W x H	16.13 x 12.69 x 11.63
Item D x W x H	3.00 x 5.14 x 10.63
Item Cube	0.095
Item Weight	2.40
Item UPC	019200003513
SCS Case GTIN	10019200003510

Technical Specifications

Technical Data	Lysol® Advanced Deep Clean All Purpose Cleaner
Color/Form	Clear / Liquid
Fragrance	Lemon Breeze®
Active Ingredient	Alkyl (67% C ₁₂ , 25% C ₁₄ , 7% C ₁₆ , 1% C ₈ -C ₁₀ -C ₁₈) dimethyl benzyl ammonium chloride
Other Ingredients	99.8924%
pH	10.5 to 11.5
EPA Registration #	777-91

USE AREAS	SURFACE TYPES ²
<ul style="list-style-type: none"> - Desks - Counters¹ - Tables¹ - Chairs - Appliance Exteriors - Sinks - Faucets 	<ul style="list-style-type: none"> - Door Handles - Handrails - Water Fountain Push Buttons¹ - Walls - Floors - Hard, non-porous surfaces
	<ul style="list-style-type: none"> - Chrome - Enamel - Fiberglass - Glazed Ceramic - Glazed Porcelain - Glazed Tile - Plastic
	<ul style="list-style-type: none"> - Sealed Granite - Sealed Marble - Stainless Steel - Vinyl - Hard, non-porous surfaces

*Compared to Lysol® All Purpose Cleaner – Trigger – Lemon Breeze®

**When used as directed

¹Rinse all food contact surfaces with potable water after use.

²Do not use on brass, copper or unwaxed vinyl. Natural porous, lacquered and hand finished wood surfaces should be avoided. For other surfaces, test on a small hidden area before use.

GERMICIDAL EFFICACY

10 Minute Disinfection - Bacteria	ATCC No.
(Vancomycin Resistant) Enterococcus faecalis [VRE]	(51299)
2 Minute Disinfection - Bacteria / Fungi	ATCC No.
Acinetobacter baumannii MDR	(19606)
Bordetella pertussis	(12743)
Campylobacter jejuni	(29428)
Candida albicans	(10231)
Enterobacter aerogenes MDR	(29751)
(Vancomycin Resistant) Enterococcus faecalis [VRE]	(51575)
Escherichia coli	(43893)
Escherichia coli O111:H8	(BAA-184)
Escherichia coli O157:H7	(43888)
Klebsiella pneumoniae NDM-1 positive	(CDC1000527)
Klebsiella pneumoniae Carbapenem resistant	(BAA1705)
Legionella pneumophila	(33153)
Listeria monocytogenes	(7644)
Pseudomonas aeruginosa	(15442)
Salmonella enterica	(10708)
Salmonella enterica serovar typhi	(6539)
Serratia marcescens	(14756)
Shigella dysenteriae	(11835)
Staphylococcus aureus	(6538)
(Methicillin Resistant) Staphylococcus aureus [MRSA]	(33592)
(Community-Associated Methicillin Resistant) Staphylococcus aureus - CA-MRSA USA 300	(NRS 384)
(Vancomycin Resistant) Staphylococcus aureus - VSRSA	(NARSA VRS1)
Streptococcus pyogenes (Strep)	(12384)
Vibrio cholerae	(11623)
Yersinia enterocolitica	(23715)
10 Minute Disinfection - Viruses	ATCC No.
Influenza A2 [Japan 305/57] (Flu Virus)	(VR-100)
2 Minute Disinfection - Viruses	ATCC No.
Canine Distemper Virus	(VR-128)
(Human) Coronavirus	(VR-740)
Cytomegalovirus	(VR-538)
Hepatitis B Virus (HBV) (DHBV - surrogate)	(Hepadna)
Hepatitis C Virus (HCV) (BVDV - surrogate)	(NVSL)
Herpes Simplex Virus Type 1	(VR-733)
Herpes Simplex Virus Type 2	(VR-734)
Human Immunodeficiency Virus (HIV) Type 1	(n/a)

2 Minute Disinfection - Viruses (continued)	ATCC No.
Infectious Bovine Rhinotracheitis	(VR-188)
Influenza A (Flu Virus)	(VR-544)
(Avian) Influenza A (H1N1) Virus	(VR-98)
Influenza A (2009-H1N1) Virus	(CDC2009712192)
(Avian) Influenza A (H3N2) Reassortant Virus	(VR-2072)
(Avian) Influenza A (H7N9) Virus	(CDC2013759189)
Newcastle Disease Virus	(VR-108)
Parainfluenza Virus Type 3	(VR-93)
Pseudorabies Virus	(VR-135)
Rabies Virus	(CDC Rupprecht)
Respiratory Syncytial Virus (RSV)	(VR-26)
SARS Coronavirus	(CDC200300592)
Transmissible Gastroenteritis Virus (TGE)	(n/a)
Vaccinia Virus	(VR-119)
SARS-CoV-2 (USA-WA1/2020)	
3 Minute Mildew Fungistat	ATCC No.
Aspergillus niger	(6275)
30 Second Sanitization - Bacteria - Hard, Non-Porous - Non-Food Contact Surfaces	ATCC No.
Enterococcus faecalis [VRE]	(51299)
Escherichia coli O157:H7	(43888)
Klebsiella pneumoniae	(4352)
Salmonella enterica	(10708)
Staphylococcus aureus	(6538)
Staphylococcus aureus [MRSA]	(33592)
Streptococcus pyogenes	(12384)
10 Second Sanitization - Bacteria - Hard, Non-Porous - Non-Food Contact Surfaces	ATCC No.
(Vancomycin Resistant) Enterococcus faecalis [VRE]	(51575)
Escherichia coli O157:H7	(43888)
Klebsiella pneumoniae	(4352)
Salmonella enterica	(10708)
Staphylococcus aureus	(6538)
Staphylococcus aureus (Methicillin Resistant) [MRSA]	(33592)
Streptococcus pyogenes	(12384)

DIRECTIONS FOR USE

Lysol® Advanced Deep Clean All Purpose Cleaner

To Operate: Turn nozzle to desired position.

To Clean: Apply to surface until thoroughly wet. Wipe with clean cloth or sponge.

To Clean Greasy Soil: Allow product to sit 15-20 seconds to penetrate soil before wiping. Repeat if necessary.

To Sanitize/Disinfect: Pre-clean surface. Spray surface until thoroughly wet.

To Sanitize: Leave for 10 seconds before wiping.

To Disinfect: Leave for 2 minutes before wiping.

**For additional product information and Safety Data Sheet,
please visit www.rbnainfo.com**