



Poly Savi 8220 Office Stereo DECT 1920-1930 MHz Headset (7S4B5AA)

Overview

Power through the noise

Hearing every word clearly on a call is not a nice-to-have, it is a must-have. With the Poly Savi 8200 Office series, you can tune out noise and nearby conversations with noise-canceling microphone plus close conversation limiting.

Freedom to roam

Being able to talk for a long time on a single charge means work gets done. And with the freedom to roam up to 590 ft/180 m means you can keep the calls going, even away from the desk [1].

Multi-device connectivity

Today's enterprise and contact center professionals work on a range of devices. Savi 8200 Office Series headset systems have 3-way connectivity – computer, desk phone and mobile phone – for convenient conferencing on up to two devices at once.

Features

3-way connectivity

Manage all your calls with a compatible single base that offers 3-way connectivity – computer, desk phone and mobile.

Crystal-clear calls

Reduce background sounds for the person you are talking to with a noise-canceling microphone and close conversation limiting while you stay in the zone with active noise canceling.

Take it further

Everyone can move, multitask, and get more done with up to 13 hours of talk time on a single charge. Convenient voice prompts notify of mute status, wireless range limit and more.

Privacy is ensured

Privacy of your conversation is ensured: DECT™ security-certified headset.

Training made easy

Make training and collaboration easy with the ability to conference up to 4 headsets onto a single base.

Communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.^[2]

[1] Line of sight from computer.

[2] Visit www.poly.com/savi-8200-office for more detail.

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Audio	Active noise cancellation (ANC)
Battery life	Up to 50 days (standby time); Up to 13 hours (talk time)
Battery type	Rechargeable Li-ion polymer
Button user controls	Call answer/end; Mute; Volume +/-; Power on/off; ANC on/off
Cartons per layer	6
Cartons per pallet	30
Certified collaboration software	Zoom
Charge time	3 hours
Color	Black
Connection type	DECT™
Connects to	Desk phone; PC; Mobile
Country of origin	Made in Mexico
ECCN	5A992
Ear cushions	Artificial leather (surface material)
HTS code	8517620090
Headphone type	On-ear (stereo)
Impedance	32 ohms
Indicator light	On call
Management Software	Poly Lens
Manufacturer Warranty	Poly standard two-year limited warranty
Multiple order quantity	1
Package dimensions (W x D x H)	2
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	300 g
Package weight	0.66 lb
Paired devices	Up to 2
Pallet (layers)	5
Pallet dimensions	40 x 48 x 55.11 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 140 cm
Pallet weight	197.67 kg
Pallet weight	435.78 lb
Products per pallet	180

Products per pallet layer	36
Sensitivity (microphone)	112 dB SPL
Speaker size	32 mm
Special features	Adjustable headband
UNSPSC code	52161514
UPC number	(A2K) 197192932070; (ABA) 197497168969; (ABB) 197497168976; (ABG) 197192932087; (AC3) 197192932094; (AC4) 197192932100; (UUF) 197192600061
Voice alerts	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
Weight	0.35 lb
Weight	160 g
What's in the box	Wireless headset; Office base; USB Type-A cable; USB Type-C® cable; Telephone cable; AC power adapter
Wireless range	Up to 180 m in open area; Up to 55 m in typical office environment
Wireless range (imperial)	Up to 590 ft in open area; Up to 180 ft in typical office environment

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Services

Poly Services

★ : Recommended

Poly Support Services

3 year Poly+ Savi Service	PSAVI312 ★
3 year Partner Poly+ Savi Service	PSAVI362

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

Poly APA-23 Electronic Hookswitch TAA	85Q50AA
Poly APA-24 Electronic Hookswitch TAA	85Q52AA
Poly APC-43 Electronic Hookswitch (Bagged) TAA	85Q56AA
Poly APC-43 Electronic Hookswitch TAA	85Q55AA
Poly APC-45 Electronic Hookswitch TAA	85Q57AA
Poly APC-82 Electronic Hookswitch TAA	8H981AA
Poly APD-80 Electronic Hookswitch TAA	85Q58AA
Poly APN-91 Electronic Hookswitch TAA	85Q59AA
Poly APP-51 Electronic Hookswitch TAA	85Q60AA
Poly APS-11 Electronic Hookswitch TAA	85Q78AA
Poly APT-31 Electronic Hookswitch TAA	85Q84AA
Poly APU-72 Electronic Hookswitch TAA	85Q95AA
Poly APU-75D Electronic Hookswitch TAA	85Q99AA
Poly APU-76 Electronic Hookswitch TAA	85R00AA
Poly APV-63 Electronic Hookswitch TAA	85R01AA
Poly APV-66 Electronic Hookswitch TAA	85R02AA
Poly Busy Light (Angle Plug)	920Q4AA
Poly EHS 3.5mm to 3.5mm Cable	85R17AA
Poly HL10 Extended Arm	8L554AA
Poly HL10 Handset Lifter	784Q1AA
Poly HL10 Handset Lifter TAA	8R713AA
Poly HL10 Handset Lifter with Straight Plug TAA	784Q2AA
Poly HL10 Lifter Arm +Ring Detector Accessory	8A7E3AA
Poly RD-1 Electronic Hookswitch	85R71AA
Poly Savi 7410/7420 Office Charging Cradle	8L556AA
Poly Savi 8200 5 Unit Charge Base	85R34AA
Poly Savi 8200 Leatherette Ear Cushions (2 Pieces)	85Q63AA
Poly Savi 8200 USB-A Headset Charging Cable	85R35AA
Poly Savi 8210 Battery with Removal Tool	85R37AA
Poly Savi 8210 Monaural DECT 1880-1900 MHz Top +Charging Cradle	8Y9C3AA

Poly Savi 8210 Top and Charging Cradle	85T30AA
Poly Savi 8210/8220 Universal Power Supply -9V 500mA	783M9AA
Poly Savi 8220 Battery with Removal Tool	85R39AA
Poly Savi 8220 Stereo DECT 1880-1900 MHz Top +Charging Cradle	8Y9C4AA
Poly Savi 8220 Top and Charging Cradle	85T31AA
Poly Savi 8240/8245 Battery	85R41AA
Poly Savi 8240/8245 Deluxe Charging Cradle	85R44AA
Poly Savi 8240/8245 Fit	85R45AA
Poly Savi 8240/8245 Foam Sleeves for Earloop (20 Pieces)	85Q65AA
Poly Savi 8240/8245 Standard Charging Cradle	85R47AA
Poly Savi 8240/8245 USB-A Charging Cable for Headset and Battery	85R43AA
Poly Savi 8245 Deluxe Cradle with Battery	85R49AA
Poly Savi 8245 Headset Cradle and Wearing Accessories	85T32AA
Poly Savi 8400/7400 Office DECT 1880-1900 MHz Base	8L569AA
Poly Savi 8400/7400 Office DECT 1920-1930 MHz Base	8L571AA
Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1880-1900 MHz Base	8L558AA
Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1920-1930 MHz Base	8L562AA
Poly Savi 8410/8420 Office Charging Cradle	8L573AA
Poly Savi 8440/8445 Office Charging Cradle	8L577AA
Poly Savi D400 UC DECT 1880-1890 MHz Dongle	8J8V9AA
Poly Savi D400 UC DECT 1880-1900 MHz Dongle	8J8V7AA
Poly Savi D400 UC DECT 1893-1906 MHz Dongle	8J8V6AA
Poly Savi D400 UC DECT 1910-1920 MHz Dongle	8J8V8AA
Poly Savi D400 UC DECT 1920-1930 MHz Dongle	85T33AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1880-1900 MHz Dongle	8J8W1AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1893-1906 MHz Dongle	8J8W0AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1910-1920 MHz Dongle	8J8W2AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1920-1930 MHz Dongle	85T34AA
Poly Savi Hard Case	85R51AA
Poly Savi Office Power Supply with Right Angled Plug -9V 1000mA	8L5A2AA
Poly Savi Office S2 Telephone Cable	85R55AA
Poly Savi Office Straight Plug Online Indicator	85R52AA
Poly Savi Office Telephone Interface Cable	85R57AA
Poly Savi Office USB-A PC Connection Cable	85R54AA

Poly Savi Office Universal AC Power Supply with Straight Plug -9V 1000mA	85R59AA
Poly Savi Office Universal AC Power Supply with Straight Plug -9V 500mA	85R61AA
Poly Savi Universal Power Supply -9V 500mA	85R63AA
Poly Savi W8210/8220 Charging Cradle	85R65AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – May 16, 2024 6:38 AM UTC+0000