

ThinkStation P3 Tower

Business professionals can enhance their work experience and performance with this 27-liter tower, powered by up to 13th Gen Intel Core i9 Processor. Optional Wi-Fi 6E enables faster connection speeds even in densely congested areas, while the optional Thunderbolt 4 port allows for high-speed display connectivity and file sharing. The tower also includes a slew of security features, such as a discrete TPM 2.0 chipset, power-on password, and UEFI secure boot, that keep data well-protected.



With up to 128GB DDR5 memory configuration, this device provides exceptional portable power, allowing users to easily multitask on compute-intensive workflows. Additionally, EPEAT Gold and ENERGY STAR 8.0 certification means the laptop is energy-efficient and built to last longer.

Business specialists can easily view and compare detailed spreadsheets by connecting multiple independent displays through onboard video ports and discrete graphics.

EPEAT Gold and ENERGY STAR 8.0 certification means it is an energy efficient device.

**Professional machines for
advanced users**

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service

If a problem can't be fixed remotely, we will visit your location
Normally next business day service
Agreed appointment times



Accessories

Lenovo Go Wired Speakerphone

Microsoft Teams certified, omni-directional far-field 2x microphones array
Portable plug-and-play capabilities and effortless PC UC support
Comes with intuitive control with volume wheel, tactile keys, and readable LEDs



PN: 4XD1C82055, GXD1C82051

Lenovo Pro Stereo Wired VOIP Headset

USB or 3.5mm analog connection with integrated call controls
Skype for Business and Microsoft Teams certified HD noise-cancelling microphone



PN: 4XD0S92991

ThinkStation P3 Tower

Performance

Processor

Up to one 13th Gen Intel Core i3/i5/i7/i9

Operating System

Windows 11 Pro
Windows 11 DG Windows 10 Pro 64
Windows 11 Home
Ubuntu Linux LTS
Red Hat Enterprise Linux (certified only)

Graphics

Supports up to one NVIDIA RTX A5500 or two NVIDIA RTX A2000

Chipset

Intel W680 chipset

Memory ¹

Up to 128GB, four DDR5 DIMM slots

¹The max memory is based on the test results with current Lenovo memory offerings.

Storage ²

Up to 5 drives (4x HDD + 1x M.2 SSD) or 6 drives (3x HDD + 3x M.2 SSD)
• 3.5" HDD up to 6TB each
• 2.5" HDD up to 1TB each
• M.2 SSD up to 4TB or 2TB each
• RAID 0/1/0/5 supported for HDD
• RAID 0/1 supported for M.2 SSD

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Design

Dimensions ³

180 x 415 x 370 mm (7.09 x 16.34 x 14.57 inches)

³The system dimensions may vary depending on configurations.

Weight ⁴

13.6 kg (29.9 lbs, maximum configuration)

⁴The system weight is approximate and may vary depending on configurations

Connectivity

Ethernet

One onboard Gigabit Ethernet
Additional Ethernet options via PCIe adapter

WLAN + Bluetooth ⁵

Up to Intel Wi-Fi 6E AX211, Bluetooth 5.1, vPro

⁵Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

Security & Privacy

Discrete TPM 2.0

Cable lock*

E-lock*

Kensington Security Slot, 3 x 7 mm

Padlock Loop

Chassis intrusion switch*

Manageability

Intel vPro Enterprise with Intel AMT 16.0*

⁶Intel vPro offers a superset of DASH's defined capabilities.

Certifications

ENERGY STAR 8.0*

EPEAT Gold Registered*

ErP Lot 3

TCO Certified 9.0

RoHS compliant

⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁸EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.