

Lenovo Legion Y27qf-30

PSREF

Product Specifications Reference

PERFORMANCE

Display Size	27"
View Area	596.7x335.7 mm
Panel	In-Plane Switching
Backlight	WLED
Aspect Ratio	16:9
Resolution	2560x1440
Pixel Pitch	0.311x0.311 mm
Dot / Pixel Per Inch	109 dpi
View Angle (H / V)	178° / 178°
Response Time	0.5ms (MPRT) / 1ms (Level 4) / 2ms (Level 3) / 3ms (Level 2) / 4ms (Level 1) / 5ms (Off)
Color Support	1.07 Billion
Refresh Rate	240Hz / 250Hz (Overclock)
Brightness	400 cd/m ² (Typical)
Contrast Ratio	1000:1
Color Gamut	99% sRGB, 95% DCI-P3
Screen Surface Treatment	Anti-glare
Curvature	None
Camera	Modular Camera Support
Microphone	None
Speakers	3Wx2
Power Consumption (Typical / Maximum)	34.6W / 79.4W
Power Adapter	Integrated
Touchscreen	None

Smart System	None
DESIGN	
Stand	Tilt, Swivel, Pivot, Height Adjust Stand
Case Color	Raven Black
Side Bezel Width	2 mm
Mounting	Supports VESA mount 100mm
ThinkCentre® M Series Support	None

Dimensions (WxDxH)	<ul style="list-style-type: none">Lowest Position 613.7 x 258.8 x 401.5 mm (24.16 x 10.19 x 15.81 inches)Highest Position 613.7 x 258.8 x 536.5 mm (24.16 x 10.19 x 21.12 inches)Unpacked Head Only 613.7 x 61 x 365.9 mm (24.16 x 2.4 x 14.41 inches)
Packaging Dimensions (WxDxH)	720 x 160 x 510 mm (28.35 x 6.30 x 20.08 inches)
Weight	<ul style="list-style-type: none">Monitor With Stand 6.5 kg (14.3 lbs)Monitor Head Only 4.5 kg (9.9 lbs)

Packaging Weight	9.7 kg (21.38 lbs)
CONNECTIVITY	
USB Port	4x USB 3.2 Gen 1, 1x USB-B 3.2 Gen 1
Video Connector	2x HDMI® 2.1 TMDS, 1x DP 1.4
Network Connectivity	None

SERVICE	
Base Warranty	1-year

CERTIFICATIONS	
Environmental Certification	RoHS, EU Energy Efficiency Level (Level-F)
Ergonomic Certification	Eyesafe® Display 2.0, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Eye Comfort 2.0
Sync Technology	AMD FreeSync™ Premium, Adaptive Sync

Special Features	<ul style="list-style-type: none">Factory Calibration: Avg. Delta E<2AMD FreeSync™ Premium AMD FreeSync™ technology only can work with AMD Radeon™ series graphics card.Lenovo® Artery (Lenovo® Accessories and Display Manager) Support Lenovo® Artery supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems). Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.Adaptive SyncNatural Low Blue Light
------------------	---

SOFTWARE	
Operating System	Support Windows® 10, Windows® 11

ACCESSORIES	
Video Cables	DP Cable, USB Type-A to Type-B Cable

MODEL	
Announce Date	: 2023-01-30
EAN / UPC / JAN	: 0196802793131 / 0196802793131 / None



Product image is a sample, it may not match the real color of this model

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



PSREF
Product Specifications
Reference