

# ThinkPad T14s Gen 2 (AMD)

This newly redesigned ThinkPad combines mobility and performance for the ultimate productivity experience in today's hybrid work environment. Powered by the latest AMD Ryzen™ 5000 PRO series processors and up to 32GB LPDDR4x RAM for faster processing, the device can breeze through day-to-day tasks with ease. At 1.28 kg (2.83lbs), it is remarkably lightweight yet offers outstanding durability and a battery that can last up to 14.9 hours.



Users will appreciate the optional 4K Dolby Vision HDR display offering exceptional contrast and colour depth. Alternatively, the Full HD display with PrivacyGuard digitally prevents shoulder surfers from viewing information on the screen. Onboard Thunderbolt 3 port enables quick transfer of large files.

With Modern Standby, busy professionals can configure the device to receive important updates even with the lid closed, and resume in a second when needed – just like a smartphone. Optional 4G/5G WWAN module enables reliable connectivity when WiFi network is weak or unavailable.

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

## Lenovo devices that are a class apart

The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.

## Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### Premier Support

Talk directly with advanced technical support agents  
 Support for software & hardware  
 Next business day onsite repairs

## Accessories

### Lenovo Professional Wireless Keyboard & Mouse

Wireless keyboard and mouse combo with reliable 2.4 GHz wireless connection  
 Slim keyboard with number pad, noise-suppression design, dedicated media controls & adjustable tilt legs  
 Contoured design of the mouse suits both left-handed & right-handed users



PN: 4X30H56796

### ThinkPad USB-C Dock Gen 2

Connects via a single USB-C cable which also charges the PC  
 1x USB-C, 2x USB2.0, 3x USB3.1 ports (including 1x always-on for charging devices)  
 2x DisplayPort and 1x HDMI. Supports 1x 4K or 3x Full HD displays



PN: 40AS0090xx

# ThinkPad T14s Gen 2 (AMD)

## Performance

---

### Processor

AMD Ryzen™ 3/5/7 Processor

---

### Operating System

Powered by Windows 10 Pro

---

### Graphics

AMD Radeon Graphics

---

### Memory

Up to 32GB LPDDR4x-4266

---

### Storage

One drive, up to 2TB M.2 2280 SSD

---

### Optical

---

### Audio

Stereo speakers, 2W x2, Dolby® Audio™  
Dual array microphones, far-field

---

### Battery

Up to 14.9hrs, 57Wh

---

## Design

---

### Display

14.0" Dolby Vision HDR 400 screen, UHD (3840x2160), IPS, 1500:1 contrast ratio, 100% Adobe RGB, 500 nits  
14.0" ThinkPad Privacy Guard screen, Full HD (1920x1080), IPS, 1000:1 contrast ratio, 72% gamut, 500 nits (touch)  
14.0" Low Power screen, Full HD (1920x1080), IPS, 1200:1 contrast ratio, 72% gamut, 400 nits  
14.0" screen, Full HD (1920x1080), IPS, 700:1 contrast ratio, 45% gamut, 300 nits (touch)  
14.0" screen, Full HD (1920x1080), IPS, 700:1 contrast ratio, 45% gamut, 300 nits

---

### Keyboard

6-row, spill-resistant, multimedia Fn keys with Unified Communications controls

---

### Dimensions

From 327.5 x 224 x 16.14 mm (12.89 x 8.82 x 0.64 inches)

---

### Weight

From 1.28kg (2.83lbs)

## Connectivity

---

Compatible with USB-C and side mechanical docking solutions

## Security & Privacy

---

Touch style fingerprint reader on power button, match-on-chip (optional)  
Camera privacy shutter (optional)  
Smart card reader (optional)  
Kensington Nano Security Slot

## Certifications

---

EPEAT Gold. Energy Star 8.0