

ThinkPad T14 Gen 3 (Intel)

Designed for the modern workforce who need to work from anywhere, this compact desktop is a powerhouse of modern features. It has up to 12th Gen Intel Core processor and multiple display options with technologies like low power consumption, anti-glare, and anti-smudge to choose from. With its onboard Intel UHD graphics and discrete NVIDIA GeForce, combined with up to 2TB ultra-fast SSD storage, it delivers quicker responsiveness while working on heavy-duty applications and complex data or files.



Comes with a slew of ports, including 2x USB 3.2 Gen 1. Users can connect up to 3 external monitors via Thunderbolt and HDMI ports for seamless multitasking. WiFi 6 support enables faster uploads and downloads as well as lower latency when used with compatible routers.

Security solutions include an optional IR camera for Windows Hello for facial recognition, an optional web camera shutter for user privacy during calls or meetings, and a Kensington slot for device safety.

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

Lenovo devices that are a class apart

The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Premier Support

Talk directly with advanced technical support agents
 Support for software & hardware
 Next business day onsite repairs

Accessories

Lenovo Powered USB-C Travel Hub

Connects to a PC through a single USB-C cable which also recharges the device
 Connect to an external display with HDMI or VGA, and other peripherals with 2x USB ports
 Compact 183x100mm (7.2x4") design with integrated cable management



PN: 4X90S92381

Lenovo 700 Ultraportable Bluetooth Speaker

Just 11mm (0.43") thin and weighing 145g (0.32lb), this ultra-thin Bluetooth speaker delivers 360-degree sound with 2x 2Watt power output
 Supports Siri and Google Assistant voice commands for your iOS and Android devices, as well as a dedicated button for taking calls
 Fast-charges in 2 hours and lasts for up to 12hours of audio playback or voice calls



PN: 4XD0T32974

ThinkPad T14 Gen 3 (Intel)

Performance

Processor

12th Gen Intel U or P Series Core i5/i7

Operating System

Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language
Windows 11 DG Windows 10 Pro 64
Linux
Ubuntu Linux

Graphics¹

Intel Iris Xe Graphics eligible (integrated)
NVIDIA GeForce MX550

¹Intel Iris Xe Graphics capability requires system to be configured with dual-channel memory. On the system with single-channel memory, Intel Iris Xe Graphics will function as Intel UHD Graphics.

Memory²

Up to 40GB or 48GB DDR4-3200, 1x Soldered + 1x SO-DIMM

²The max memory is based on the test results with current Lenovo memory offerings.

Storage³

Up to 1x 2TB M.2 2280 PCIe NVMe SSD

³The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Audio
Dual-microphone array, far-field, Dolby Voice*

Camera

HD 720p, with privacy shutter
FHD 1080p, with privacy shutter
FHD 1080p + IR hybrid, with privacy shutter

Battery⁴

39.3Wh or 52.5Wh battery, up to 10.0 hr, Rapid Charge

⁴Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter

45W USB-C adapter, PD 3.0
65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0

Design

Display⁵

14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 300nits, 45% NTSC
- 300nits, 45% NTSC, touch
- 400nits, 100% sRGB, low power, Eyesafe
- 500nits, 100% sRGB, touch, ThinkPad Privacy Guard

14" 2.2K (2240x1400) IPS Anti-glare 16:10
- 300nits, 100% sRGB, Eyesafe

14" WQUXGA (3840x2400) IPS ARAS 16:10
- 500nits, 100% DCI-P3, DisplayHDR 400, Dolby Vision, Eyesafe

⁵IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard

6-row, spill-resistant, optional backlight

Touchpad

TrackPoint and glass-like Mylar surface touchpad
61 x 115 mm (2.40 x 4.53 inches)

Dimensions⁶

Models with storm grey cover:
317.7 x 227.36 x 17.9 mm (12.51 x 8.95 x 0.70 inches)
Models with black cover:
317.7 x 226.9 x 17.9 mm (12.51 x 8.93 x 0.70 inches)

⁶The system dimensions may vary depending on configurations.

Weight⁷

Starting at 1.358 kg (2.99 lbs)

⁷The system weight is approximate and may vary depending on configurations

Color

Storm grey
Thunder black

Case material

Aluminium (top), PPS (bottom)
PC + 20% CF + 50% GF (top), PPS (bottom)
PC + 20% CF + 50% GF (top), aluminium (bottom)

Connectivity

Ethernet

Gigabit onboard Ethernet

WLAN + Bluetooth^{8 9}

802.11ax (Wi-Fi 6E), Bluetooth 5.1
Up to Intel Wi-Fi 6E AX211, Bluetooth 5.1

⁸Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitations.

⁹Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

WWAN

4G LTE CAT4
4G LTE CAT6

NFC

Near Field Communication*

Ports

1x USB 3.2 Gen 1
1x USB 3.2 Gen 1 (Always On)
2x Thunderbolt 4 / USB4 40Gbps (data, PD 3.0, DP 1.4)
1x HDMI 2.1, up to 4K/60Hz
1x Ethernet (RJ-45)
1x Headphone / microphone combo jack (3.5mm)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt or USB-C

Security & Privacy

Discrete TPM 2.0
Kensington Nano Security Slot
Smart card reader*
Touch style MOC fingerprint reader*
Camera privacy shutter*
IR camera for Windows Hello*
Privacy Guard with Privacy Alert*
Human Presence Detection (software)
Glance by Mirametrix
RFID reader*

Manageability

Intel vPro Enterprise
Intel vPro Essentials

¹⁰Intel vPro offers a superset of DASH's defined capabilities

Certifications

Green Certifications^{11 12}

ENERGY STAR 8.0*
EPEAT Gold Registered*
ErP Lot 3
TCO Certified 9.0
RoHS compliant

¹¹The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

¹²EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country

Other Certifications

Eyesafe Certified*
MIL-STD-810H