




F110 FULLY RUGGED TABLET

- 11th Generation Intel® Core™ i7 / i5 vPro™ Processor
- Thunderbolt™ 4 brings lightning speed and performance
- Enhanced enterprise security with optional Intel® vPro™, Windows Hello face-authentication camera, TPM 2.0 and many more multi-factor authentication options
- Configurable options to fit diverse data collection needs: Optional 1D/2D imager barcode reader / USB 2.0 port / Serial port + LAN port (RJ45)
- LifeSupport™ battery swappable technology



F110 FULLY RUGGED TABLET

SPECIFICATIONS

Operating System	Windows 10 Pro
Mobile Computing Platform Options	<p>Intel® Core™ i5-1135G7 Processor Max. 4.2GHz with Intel® Turbo Boost Technology - 8MB Intel® Smart Cache</p> <p>Platform options: Intel® Core™ i5-1145G7 vPro™ Processor Max. 4.4GHz with Intel® Turbo Boost Technology - 8MB Intel® Smart Cache</p> <p>Intel® Core™ i7-1165G7 Processor Max. 4.7GHz with Intel® Turbo Boost Technology - 12MB Intel® Smart Cache</p> <p>Intel® Core™ i7-1185G7 vPro™ Processor Max. 4.8GHz with Intel® Turbo Boost Technology - 12MB Intel® Smart Cache</p>
VGA Controller	Intel® Iris® X® Graphics
Display	<p>11.6" IPS TFT LCD FHD (1920 x 1080) Protection film 1,000 nits LumiBond® display with Getac sunlight readable technology Capacitive multi-touch screen</p>
Storage & Memory	<p>8GB DDR4 Optional: 16GB / 32GB DDR4</p> <p>256GB PCIe NVMe SSD Optional: 512GB / 1TB / 2TB PCIe NVMe SSD</p>
Keyboard	<p>Power button 4 tablet programmable buttons</p>
Pointing Device	<p>Touchscreen - Capacitive multi-touch screen - Optional: Dual mode touchscreen (multi-touch and digitizer)</p>
Expansion Slots	<p>Optional: Smart card reader Optional: 1D/2D imager barcode reader, or USB 2.0 port, or serial port + LAN (RJ45) ⁱ Optional ⁱⁱ: HF RFID Reader, or Fingerprint Reader</p>

F110 FULLY RUGGED TABLET

I/O Interface	FHD webcam x 1 ⁱⁱⁱ 8M pixels auto focus rear camera x 1 Audio in/out combo x 1 DC in Jack x 1 Thunderbolt™ 4 Type-C x 1 USB 3.2 Gen 2 Type-A x 1 Docking connector x 1 Optional: SIM card slot x 1 (Micro-SIM, 3FF) Optional: Windows Hello face-authentication camera (front-facing) x 1 ⁱⁱⁱ Optional: RF antenna pass-through for GPS, WWAN and WLAN
Communication Interface	Intel® Wi-Fi 6 AX201, 802.11ax Bluetooth (v5.2) ^{iv} Optional: Dedicated GPS Optional: 4G LTE mobile broadband with integrated GPS ^v Optional: 10/100/1000 base-T Ethernet ⁱ (Occupies expansion slot)
Pre-installed software	Getac Utility Getac Camera Getac Geolocation Getac Barcode Manager ^{xi} Optional: Absolute Persistence®
Security Features	TPM 2.0 Kensington lock Optional: Intel® vPro™ Technology Optional: Windows Hello face-authentication camera (front-facing) ⁱⁱⁱ Optional: HF RFID Reader ^{vi, ii} , or Smart Card Reader, or Fingerprint Reader ⁱⁱ
Power	AC adapter(90W,100-240VAC, 50/60Hz) Li-ion smart battery(11.4V,typical 2680mAh;min. 2640mAh) x 2 LifeSupport™ battery swappable technology Optional: High capacity battery (11.1V, typical 4200mAh; min.4080mAh) x 2
Dimension (W x D x H) & Weigh	314 x 207 x 25mm (12.4" x 8.15" x 0.98") 1.52kg (3.35lbs) ^{vii}

F110 FULLY RUGGED TABLET

Rugged Features

MIL-STD-810H certified
IP66 certified
MIL-STD-461G certified ^{viii}
Vibration & 6ft (1.8m) drop resistant
e-Mark certified for vehicle usage
Optional: ANSI/UL 121201, CSA C22.2 NO. 213 (Class I, Division 2, Groups A, B, C, D) ^{ix}

Environmental Specifications

Temperature ^x:
- Operating: -29°C to 63°C / -20°F to 145°F
- Storage: -51°C to 71°C / -60°F to 160°F
Humidity:
- 95% RH, non-condensing

Accessories

Battery (11.4V, typical 2680mAh; min. 2640mAh)
AC adapter (90W, 100-240VAC, 50 / 60Hz)
Capacitive stylus with tether

Optional:

Carry bag
Battery (11.4V, typical 2680mAh; min. 2640mAh)
High capacity battery (11.1V, typical 4200mAh; min. 4080mAh)
Multi-Bay charger (Dual-Bay)
Multi-Bay charger (Eight-Bay)
AC adapter (90W, 100-240VAC, 50 / 60Hz)
Office dock AC adapter (90W, 100-240VAC)
MIL-STD-461 certified AC adapter (90W, 115-230VAC)
DC-DC vehicle adapter (120W, 11-32VDC)
Digitizer pen
Capacitive stylus with tether
Hand strap
Shoulder strap (2-point)
Shoulder harness (4-point; handsfree)
Detachable keyboard
Vehicle cradle
Vehicle dock
Office dock
100W Type-C adapter

Bumper-to-Bumper warranty

Accidents can take your equipment out of service when you least expect it, especially in a rugged environment, which can cause costly equipment downtime.

That is why Getac has introduced accidental damage as standard under our Bumper-to-Bumper warranty, to help minimize your enterprise IT costs. Bumper-to-Bumper is your hassle-free guarantee.

That means you can depend on us to have your unit back in service within days.

Standard

3 years Bumper-to-Bumper

F110 FULLY RUGGED TABLET

- I. 1D/2D imager barcode reader, or USB (USB 2.0) port, or Serial port + LAN are mutually exclusive options.
- II. HF RFID reader and fingerprint reader are mutually exclusive options.
- III. FHD webcam and optional Windows Hello face-authentication camera (front-facing) are mutually exclusive options.
- IV. Bluetooth performance and connectable distance may be subject to interference with the environments and performance on client devices, users may be able to reduce effects of interference by minimizing the number of active Bluetooth wireless devices that is operating in the area.
- V. Units with 4G LTE option comes with an embedded SIM card slot.
- VI. 13.56MHz HF RFID reader (ISO 15693, 14443 A/B, Mifare and FeliCa™ compliant).
- VII. Weight and dimensions vary from configurations and optional accessories; optional high-capacity batteries add approx. 6mm (H), 0.24kg.
- VIII. MIL-STD-461 90W AC adapter sold separately.
- IX. Available with limited configurations.
- X. Tested by an independent third-party test lab following MIL-STD-810H.
- XI. Available when barcode reader option is selected.

Information provided herewith is for reference only, available specification shall be subjected to quotation by request.

	Vehicle Dock	Office Dock
Serial Port	2	2
External VGA	1	1
Microphone	1	1
Audio Output	1	1
DC in Jack	1	1
USB	4	4
LAN	1	1
HDMI	1	1
RF Antenna Connector	3 (WWAN, WLAN, GPS)	-

GETAC TECHNOLOGY CORPORATION

5F, Building A, No. 209, Section 1, Nangang Rd.,
Nangang Dist., Taipei City, 11568, Taiwan, R.O.C.
Tel : +886 2 2785 7888

globalmarketing@getac.com | www.getac.com

Copyright © 2021 Getac Technology Corporation and/or any of its affiliates. All Rights Reserved.

Information provided herewith is for reference only, available specification shall be subjected to quotation by request.

V01M08Y21WWW