



Poly Savi 7410 Office Monaural Microsoft Teams Certified DECT 1920-1930 MHz Headset (8L7D7AA)



Overview

Built for the modern office

Designed for the modern office with enhanced density performance, multi-device connectivity and advanced security features. You can deploy this headset across the company so everyone will benefit from increased productivity and wireless freedom.

Keep conversations private

Your conversations are private with DECT™ Security Step C, FIPS 140-2 military-grade features, and 256-bit AES encryption. You can be sure your conversations are clear thanks to a noise-canceling microphone boom with acoustic fence technology.

Increased productivity

With 3-way connectivity, a universal base, and easy set-up and pairing, the Savi 7400 office series is the perfect solution for the modern office. You can even conference four headsets together with the base for increased productivity.

Wireless freedom

With 2x better density than other DECT™ headsets, more people in shared spaces benefit from wireless headsets with clear, interference-free audio. And with a roaming range of up to 590 ft/180 m everyone can benefit from increased productivity.

Features

3-way connectivity

Manage all your calls with a compatible single base that offers 3-way connectivity – computer, desk phone and mobile.

Crystal-clear calls

Keep your conversations clear with a noise-canceling boom with Acoustic Fence technology to reduce background noise.

Privacy is ensured

Designed to meet the highest-level DECT™ Security Step C enhanced with military-grade FIPS 140-2 listed features, such as 256-bit AES encryption.^[1]

Remote management

Stay in control with remote device management for settings, firmware, and security updates.

Training made easy

Make training and collaboration easy with the ability to conference up to 4 headsets onto a single base.

Certified for Microsoft Teams

Full Microsoft Teams certification takes your Microsoft Teams experience to the next level with a button for instant access to the app and more.

[1] DECT security standards can be found on <https://etsi.org>

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Audio	Noise cancellation with Acoustic Fence technology; Microsoft Teams Open Office certified; Up to 2x more density than other DECT™ headsets; Adaptive power control to maximize user density
Base controls	Scroll wheel; Back key; USB softphone line button; Bluetooth® line button; Telephone interface line button; Configurable button
Battery life	Up to 13 hours (talk time); Up to 52 hours (standby time)
Battery type	Rechargeable Li-ion polymer
Bluetooth version	5.2
Button user controls	Power on/off; Call answer/end; Mute; Volume +/-
Cartons per layer	10
Cartons per pallet	80
Certified collaboration software	Microsoft Teams
Charge time	2 hours
Color	Black
Compatible Operating Systems	macOS; Windows
Connection type	Bluetooth®; DECT™
Connects to	Desk phone; PC; Mobile
Country of origin	Made in Mexico
ECCN	5A992
Ear cushions	Artificial leather (surface material)
HTS code	8517620090
Manufacturer Warranty	Poly standard two-year limited warranty
Minimum System Requirements	USB Type-A port (PC); USB Type-C® port (PC); Bluetooth® (mobile phone); EHS interface (desk phone)
Multiple order quantity	5
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	300 g
Package weight	0.66 lb
Pallet (layers)	8
Pallet dimensions	40 x 48 x 58.66 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 149 cm
Pallet weight	787.05 lb
Pallet weight	357 kg
Products per pallet	400

Products per pallet layer	50
Special features	Color display on office base for audio settings management
Supported bluetooth profiles	A2DP; HFP; HSP
UNSPSC code	43191638
UPC number	197497822403
Weight	0.26 lb
Weight	120 g
What's in the box	Wireless headset; USB Type-A cable; USB Type-C® cable; Office base; AC power adapter; Charging cradle; Telephone interface cable (TIC)
Wireless range	Up to 180 m in open area; Up to 55 m in typical office environment
Wireless range (imperial)	Up to 590 ft in open area; Up to 180 ft in typical office environment

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Services

Poly Services

★ : Recommended

Poly Support Services

3 year Poly+ Savi Service	PSAVI312 ★
3 year Next Business Day Hardware Advance Replacement Savi Poly DaaS Service	DSAVIDS3
3 year Partner Poly+ Savi Service	PSAVI362

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Jul 02, 2024 5:43 AM UTC+0000