

## PERFORMANCE

### Processor

AMD Ryzen™ 5 PRO 5650GE (6C / 12T, 3.4 / 4.4GHz)

### Graphics

Integrated AMD Radeon™ Graphics

### Chipset

AMD PRO 500 chipset

### Memory

1x 8GB SO-DIMM DDR4-3200

### Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

### Max Memory<sup>[1]</sup>

Up to 64GB DDR4-3200

### Storage

256GB SSD M.2 2280 PCIe® NVMe® Opal 2.0

### Storage Support<sup>[2]</sup>

Up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- M.2 SSD up to 1TB

### Optical

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC222 codec

### Speakers

1.5Wx1

### Power Supply

65W 89% Adapter

## DESIGN

### Keyboard

USB Traditional Keyboard, Black, English

### Mouse

USB Calliope Mouse, Black

### Expansion Slots

- One M.2 slot (for SSD)
- One M.2 slot (for WLAN)

### Case Color

Black

### Stand

Vertical Stand

### Adapter Cage

None

### Toolless Chassis Screw

None

### Dust Filter

None

### Mounting

None

### Form Factor

Tiny (1L)

### Dimensions (WxDxH)<sup>[3]</sup>

179 x 183 x 34.5 / 37 mm with rubber feet (7.05 x 7.2 x 1.36 / 1.5 inches with rubber feet)

### Weight<sup>[4]</sup>

1.25 kg (2.76 lbs)

## CONNECTIVITY

### Ethernet

Integrated 100/1000M (Realtek RTL8111FP)

### WLAN + Bluetooth®

Intel® Wi-Fi® 6 AX200, 11ax 2x2 + BT5.1

### Front Ports

- 1x USB-C® 3.2 Gen 1 (support data transfer)
- 1x USB 3.2 Gen 2 (Always On and fast charge)
- 1x headphone / microphone combo jack (3.5mm)

### Rear Ports

- 2x USB 2.0
- 2x USB 3.2 Gen 1
- 1x HDMI® 1.4b
- 1x DisplayPort™ 1.4
- 1x Ethernet (RJ-45)

### Optional Rear Ports (configured)

1x DP

### Monitor Cable

None

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0, TCG certified

### Physical Locks

Kensington® Security Slot™, 3 x 7 mm

### Kensington Cable Lock

None

### Chassis Intrusion Switch

Chassis Intrusion Switch

## MANAGEABILITY

### System Management

DASH 1.2

## SERVICE

### Base Warranty

3-year, Onsite

### Included Upgrade

None

## CERTIFICATIONS

### Green Certifications<sup>[5]</sup>

- ENERGY STAR® 8.0
- EPEAT™ Silver Registered
- ErP Lot 3
- TCO Certified 9.0
- RoHS compliant

### Mil-Spec Test

MIL-STD-810H military test passed

## SOFTWARE

### Operating System

Windows® 11 Pro, English

### Bundled Software

None

## MODEL

TopSeller : Yes

Announce Date : 2023-08-15

EAN / UPC / JAN : 197532620186

End of Support : 2027-05-29



AMD

Product image is a sample, it may not match the real color of this model  
Note:

<sup>[1]</sup> The max memory is based on the test results with current Lenovo memory offerings. The system may support more memory as the technology develops.

<sup>[2]</sup> The max capacity of each disk type is based on the test.....  
· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to  
<https://psref.lenovo.com/Detail/1490?M=11JN008WUS>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.


## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkCentre Tiny VESA Mount II

4XFON03161

The ThinkCentre Tiny VESA Mount II is a unique design specific to house the Tiny PC while featuring the universal VESA mount configuration. The VESA standard enables this mount to attach to anything that is VESA comp...

## Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39202)
BETTER	3Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39468)
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WS0U26647)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference