

## PERFORMANCE

### Processor

Intel® Core™ i7-1355U, 10C (2P + 8E) / 12T, P-core 1.7 / 5.0GHz, E-core 1.2 / 3.7GHz, 12MB

### Graphics

Integrated Intel Iris® Xe Graphics

### Chipset

Intel SoC Platform

### Memory

16GB Soldered LPDDR5x-4800

### Memory Slots

Memory soldered to systemboard, no slots, dual-channel

### Max Memory

16GB soldered memory, not upgradable

### Storage

512GB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

### Storage Support<sup>(1)</sup>

One drive, up to 2TB M.2 2280 SSD

### Storage Slot

One M.2 2280 PCIe 4.0 x4 slot

### Card Reader

None

### Optical

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

### Speakers

Stereo speakers, 2W x2, Dolby® Audio™

### Camera

FHD 1080p with Privacy Shutter

### Microphone

2x, 360°

### Battery

Integrated 57Wh

### Power Adapter

65W USB-C® Slim (2-pin)

## DESIGN

### Display<sup>(2)</sup>

14" WUXGA (1920x1200) IPS 300nits Anti-glare, 45% NTSC, Touch

### Touchscreen

On-cell, 10-point Multi-touch

### Keyboard

Backlit, English

### Case Color

Deep Black

### Case Material

Carbon Fiber Hybrid (Top), Aluminium (Bottom)

### Dimensions (WxDxH)<sup>(3)</sup>

317.5 x 226.9 x 16.9 mm (12.5 x 8.93 x 0.67 inches)

### Weight<sup>(4)</sup>

Starting at 1.25 kg (2.76 lbs)

## SOFTWARE

### Operating System

Windows® 11 DG Windows 10 Pro 64, English

### Bundled Software

None

## CONNECTIVITY

### Ethernet<sup>(5)</sup>

No Onboard Ethernet

### WLAN + Bluetooth<sup>(6)(7)</sup>

Intel Wi-Fi® 6E AX211, 11ax 2x2 + BT5.1

### WWAN

None

### SIM Card

None

### NFC

None

### Standard Ports

- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 2x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 2.0)

### Optional Ports (configured)

None

### Docking

Various docking solutions supported via Thunderbolt / USB-C.

For more compatible docking solutions, please visit [Docking for ThinkPad® T14s Gen 4 \(Intel\)](#)

### Monitor Cable

None

## SECURITY & PRIVACY

### Smart Card Reader

None

### Security Chip

Discrete TPM 2.0 Enabled

### Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

### Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

### Other Security

- Camera privacy shutter
- IR camera for Windows® Hello
- Glance by Mirametrix®

## MANAGEABILITY

### System Management

Non-vPro®

## SERVICE

### Base Warranty

3-year, Courier or Carry-in

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications<sup>(8)</sup>

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 9.0

### Mil-Spec Test

MIL-STD-810H military test passed

## MODEL

**TopSeller** : Yes **Announce Date** : 2023-08-22

**EAN / UPC / JAN** : 197532704916 **End of Support** : 2029-11-26

Note:

<sup>(1)</sup> The storage capacity supported is based on the test.....  
· Lenovo reserves the right to change specifications without notice.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to

<https://psref.lenovo.com/Detail/2296?M=21F60099US>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad USB-C Dock Gen 2

40AS0090US

- Lenovo understands that modern business depends on a wide variety of PC's and even brands to meet their business needs. To make this easier Lenovo USB-C dock is compatible with Lenovo notebooks as well as note...

## Recommended Services

BEST	3Y Premier Support Plus upgrade from 3Y Courier/Carry-in (5WS1L39101)
BETTER	3Y Premier Support Upgrade from 3Y Courier/Carry-in (5WS0T36152)
GOOD	3Y Onsite upgrade from 3Y Courier/Carry-in (5WS0A23006)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference