

PERFORMANCE

Display Size
24.5"

View Area
543.7x302.6 mm

Panel
In-Plane Switching

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920x1080

Pixel Pitch
0.283x0.280 mm

Dot / Pixel Per Inch
90 dpi

View Angle (H / V)
178° / 178°

Response Time
0.5ms (MPRT) / 1ms (Level 5) / 2ms (Level 4) / 3ms (Level 3) / 4ms (Level 2) / 5ms (Level 1)

Color Support
16.7 Million

Refresh Rate
165Hz (Overclock to 180Hz)

Brightness
400 cd/m²

Contrast Ratio
1000:1

Color Gamut
99% sRGB, 90% DCI-P3

Screen Surface Treatment
Anti-glare

Curvature
None

Camera
None

Microphone
None

Speakers
3Wx2

Power Consumption (Typical / Maximum)
18.5W / 28W

Power Adapter
Integrated

Touchscreen
None

Smart System
None

DESIGN

Stand
Tilt, Swivel, Pivot, Height Adjust Stand

Case Color
Raven Black

Side Bezel Width
2 mm

Mounting
Supports VESA mount 100mm

ThinkCentre® M Series Support
None

Dimensions (WxDxH)

- Lowest Position | 557.3 x 258.8 x 364.2mm (21.94 x 10.19 x 14.34 inches)
- Highest Position | 557.3 x 258.8 x 499.2mm (21.94 x 10.19 x 19.65 inches)
- Head Only | 557.3 x 50.5 x 329.1 mm (21.94 x 1.99 x 12.96 inches)

Packaging Dimensions (WxDxH)
647 x 188 x 420 mm (25.47 x 7.4 x 16.54 inches)

Weight

- Monitor With Stand | 4.9 kg (10.8 lbs)
- Monitor Head Only | 3.0 kg (6.6 lbs)

Packaging Weight
7.5 kg (16.5 lbs)

CONNECTIVITY

USB Port
None

Video Connector
2x HDMI® 2.1 TMDS, 1x DP 1.4

Network Connectivity
None

SERVICE

Base Warranty
3-year

CERTIFICATIONS

Environmental Certification
RoHS, EU Energy Efficiency Level (Level-E)

Ergonomic Certification
Eyesafe® Display 2.0, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Eye Comfort

Sync Technology
AMD FreeSync™ Premium

Special Features

- DisplayHDR™ 400
- AMD FreeSync™ Premium
AMD FreeSync™ technology only can work with AMD Radeon™ series graphics card.
- Lenovo® Artery (Lenovo® Accessories and Display Manager) Support
Lenovo® Artery supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems).
Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
- Gaming Console Support: Xbox
- Natural Low Blue Light

SOFTWARE

Operating System
Support Windows® 10, Windows® 11

ACCESSORIES

Video Cables
DP Cable

MODEL

Product : Lenovo® R25i-30

EAN
/
/
/
JAN

Announce Date : 2023-07-28

UPC : 0197529455548 / 197529455548 / None



Product image is a sample, it may not match the real color of this model

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Lenovo

PSREF
Product Specifications
Reference