




# PR750RT2UC SMART APP SINEWAVE UPS



Protect corporate and network servers, telecom installations, and Voice Over Internet Protocol (VoIP) systems.

The PR750RT2UC is a Smart App Sinewave rack/tower convertible UPS with line-interactive topology, surge protection, and battery backup. CyberPower's Smart App Sinewave series has sine wave output to eliminate power gaps that can be detected by sensitive equipment and cause unexpected shutdowns.

The Smart App Sinewave PR750RT2UC improves battery life through battery equalization technology and Automatic Voltage Regulation (AVR), which corrects minor power fluctuations without switching to battery power. The enhanced chassis design with an easy-to-access toolless front panel, captive screws for battery panel access, and color-coded rear panel make battery changes and installations simple and fast. The PR750RT2UC also has an innovative LCD panel that rotates 90°, tilts for a better viewing angle, and provides information on 47 different settings including UPS stats, UPS setup and control management, and testing options.

This model accepts the RMCARD205 network management card for remote management and control via a standard web browser or network management system. Includes built-in cloud monitoring.

With a \$400,000 connected equipment guarantee and a three-year warranty, you can trust CyberPower's commitment to the quality of the PR750RT2UC.

## TYPICAL APPLICATIONS

- Department Servers
- Storage Devices
- VoIP Installations
- Network Devices
- Corporate Servers
- Telecom Installations


## FEATURES

- Capacity: 750 VA / 750 W
- Topology: Line Interactive
- Waveform: Sine Wave
- Output: 100-125 VAC +/- 5%
- Runtime (half/full): 19.0 minutes / 7.5 minutes
- Plug type & cord: NEMA 5-15P, 10 ft. cord
- Outlets: 8 surge + battery backup
- Outlet types: 8 x NEMA 5-15R
- Communication: USB, Serial, SNMP, Cloud, Relay, EPO
- Management software: PowerPanel® Business
- Remote management: Yes, with optional RMCARD205. Includes built-in cloud
- Warranty: 3-year
- Connected Equipment Guarantee: \$400,000
- ENERGY STAR® qualified: Yes

## SPECIFICATIONS

GENERAL		INPUT - CONT.	
Active PFC Compatible	Yes	Cord Length	10 ft. (3.0 m)
Energy Saving	GreenPower UPS™ Bypass Technology	Input Frequency Range	47 Hz - 63 Hz
ENERGY STAR® Certified	Yes	Input Plug Type	NEMA 5-15 P
UPS Topology	Line Interactive	Input Voltage	100 - 125 VAC
INPUT		Input Voltage Range	75 - 149 VAC
Adjustable Voltage Range	70 - 155 VAC	Nominal Input Voltage	120 VAC
Circuit Breaker	15 A	Plug Style	Right Angle, 45° Offset

# PR750RT2UC SMART APP SINEWAVE UPS



## SPECIFICATIONS - CONT.

OUTPUT	
Automatic Voltage Regulation	Double Boost, Single Buck
On Battery Frequency	50 Hz - 60 Hz +/- 1%
On Battery Voltage	100/110/120/125 VAC +/- 5%
On Battery Waveform	Sine Wave
Outlet Type	NEMA 5-15 R
Outlets - Battery & Surge Protected	8
Outlets - Critical Load	4
Outlets - Total	8
Output Power Factor	1
Overload Protection	On Battery: Internal Circuitry Limiting On Utility: Circuit Breaker Protected
Typical Transfer Time	4 ms
VA	750 VA
Watts	750 W
BATTERY	
Battery Quantity	4
Battery Size	12 V / 5 Ah
Battery Type	Sealed Lead-Acid
Hot-Swappable	Yes
Replacement Battery Cartridge	1 x RB1250X4
Runtime at Full Load	7.5 min.
Runtime at Half Load	19 min.
Typical Recharge Time	3 Hours
User-Replaceable Battery	Yes

SURGE PROTECTION & FILTERING	
EMI/RFI Filtration	Yes
Surge Suppression	2430 J
MANAGEMENT & COMMUNICATIONS	
Audible Alarms	Battery Mode Low Battery Overload Overcharge Overheat
Emergency Power Off (EPO) Port	Yes
HID Compliant USB Port	Yes
LCD	Multifunction LCD
LED Indicators	Power On Line Mode Battery Mode Fault Wiring Fault
Management Cable	USB Cable Serial Cable EPO Cable
Serial Port	1 Serial 1 Dry Contact
SNMP / HTTP Remote Monitoring	Yes - with optional RMCARD205
Software (Free Download)	PowerPanel® Business
PHYSICAL	
Color	Black
Form Factor	Rack/Tower
Material of Construction	Metal
Rack Height	2U

# PR750RT2UC

## SMART APP SINEWAVE UPS

### SPECIFICATIONS - CONT.

DIMENSIONS	
Dimensions - Width/Height/Depth (cm)	43.43 x 8.64 x 41.15 cm
Dimensions - Width/Height/Depth (mm)	434 x 86 x 411 mm
Dimensions - Width/Height/Depth (in.)	17.1 x 3.4 x 16.2 in
Weight (kg)	19.6 kg
Weight (lbs.)	43.2 lbs.
Country of Origin	China
SHIPPING DIMENSIONS	
Shipping Dimensions - Width/Height/Depth (cm)	52.71 x 26.67 x 55.88 cm
Shipping Dimensions - Width/Height/Depth (mm)	527.05 x 266.7 x 558.8 mm
Shipping Dimensions - Width/Height/Depth (in.)	20.75 x 10.5 x 22 in
Shipping Weight (kg)	23.77 kg
Shipping Weight (lbs.)	52.4 lbs.
ENVIRONMENTAL	
Audible noise at 1m from surface of unit	52.5 dBA
Online Thermal Dissipation	34.5 BTU/hr
Operating Elevation	0 - 9,843 ft (0 - 3,000 m)
Operating Relative Humidity	0 - 95 % (non-condensing)
Operating Temperature	32 - 104 °F (0 - 40 °C)
Storage Elevation	0 - 49,213 ft (0 - 14,999 m)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
CERTIFICATIONS	
Environmental	RoHS Compliant
Safety	UL1778 CSA C22.2 No 107.3 FCC Class B VCCI DOE Compliant
WARRANTY	
CEG Amount	\$400,000
Connected Equipment Guarantee	Lifetime
Extended Warranty Option	WEXT5YR-U4A
Product Warranty	3-Year Limited

