




HP P22va G4 FHD Monitor (453D2AA)

Overview

An everyday, affordable business monitor that's easy on you.

Tackle your daily task list with the budget-friendly HP P22va G4 Monitor that adjusts to your comfort needs and delivers Full HD picture quality.



Crisp image clarity for all your content.

Get lifelike color and sharp details for everything you do on a 21.5" diagonal Full HD screen with 178° x 178° viewing angles.

Make conscientious buying choices.

Choose a monitor that's TCO and ENERGY STAR® certified to help meet your environmental buying requirements.

Modern connectivity.

Conveniently and quickly connect to your devices and additional monitors through the HDMI and VGA ports, no dongles required.

Features

Personalize your comfort settings.

See your screen in a whole new light with HP Low Blue Light for more comfortable viewing, then tilt the screen up to 5° forward or 20° back for your best viewing position.

Personalize and help protect your monitor.

Customize your monitor and help deter its theft with easy, intuitive HP Display Center software that lets you tailor your settings, partition screens, and more through the host PC.^[1]

We have your back.

Rest assured that your IT investment is supported with our three-year standard limited warranty.^[2]

[1] Requires Windows 10 on host PC.

[2] HP Care Packs sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit www.hp.com/go/cpc. HP Services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.

Specifications

Display size (diagonal)	21.5"
Panel technology	VA
Display size (diagonal)	54.6 cm (21.5")
Aspect ratio	16:9 ^[1]
Native resolution	FHD (1920 x 1080) ^[1]
Resolutions supported	1024 x 768; 1280 x 1024; 1280 x 720; 1280 x 800; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 640 x 480; 720 x 400; 800 x 600
Pixel pitch	0.0831 mm x 0.241 mm
Brightness	250 nits ^[1]
Contrast ratio	3000:1 ^[1]
Response time (typical)	7ms GtG (with overdrive) ^[1]
Minimum dimensions (W x D x H)	50.43 x 4.4 x 30.02 cm (Without stand.)
Minimum dimensions (W x D x H)	19.85 x 1.73 x 11.82 in (Without stand.)
Dimensions With Stand (W x D x H)	50.43 x 18.1 x 36.71 cm
Weight	2.84 kg (With stand.)
Weight	6.27 lb (With stand.)
Display features	Anti-glare; Low blue light mode
Onscreen controls	Exit; Information; Management; Menu; Power control; Input control; Brightness+; Image; Color
Display colors	Up to 16.7 million colors supported (through FRC technology)
Display scan frequency (horizontal)	30-80 KHz
Display scan frequency (vertical)	50-60 Hz
Camera	No integrated camera
Power	100 - 240 VAC 50/60 Hz
Power consumption	20 W (maximum), 18.5 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% non-condensing
Certifications and compliances	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CECP; CEL; cTUVus; EAC; ENERGY STAR®; E-standby; EUP Lot-5; EUP Lot-6; FCC; ICES; ISO 9241-307; KC/KCC; NOM; VCCI; Vietnam MEPS; WEEE; Low blue light; EUP Lot-26; California Energy Commission (CEC); South Africa Energy; WW application; UAE; Ukraine certificates; NRCS of South Africa

Ecolabels	EPEAT® Silver
Physical security	Security lock-ready ^[2]
Management Software	HP Display Assistant
UPC number	195908960966
What's in the box	Monitor; HDMI cable; Documentation; AC power cord ^[4,5]

Additional specifications

Additional information about HP in the countries	hp.com
Backlight type	Edge-lit
Bezel	Narrow
Color gamut	72% NTSC
Curvature	Flat
Datasheet photo 1	AHID/5fc8b86f194f269d8421b4fe2b5a0b3eba283d5e
Datasheet photo 3	AHID/5686c574eefdacd8a058dfbc7d7946df333f7125
Datasheet photo 4	AHID/e0dd526d27cf6b10a8ced010667b86384f7ad26
Datasheet photo 5	AHID/6d531bf90e298a684d2a93646d9956e2595daca7
Detachable stand	Yes
Display area (imperial)	188.4 x 102.47 in
Display area (metric)	47.8 x 26 cm
Display contrast ratio (dynamic)	8000000:1
Flicker-free	Yes
HDCP	Yes, HDMI
HDMI	1 HDMI 1.4
Hardness	3H
Height adjustment range	No height adjust
Horizontal viewing angle	178°
Integrated privacy filter	No
Low blue light	Yes
Microphone	No
Operating temperature range	41 to 95°F
Package dimensions (W x D x H)	56.7 x 12 x 38.7 cm
Package dimensions (W x D x H)	22.32 x 4.72 x 15.23 in
Package weight	7.52 lb
Package weight	3.41 kg
Panel bit depth	8 bit (6 bit + 2 FRC)
Pixels per inch (ppi)	105 ppi
Power supply type	External
Product dimensions with stand (W x D x H)	19.85 x 7.13 x 14.45 in
Recommended resolution	FHD (1920 x 1080 @ 60 Hz)

Resolution (maximum)	FHD (1920 x 1080 @ 60 Hz)
Screen treatment	Anti-glare
Speaker type	No
Tilt	-5 to +20°
Touch-enabled	Not touch-enabled
UNSPSC code	43211902
VESA mounting	100 mm x 100 mm
VGA	1 VGA
Vertical viewing angle	178°
pivot	No pivot
swivel	No swivel

[1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[2] Lock sold separately.

[4] Monitors produced until December 2020 are delivered with VGA cable. Monitors produced from December 2020 are delivered with HDMI cable.

[5] China continues shipping with VGA cable, no HDMI cable is included.

Services

HP Care Pack Services

★ : Recommended

Personal Systems Commercial Care Pack Services

HP 4y Next Business Day Response Advanced Exchange Small DisplayHardware Support	U0J10E ★
HP 5y Next Business Day Response Advanced Exchange Small DisplayHardware Support	U0J11E ★
HP 1y Post Warranty Next Business Day Response Advanced Exchange DisplayHardware Support	U0J16PE

Accessories

Security and Protection

★ : Recommended

PC Locks

HP Business PC Security Lock v3 Kit

3XJ17AA

Cabinets and Stands

Monitor Stands

HP Integrated Work Center for Desktop Mini and Thin Client

G1V61AA

Rack Brackets/Bezels/ Panels/Rails/ Trays/Mounting

Mounting Kits

HP Quick Release Bracket 2

6KD15AA

Disclaimer — Copyright

ENERGY STAR® is a registered trademark of the U.S. Environmental Protection Agency.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (us-en) – Oct 20, 2023 4:22 PM UTC+0000