



UX10 FULLY RUGGED TABLET

- 10th Generation Intel® Core™ i7/i5 Processor
- 10.1" FHD LumiBond® 2.0 Display with Getac Sunlight Readable Technology (1,000 nits) and Capacitive Touchscreen
- Enhanced Enterprise Security with Optional Intel vPro™, Windows Hello Face-authentication Camera and Multi-factor Authentication Options
- Detachable Keyboard and Multifunctional Hard Handle for On-the-job Flexibility
- Multiple Configurable Options to Fit Diverse Usage Scenarios



Detachable Keyboard



Hard Handle



Specifications

Operating System

Windows 10 Pro

Mobile Computing Platform

Platform Options:

Intel® Core™ i7 Technology
 Intel® Core™ i7-10510U Processor 1.80 GHz
 8MB Intel® Smart Cache
 Intel® Core™ i7 vPro™ Technology
 Intel® Core™ i7-10610U Processor 1.80 GHz vPro
 8MB Intel® Smart Cache
 Intel® Core™ i5 Technology
 Intel® Core™ i5-10210U Processor 1.60 GHz
 6 MB Smart Cache
 Intel® Core™ i5 vPro™ Technology
 Intel® Core™ i5-10310U Processor 1.70 GHz vPro
 6MB Intel® Smart Cache

VGA Controller

Intel® UHD Graphics

Display

10.1" IPS TFT LCD FHD (1920 x 1200)
 1000 nits LumiBond® display with Getac sunlight readable technology
 Capacitive multi-touch screen

Storage & Memory

8GB DDR4
 Optional: 16GB / 32GB DDR4
 256GB PCIe NVMe SSD
 Optional: 512GB / 1TB PCIe NVMe SSD

Keyboard

6 tablet buttons (Windows, Power, Function Key, Camera Capture/ Barcode Reader Trigger, Volume Up, Volume Down)

Pointing Device

Touchscreen
 - Capacitive multi-touch screen
 - Optional: Dual mode touchscreen (multi-touch and digitizer)

Expansion Slot

- Optional (top side): 1D/2D imager barcode reader, or serial port, or MicroSD slot, or USB 3.0 Type-A port, or USB 3.1 Gen 1 Type-C port, or LAN port (RJ-45), or VGA port, or HF RFID reader.
 - Optional (right side): fingerprint reader, or serial port+LAN port (RJ-45), or HF RFID reader^{iv}.
 - Optional (back side): smart card reader, or bridge battery, or bridge battery+smart card reader^v

I/O Interface

FHD webcam x 1 or Optional Windows Hello face-authentication camera (front-facing) x 1
 8M pixels auto focus rear camera x 1
 Headphone out / mic-in combo x 1
 DC in Jack x 1
 USB 3.1 Gen 2 Type-A x 1
 HDMI x 1
 Docking connector x 1
 Optional: RF antenna pass-through for GPS, WLAN and WWAN

Communication Interface

Optional: 10/100/1000 base-T Ethernet
 Intel® Wi-Fi 6 AX200, 802.11ax
 Bluetooth (v5.1)ⁱⁱ
 Optional: Dedicated GPSⁱⁱⁱ
 Optional: 4G LTE mobile broadband with integrated GPSⁱⁱⁱ

Security Feature

Optional: Intel® vPro™ Technology
 TPM 2.0
 Optional: HF RFID readerⁱⁱ
 Optional: Fingerprint scanner^{iv}
 Optional: smart card reader^v
 Kensington lock

Power

AC adapter (65W, 100-240VAC, 50 / 60Hz)
 Li-Ion smart battery (11.1V, typical 4200mAh; min.4080mAh) x 1
 Optional: High capacity battery (10.8V, 9240mAh) x 1
 Optional: Bridge battery^v

Dimension (W x D x H) & Weight

276.8 x 194.5 x 23.5 mm (10.89" x 7.65" x 0.92"),
 1.22 kg (2.68 lbs)^{vi}

Rugged Feature

MIL-STD-810H certified and IP65 certified
 MIL-STD-461G certified^{viii}
 Optional: ANSUL 121201, CSA C22.2 NO. 213
 Optional: Salt fog certified
 6 feet drop resistant^{ix,x}
 e-Mark certified for vehicle usage

Environmental Specification

Temperature:
 - Operating: -29°C to 63°C / -20°F to 145°F
 - Storage: -51°C to 71°C / -60°F to 160°F
 Humidity:
 - 95% RH, non-condensing

Software

Getac Utility
 Getac Camera
 Getac Geolocation
 Getac Barcode Manager
 Optional Absolute Persistence

Accessories

Carry bag
 Multi-bay charger (Dual Bay)
 Multi-Bay charger (Eight-Bay)
 Vehicle adapter (120W, 11-32VDC)
 AC adapter (65W, 100-240VAC)
 Office dock AC adapter (90W, 100-240VAC)
 MIL-STD-461 certified AC adapter (90W, 100-240VAC)
 Digitizer pen
 Capacitive stylus (Hard-tip)
 Protection film
 Tablet folio case
 Hand strap
 Shoulder harness (4-point; handsfree)
 Shoulder strap (2-point)
 Standard battery (11.1V, typical 4200mAh; min. 4080mAh)
 High capacity battery (10.8V, 9240 mAh)
 Detachable keyboard
 Vehicle dock
 Office dock

Bumper-to-Bumper warranty

Accidents can take your equipment out of service when you least expect it, especially in a rugged environment, which can cause costly equipment downtime.

That is why Getac has introduced accidental damage as standard under our Bumper-to-Bumper warranty, to help minimize your enterprise IT costs.

Bumper-to-Bumper is your hassle-free guarantee. That means you can depend on us to have your unit back in service within days.

Standard

3 years Bumper-to-Bumper

- i 13.56MHz Contactless HF RFID reader (ISO 15693, 14443 A/B, Mifare and FelicA™ compliant).
- ii 1D/2D imager barcode reader, HF RFID reader, serial port, LAN port (RJ45), USB 3.0 port, USB 3.1 Gen 1 Type-C port, MicroSD slot and VGA port are mutually exclusive options.
- iii Supports GPS and Glonass.
- iv Fingerprint scanner, HF RFID reader and serial port+LAN port (RJ45) are mutually exclusive options.
- v Smart card reader, bridge battery and bridge battery+smart card reader are mutually exclusive options.
- vi Bluetooth performance and connectable distance may be subject to interference with the environments and performance on client devices, users may be able to reduce effects of interference by minimizing the number of active Bluetooth wireless devices that is operating in the area.
- vii Weight and dimensions vary from configurations and optional accessories.
- viii MIL-STD-461G 90W AC adapter sold separately.
- ix Drop test results vary from configurations and optional accessories.
- x Tested by a national independent third party test lab following MIL-STD-810H.

UX10

Fully Rugged Tablet



Docking Solutions

	Vehicle Dock	Office Dock
Serial Port	1	1
VGA	--	1
Microphone	--	1
Audio Output	--	1
DC in Jack	1	1
USB	USB 3.0 x2 USB 2.0 x2	USB 3.0 x2 USB 2.0 x2
LAN	1	1
HDMI	--	1
RF Antenna Connector	3 (WWAN, WLAN, GPS)	--
Kensington Lock	1	1

Getac

GETAC TECHNOLOGY CORPORATION

5F, Building A, No. 209, Section 1, Nangang Rd.,
 Nangang Dist., Taipei City, 11568, Taiwan, R.O.C.
 Tel : +886 2 2785 7888
 globalmarketing@getac.com | www.getac.com



Copyright © 2020 Getac Technology Corporation and/or any of its affiliates. All Rights Reserved.
 Information provided herewith is for reference only,
 available specification shall be subjected to quotation by request. V01M08Y20WWW