

# Lenovo K14 Gen 2

Delivering exceptional performance for the on-the-go professional, the laptop, powered by up to 13th Gen Intel U Series Core i7 processor, enables swift decision-making and multitasking. Its Intel UHD or Intel Iris Xe Graphics ensures presentations make an impact, while the up to 12.83 hours of battery life keeps professionals productive during long business trips without worrying about finding a place to recharge. Moreover, with optional Wi-Fi 6E, stay connected seamlessly for video conferences and client interactions.



Discrete TPM 2.0 chipset encrypts data on the laptop's storage drive, enhancing the security of sensitive files and preventing unauthorized access. Additionally, dual USB-C 3.2 Gen 2 ports quickly transfer large files such as videos, images, and backups.

Experience crystal clear visuals on the 16:9 anti-glare screen featuring up to 2.2k resolution and up to 300nits of brightness, perfect for business presentations and client meetings.

Battery life of up to 12.93 hour reduces the reliance on power adapters, making the laptop setup simpler and more portable. This is especially advantageous when working in cramped spaces or on-the-go.

## Lenovo devices that are a class apart

Lenovo 14 Series ultraportables are ideal for buyers seeking lightweight full-size notebooks on a budget.

## Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

## Accessories

### Lenovo USB-C Travel Hub

This mini hub connects to your PC through a single USB-C cable

Connect to an external display (up to 4K via DisplayPort or FHD via VGA), wired network (ethernet), and any USB3.0 device (1x USB3.0)  
Travel-friendly compact design (63x68mm) and weighing just 80g (0.18lbs)



PN: 4X90M60789

### Lenovo Pro Stereo Wired VOIP Headset

USB or 3.5mm analog connection with integrated call controls  
Skype for Business and Microsoft Teams certified  
HD noise-cancelling microphone



PN: 4XD0S92991



# Lenovo K14 Gen 2

## Performance

### Processor

13th Gen Intel U Series Core i3/i5/i7

### Operating System

Windows 11 Pro  
Windows 11 Home  
Windows 11 Home Single Language

### Graphics<sup>1</sup>

Intel UHD Graphics (Integrated)  
Intel Iris Xe Graphics eligible (Integrated)

<sup>1</sup>Intel Iris Xe Graphics capability requires system to be configured with dual-channel memory. On the system with single-channel memory, Intel Iris Xe Graphics will function as Intel UHD Graphics.

### Memory<sup>2</sup>

Up to 64GB DDR5-5200 offering, 2x SO-DIMM

<sup>2</sup>Maximum memory is only to test technical readiness of notebook. Available memory to sell would vary.

### Storage<sup>3</sup>

Up to two M.2 PCIe NVMe SSD  
M.2 2280 SSD up to 2TB

<sup>3</sup>The system supports dual SSD via two M.2 slots, but Lenovo only offers one SSD configuration, another SSD slot for user self-extension. The max storage capacity is only technical readiness and may be different with current Lenovo storage offerings.

### Audio

High Definition (HD) Audio  
Stereo speakers, 2W x2, Dolby Audio  
Dual-microphone array with smart noise-cancelling

### Camera

HD 720p, with privacy shutter  
FHD 1080p, with privacy shutter  
FHD 1080p + IR hybrid, with privacy shutter

### Battery<sup>4</sup>

45Wh (up to 8.75 hr) battery, Rapid Charge Pro  
60Wh (up to 12 hr) battery, Rapid Charge

<sup>4</sup>Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

### Power Adapter

65W USB-C adapter, PD 3.0  
65W USB-C slim adapter, PD 3.0

## Design

### Display<sup>5</sup>

14" WUXGA (1920x1200) IPS Anti-glare 16:10  
- 300nits, 45% NTSC, 60Hz

14" 2.2K (2240x1400) IPS Anti-glare 16:10  
- 300nits, 100% sRGB, 60Hz

<sup>5</sup>IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

### Keyboard

6-row, spill-resistant, optional backlight

### Touchpad

Mylar surface touchpad  
75 x 120 mm (2.95 x 4.72 inches)

### Dimensions<sup>6</sup>

313.5 x 224 x 18.9 mm (12.34 x 8.82 x 0.74 inches)

<sup>6</sup>The system dimensions may vary depending on configurations.

### Weight<sup>7</sup>

Starting at 1.38 kg (3.04 lbs)

<sup>7</sup>The system weight is approximate and may vary depending on configurations

### Color

Onyx grey

### Case material

PC + ABS (top)  
PC + ABS (bottom)

## Connectivity

### Ethernet

Gigabit onboard Ethernet

### WLAN + Bluetooth<sup>8</sup>

802.11ax (Wi-Fi 6 or Wi-Fi 6E), Bluetooth 5.1  
Up to Intel Wi-Fi 6E AX211, 802.11ax, Bluetooth 5.1

<sup>8</sup>Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitations.

### Ports

1x USB 3.2 Gen 1  
1x USB 3.2 Gen 1 (Always On)  
2x USB-C 3.2 Gen 2 (data, PD 3.0, DP 1.4)  
1x HDMI 2.1, up to 4K/60Hz  
1x Card reader  
1x Ethernet (RJ-45)  
1x Headphone / microphone combo jack (3.5mm)

### Docking

Supports USB-C docking

## Security & Privacy

Discrete TPM 2.0  
Kensington Nano Security Slot  
Touch style fingerprint reader on smart power button\*  
Camera privacy shutter  
IR camera for Windows Hello\*

## Certifications

### Green Certifications<sup>9 10</sup>

EPEAT Gold Registered\*  
ENERGY STAR 8.0\*  
ErP Lot 6  
ErP Lot 26  
TCO Certified 9.0  
RoHS compliant

<sup>9</sup>The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

<sup>10</sup>EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.

### Other Certifications

TÜV Rheinland Low Blue Light (Hardware Solution)\*  
TÜV Rheinland Low Blue Light (Software Solution)\*  
MIL-STD-810H