


ThinkPad P14s *i* Gen 2

POWER THAT MOVES



LENOVO'S LIGHTEST MOBILE WORKSTATION

The ThinkPad P14s *i*, Lenovo's most mobile workstation, strikes the balance between power and mobility, all within a compact 14-inch chassis. Perfect for highly mobile power users, the P14s *i* is designed with ultimate portability and performance in mind, featuring the latest Intel Core processors, NVIDIA professional graphics, and integrated X-Rite factory color calibration for outstanding out-of-the-box color accuracy.

Built with an advanced suite of ThinkShield security features and comprehensive MIL-STD testing for ultimate durability, the P14s *i* has you protected from every angle - allowing students, engineers, and designers the freedom to innovate anytime, anywhere.

FEATURES



Up to 11th Gen Intel® Core™ i5 or i7 Processor



Multiple 14" screen options including HDR400 UHD with X-Rite Factory Color Calibration



NVIDIA Discrete Graphics with 4GB VRAM



Up to 48GB 3200MHz Memory




Up to 2TB PCIe NVMe Storage



Dual Thunderbolt™ 4

Lenovo

Lenovo Options & Accessories*



ThinkVision P27h-20



ThinkPad Universal
Thunderbolt™ 4 Dock



ThinkPad 14-inch
Professional Slim Topload



Lenovo ThinkPad P14s / Gen 2 Specifications^

PERFORMANCE

Processor

Up to 11th Gen Intel® Core™ i7 Processor
(up to 4 cores; up to 4.8GHz)

Operating System

Windows 11 Pro
Windows 11 Home
Windows 10 Pro (preinstalled through
downgrade rights in Windows 11 Pro)
Ubuntu® Linux® 20.04 LTS
Red Hat® Linux® (certified)

Graphics

Discrete: NVIDIA® T500, 4GB VRAM
Processor Integrated: Intel Iris Xe¹

Camera

HD 720p with ThinkPad Webcam
Privacy Shutter
Hybrid IR² Camera with ThinkPad
Webcam Privacy Shutter

Total Memory

Up to 48GB DDR4 3200MHz

Memory DIMM Capacity

8GB / 16GB (SDRAM/SoDIMM);
32GB (SoDIMM only)
1 Soldered Down / 1 SoDIMM Slot

Total Storage

Up to 2TB NVMe SSD

Battery

50Whr

Power Supply

65W AC Adaptor Type-C

CONNECTIVITY

Ports

(2) USB-A 3.2 Gen 1**¹, 1 Always On
(2) Intel Thunderbolt 4
(1) HDMI 2.0
(1) RJ45 Gigabit Ethernet
(1) Side Docking Connector
(1) Mic/Headphone Combo Jack
(1) Smart Card Reader²

WLAN

Intel Wi-Fi 6E (6GHz) AX210 2x2 +
Bluetooth™ 5.1³ or

Intel Wi-Fi 6 AX201 2x2ax +
Bluetooth 5.0

WWAN

Quectel CAT16 with embedded eSIM
Quectel CAT12 with embedded eSIM

Media Card Reader

MicroSD Card Reader

Near Field Communication (NFC)²

ThinkShield

dTPM 2.0
Touch Fingerprint Reader
ThinkPad Webcam Privacy Shutter
Privacy Guard Display

SOFTWARE

Windows 10 Preloads

Lenovo Commercial Vantage

ISV CERTIFICATIONS

3DEXPERIENCE®, ANSYS®, ArcGIS®,
AutoCAD®, Creo®, MicroStation®, NX™,
Revit®, Solid Edge®, SOLIDWORKS®.

For a complete list of ISV certifications visit
<https://www.thinkworkstations.com/isv-certifications/>

DESIGN

Display

14" Display
4K UHD (3840 x 2160) IPS
- 500nit, HDR400, Dolby Vision HDR,
X-Rite Factory Color Calibration (FCC)
FHD (1920 x 1080) IPS
- ePrivacy 500nit, 72% NTSC
- Low Power 400nit, 72% NTSC
- On-cell Touch 300nit, 45% NTSC
- 300nit, 45% NTSC

Keyboard

ThinkPad Backlit

Color Options

Black
Storm Grey

Dimensions (WxDxH)

(mm): 329 x 227 x 17.9
(inches): 12.95 x 8.94 x 0.70

Weight

Starting at 3.24lbs (1.47kg)

Green Certifications

EPEAT®
ENERGY STAR® 8.0
RoHS Compliant

Additional Features

Modern Standby
Wake on Voice⁴

* For a full list of accessories and options, please visit:
<https://accsmartfind.lenovo.com>

1 Dual RAM channel required

2 Optional

3 6GHz channel of Wi-Fi 6E is only available with Windows 11

4 Lid must be open

** USB port transfer speeds are approximate and depend on many factors,
such as processing capability of host/peripheral devices, file attributes,
system configuration and operating environments; actual speeds will vary
and may be less than expected.

^ For a full list of configuration details please visit: <https://psref.lenovo.com>

RECOMMENDED SERVICES

Lenovo offers a comprehensive portfolio of services to support and protect your ThinkPad investment—so you can focus on your business, not your IT.

Premier Support

Bypass phone menus and scripted troubleshooting to access advanced-level technicians with the expertise needed to quickly diagnose and solve problems.

Warranty Upgrades—Onsite and Next Business Day

Maximizes PC uptime and productivity by providing convenient, fast repair service the next business day.

Warranty Extensions (1 to 5 years total duration)

This fixed-term, fixed-cost service helps you accurately budget for PC expenses, protect your valuable investment, and potentially lower the cost of ownership over time.

©2021 Lenovo. All rights reserved. These products are available while supplies last. Lenovo is not responsible for photographic or typographic errors.
Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, ThinkPad, Lenovo Commercial Vantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft and Windows are registered trademarks of Microsoft Corporation. Intel, Xeon, Core, Thunderbolt, and Intel vPro are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries. Bluetooth is a trademark of its proprietor and used by Lenovo under license. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. The NVIDIA logo and RTX are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. Linux is the registered trademark of Linus Torvalds in the U.S. and other countries. USB Type-C and USB-C are trademarks of USB Implementers Forum. Other company, product, and service names may be trademarks or service marks of others.

