

Datasheet

FUJITSU Image Scanner fi-7240

The essential fi Series scanner with exceptional business performance



The fi-7240 scans A4 portraits at 40 ppm/80 ipm (200/300 dpi), loads up to 100 sheets at a time, and ensures utmost efficiency with amazing scanning performance.

Assistance for safe and reliable scanning

The fi-7240 possesses diverse stable paper feeding mechanisms, ensuring speedy and high quality scanning without relying on PC performance. Minimize risk of document damage with Paper Protection function monitoring paper feed distance. And bid farewell to missing edges with the scanner's Skew Reducer mechanism. Potential information loss, resulting from multiple sheets being fed through the scanner at once, is also no longer an issue with Ultrasonic Multi-feed detection.

Boosted usability with a user-friendly and versatile design

Equipped with a built-in flatbed, this scanner can scan fragile documents and thick books, impossible to scan with ADF. Scan a wide variety of paper (27 to 413 g/m²), as well as plastic cards, utilizing its straight paper feeding path, with a single push of a button. Daily maintenance tasks, including interior cleaning and roller replacement, can also be done with ease for long-lasting utilization.

High quality images in any condition

Enjoy sharp, high quality images with the fi-7240's CCD image sensors. Subtle changes in scanning environment, such as in air temperature and LED illumination, are also no longer a need for concern with the scanner automatically changing background colors to maintain consistently crisp images.

Advanced software for enhanced efficiency

The PaperStream IP scanner driver, supporting both TWAIN and ISIS, enables you to bypass the inconvenience of making fine image processing adjustments each time you scan. The driver automatically cleans scanned images, facilitating OCR accuracy even when scanning documents with background patterns or wrinkled and soiled documents. Seamlessly linked to PaperStream IP, PaperStream Capture offers various batch scanning capture features to effectively and efficiently feed information into your organization workflow. Automatically utilizing data extracted from barcodes and patch codes, the software determines your preferred saving destinations and eliminates time allocated to routine tasks.

Technical Information

Scanner Type	ADF (Automatic Document Feeder) / Flatbed, Duplex	
Scanning Speed* ¹ (A4 Portrait) (Color* ² /Grayscale* ² /Monochrome* ³)	ADF	Simplex: 40 ppm (200/300 dpi) Duplex: 80 ipm (200/300 dpi)
	Flatbed	1.7 seconds (200 dpi)
Image Sensor Type	Color CCD x 3 (front x 1, back x 1, Flatbed x 1)	
Light Source	White LED Array x 3 (front x 1, back x 1, Flatbed x 1)	
Optical Resolution	600 dpi	
Output Resolution* ⁴ (Color / Grayscale / Monochrome)	50 to 600 dpi (adjustable by 1 dpi increments), 1,200 dpi (driver)* ⁵	
Bit Depth	48 Bit (Internal), 24 Bit (External)	
Background Colors	ADF: White / Black (selectable) Flatbed: White (or optional black)	
Document Size		
ADF	Maximum* ⁶	216 x 355.6 mm (8.5 x 14 in.)
	Minimum* ⁷	50.8 x 54 mm (2 x 2.1 in.)
	Long Page Scanning* ⁸	5,588 mm (220 in.)
Flatbed	Maximum	216 x 297 mm (8.5 x 11.7 in.)
Paper Weight (Thickness)* ⁹		
Paper		27 to 413 g/m ² (7.2 to 110 lb)* ¹⁰
Plastic Card		1.4 mm (0.055 in.) or less (ADF)* ¹¹
ADF Capacity* ¹² * ¹³		100 sheets (A4 64 g/m ²)
Typical Daily Duty Cycle* ¹⁴		6,000 sheets
Multifeed Detection	Overlap detection (Ultrasonic sensor), Length detection	
Paper Protection	Lag detection	
Interface	USB 2.0 / USB 1.1	
Power Requirements	AC 100 to 240 V ±10 %	
Power Consumption		
Operating Mode	39 W or less	
Sleep Mode	1.8 W or less	
Auto Standby (Off) Mode	0.35 W or less	

In order to avail extended warranty or AMC, please write to fipl-imaging@ts.fujitsu.com.

*¹ Actual scanning speeds are affected by data transmission and software processing times. *² Indicated speeds are from using JPEG compression. *³ Indicated speeds are from using TIFF CCITT Group 4 compression. *⁴ Selectable maximum density may vary depending on the length of the scanned document. *⁵ Some limitations may apply to the size of documents that can be scanned, depending on system environment, when scanning at high resolution (over 600 dpi). *⁶ Scans folded documents of up to 297 x 432 mm (11.7 x 17 in.) with carrier sheet scanning. *⁷ Scanning area limitations only apply when using the ADF. There are no limitations when using the flatbed. *⁸ Capable of scanning documents longer than A4 (210 x 297 mm / 8.3 x 11.7 in.) sizes. When using PaperStream IP (TWAIN/ISIS) to scan at 200 dpi, the maximum scanning length is 5,588 mm (220 in.). *⁹ Paper weight limitations only apply when using the ADF. There are no limitations when using the flatbed. *¹⁰ Thicknesses of up to 127 to 209 g/m² (34 to 56 lb) can be scanned for A8 (52 x 74 mm / 2.1 x 2.9 in.) sizes. *¹¹ Capable of scanning up to 3 cards at a time (Note: does not set more than one embossed card at a time). *¹² Maximum capacity depends on paper weight and may vary. *¹³ Capable of setting additional documents while scanning. *¹⁴ This duty cycle is applicable in India and will be supported by Fujitsu India *¹⁵ Excludes the ADF paper chute and stacker. *¹⁶ Availability of support may vary depending on region. Some functions may not be available with the Image Scanner Driver for Linux. *¹⁷ Functions equivalent to those offered by PaperStream IP may not be available with the WIA Driver. *¹⁸ Software can be downloaded from the website designated in the Setup DVD-ROM.

Trademarks

ABBYY™ FineReader™ Engine © ABBYY. OCR by ABBYY. ABBYY and FineReader are trademarks of ABBYY Software, Ltd. which may be registered in some jurisdictions. ISIS is a trademark of Open Text. Microsoft, Windows, and Windows Server are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Linux is the registered trademark of Linus Torvalds in the U.S. and other countries. Any other products or company names appearing in this document are the trademarks or registered trademarks of the respective companies.

Safety Precautions

Be sure to carefully read all safety precautions prior to using this product and use this device as instructed. Do not place this device in wet, moist, steamy, dusty or oily areas. Using this product under such conditions may result in electrical shock, fire or damage to this product. Be sure to limit the use of this product to listed power ratings.

ENERGY STAR®

PFU Limited, a Fujitsu company, has determined that this product meets the ENERGY STAR® guidelines for energy efficiency. ENERGY STAR® is a registered trademark of the United States.

Specifications are subject to change without notice.

Contact

- fipl-imaging@ts.fujitsu.com
- 00080 0100 8917

Operating Environment	
Temperature	5 to 35 °C (41 to 95 °F)
Relative Humidity	20 to 80% (non-condensing)
Environmental Compliance	ENERGY STAR®, RoHS
Dimensions* ¹⁵ (Width x Depth x Height)	300 x 577 x 234 mm (11.8 x 22.7 x 9.2 in.)
Weight	8.8 kg (19.4 lb)
Supported Operating System	Windows® 10 (32-bit/64-bit), Windows® 8.1 (32-bit/64-bit), Windows® 7 (32-bit/64-bit), Windows Server® 2016 (64-bit), Windows Server® 2012 R2 (64-bit), Windows Server® 2012 (64-bit), Windows Server® 2008 R2 (64-bit), Windows Server® 2008 (32-bit/64-bit), Linux Ubuntu* ¹⁶
Included Software / Drivers	PaperStream IP Driver (TWAIN/TWAIN x64/ISIS), WIA Driver* ¹⁷ , PaperStream Capture, ScanSnap Manager for fi Series* ¹⁸ , Software Operation Panel, Error Recovery Guide, ABBYY FineReader for ScanSnap™* ¹⁸ , Scanner Central Admin
Image Processing Functions	Multi image output, Automatic color detection, Blank page detection, Dynamic threshold (iDTC), Advanced DTC, SDTC, Error diffusion, Dither, De-Screen, Emphasis, Dropout color (None/Red/Green/Blue/White/Saturation/Custom), sRGB output, Hole punch removal, Index tab cropping, Split image, De-Skew, Edge filler, Vertical streaks reduction, Cropping, Static threshold, Moire removal
Included Items	ADF paper chute, AC cable, AC adapter, USB cable, Setup DVD-ROM

Options

Black Document Pad (FI-728BK)	PA03670-D801	Black flatbed background pad
Carrier Sheets	PA03360-0013	Each package contains 5 carrier sheets

Consumables

Brake Roller	PA03670-0001	Every 200,000 sheets or one year
Pick Roller	PA03670-0002	Every 200,000 sheets or one year