



Models may vary from the image shown

The CHERRY MX 2.0S – the functional, classic keyboard that has everything you need for gaming. The streamlined German design concentrates on functionality, using the Bauhaus principle as its basis. Designed by Prof. Peter Raab, lecturer at Coburg University, the exterior and interior have been optimized.

The interior features the time-tested mechanical CHERRY MX technology and provides a choice of four switching characteristics. Special Gold Crosspoint contacts ensure consistently reliable electrical contacts, perfect responsiveness, and an unbeatable reaction speed. Multiple mechanical components under each key ensure a uniform feel.

Depending on the model, without lighting or with vivid RGB lighting effects in more than 16 million colors. A variety of plays of color, lighting modes and key assignments can be managed using the free CHERRY Utility software.

A matching palm rest is available as an optional accessory to provide more comfort. High-quality workmanship and abrasion-resistant key caps provide unfailing reliability when gaming, at home, and at work.

FUNCTION AND PERFORMANCE

- Classic, wired keyboard with original CHERRY MX switches
- Impressive RGB lighting in more than 16 million colors, with numerous integrated color routines, which can also be adjusted using the CHERRY Utility Software (depending on the version)
- CHERRY MX technology – Gold Crosspoint precision switches for all keys »Made in Germany«
- Minimalist, functional design – designed in Germany by Prof. Peter Raab
- Uniform feel across all keys due to special, multiple mechanical components
- Full n-key rollover – all keys are read simultaneously
- Anti-ghosting – no input errors
- WIN key lockout
- CHERRY key for quick access to Utility software
- Abrasion-resistant, laser-etched key caps
- Available in four different MX switch characteristics: black, red, brown, blue
- Matching palm rest available as an optional accessory
-

TECHNICAL DATA

Weight main product:	785 g
Dimensions product without packaging:	428 mm x 145 mm x 40 mm
Weight of product incl. packaging (g):	1.188 g
Cable length:	180 cm
Storage temperature:	-20 °C - 60 °C
Working temperature:	0 °C - 50 °C
Produktzulassungen:	• CE • KCC • Windows Hardware Compatibility • BSMI • EU RoHS

System Requirements-

Hardware:	USB-A
Operating system:	• Windows 10 or higher • Windows 7
Scope of delivery:	• Short Manual • Keyboard
Software support:	CHERRY Utility Software & Assistant
Service life per key (in million strokes):	100 mio. actuations
Max. current consumption (mA) of keyboard:	500 mA
Keyboard format:	Full-size (100%)
Integrated metal plate:	no
N-key rollover:	Full-Key-Rollover
Anti-ghosting:	yes
Key encryption:	no
Internal memory:	no
Tastenknopf Beschriftung:	Laser etching + UV coating

Palm rest:	Palm rest available as accessory
USB hub:	no
Special key functions:	• Browser • CHERRY Key • FN • Next track • Last track • Play/Pause • Unmute/Mute • Volume up • Volume down • Calculator
Adjustable feet:	integrated
Status LEDs:	in keys
Keycap material:	ABS
Sealing:	no

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.