

## QSFP-DD Transceiver - 400GBase-SR8, MPO/APC MMF, 400 Gbps, 850 nm, 100 m (328 ft.)

MODEL NUMBER: **N286-400G-SR8-G**



Connects a multimode Gigabit Ethernet fiber optic network cable to a router, switch or server's QSFP-DD port.

### Features

#### QSFP-DD Transceiver for Connecting to Your Network Switch or Server

This QSFP-DD transceiver allows you to connect a multimode fiber optic cable to a 400 Gbps network router, server or switch. It transmits data up to 100 meters (328 feet) using an 850 nm wavelength. The zinc housing protects against electromagnetic interference (EMI) and excessive power dissipation.

#### Functionally Equivalent to a Wide Range of 400GBASE-SR8 Transceiver Modules

The MSA-compliant N286-400G-SR8-G functions just like equivalent 400GBASE-SR8 transceiver modules and is manufactured to meet or exceed those specifications. You can use this transceiver with any compatible router, server or switch and receive the same performance as the 400GBASE-SR8.

#### Hot-Swappable for Installation Without Network Interruption

This input/output device is fully hot-swappable, so you can install it without a potentially costly 400 Gbps network shutdown or device reboot. Just plug the QSFP-DD end of the transceiver into your network device. The other end has an MPO/APC connector to link with multimode fiber optic cable (sold separately). A push/pull tab connector is easily accessible in high-density data center applications and makes the plug-and-play transceiver easy to install and remove with one hand.

#### Supports Digital Diagnostic Monitoring (DDM) for Real-Time Status Monitoring

DDM support lets you keep track of operating information in real time, such as transceiver temperature, input and output power and supply voltage.

## Specifications

OVERVIEW	
UPC Code	037332284112
Brand Compatibility	Cisco

### Highlights

- QSFP-DD transceiver module 100% compatible with 400GBase-SR8 modules
- Provides 400 Gbps throughput up to 100 m via multimode fiber cabling
- 16-strand MPO/APC connector supports 400GBase-SR8 signal at 850 nm wavelength
- Hot-swappable interface lets you install and uninstall without shutting down
- Supports DDM for monitoring temperature and other real-time operating parameters

### Package Includes

N286-400G-SR8-G QSFP-DD Transceiver

Technology	Fiber; Multimode
Optical Mode	OM4
Mode Type	Multimode
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	0.70 x 3.10 x 5.70
Shipping Weight (lbs.)	0.11
Unit Dimensions (hwd / in.)	0.700 x 3.100 x 5.700
Unit Weight (lbs.)	0.1102
Unit Weight (kg)	0.05
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	-40° to 185°F (-40° to 85°C)
Relative Humidity	5% to 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Maximum Data Rate	400 Gbps
Network Compatibility	400 Gbps
Wavelength	840nm; 850nm; 860nm
Transmission Distance	100 m
<b>CONNECTIONS</b>	
Side A - Connector 1	QSFP-DD
Side B - Connector 1	16-STRAND MTP/MPO (FEMALE)
Connector Material	Zinc Alloy
<b>FEATURES &amp; SPECIFICATIONS</b>	
Data Transfer Rate	400 Gbps
Multi-Source Agreement (MSA) Compliant	Yes
Driver Required	No
Optical Port	MPO/MTP
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	EN 55032; IEC/EN 63000
Product Compliance	RoHS; CE (Europe); FCC Part 15 Class B (USA); UKCA

**TRIPP-LITE**

by **EATON**

1000 Eaton Boulevard

Cleveland, OH 44122

United States

**WARRANTY & SUPPORT**

Product Warranty Period  
(Worldwide)

3-year limited warranty

**TRIPP-LITE**

by **EATON**

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.