

32" Desktop, Open Frame or Wall Mountable, Touch or Non Touch Display with BrightSign Built-In

MBS-32080-OF - Non-Touch

MBS-32080C-OF - Capacitive Touch



Product Specs

Display Size

32 inch

Resolution

1920 x 1080

Brightness

300cd/m2

Contrast Ratio

1200:1

Connections

Micro-SD, USB, GPIO (x6), 3.5mm Audio, Ethernet

Viewing Angle

89/89/89/89

Operating Temperature

0 to 50c

Power Consumption

40W

Mount Pattern

VESA-200mm or Side Mount Brackets

Regulatory Certifications

FCC, CE, ROHS

32" Display with BrightSign Built-In

Two trusted powerhouse digital signage leaders, Mimo Monitors and BrightSign, have teamed up to bring you the Mimo Display with BrightSign Built-In. Bringing to market a fully encompassing, reliable, all-in-one digital signage solution, this partnership leverages the power of the Mimo technology and integrates the industry-leading BrightSign platform. The result is a high quality, easy-to-install solution that's immediately digital signage ready, making it extremely simple to use, especially for those already reliant on the BrightSign platform. The Mimo Display with BrightSign Built-In features a modern zero bezel design and a bright, high contrast, IPS screen.

The BrightSign Digital Signage Media Player is an HD Series 4 class BrightSign player. Built-in module is compatible with all BrightSign software, services, and supported CMS solutions.

Features:

- HS124 - HD4 class BrightSign Built-in player
- HD class performance; runs BrightSign software or compatible CMS partners software
- H.265/H.264 video decode
- Video output up to 1080p60
- 10-bit video output (using H.265)
- Hardware accelerated HTML5 support
- Multi-point capacitive touch screen optional
- Adjustable brightness
- Displays in either landscape or portrait orientations
- Fully compatible with Windows, Linux, and Mac OS

Applications:

- POP/POS
- Gaming and entertainment
- Kiosk information system
- Conference room scheduling