



Poly Voyager Surround 85 UC Microsoft Teams Certified USB-C Headset +USB-C/A Adapter +Charging Stand (8G7T8AA)



Overview

Crafted for your work life

Experience limitless productivity with our boomless Bluetooth® headset, designed to deliver rich, clear audio for calls and music. Enjoy optimal comfort, adaptive ANC, and wireless charging, enabling you to work effortlessly anywhere, anytime.

Clear audio, focused work

Engage in what's important and avoid distractions with a headset that delivers rich, clear audio for calls and music. Work where you want and sound your best with 6 built-in boomless mics plus 4 more to support adaptive ANC.

All day productivity

Boost efficiency with a headset and wireless charge stand designed to work as hard as you do. Experience non-stop communication with effortless docking, ensuring 21-hour talk time. Stay connected without skipping a beat.

Concentrate in real comfort

Experience long-lasting comfort while you focus on work. You'll forget you're wearing a headset with the sleek carbon fiber design, ultra-soft ear cups, and adjustable headband for a weightless fit.

Make it your own

Customize your personal Poly devices with the powerful desktop or web-based Poly Lens app. Set audio settings for each device based on your workstyle.

Features

Get in the zone

Stay focused and keep out the distractions of the outside world with adaptive ANC and over-the-ear design.

Declutter and stay charged

Our wireless NFC charge stand keeps you talking all day. Dock your headset seamlessly and always know the charge status with the LED indicator. The sleek design features a no-slip base, 1.5 m USB-C cable, and tidy cable management.

Touch controls

Control your calls and pause/play your music with easy-to-use touch controls. With just one click, you can mute yourself with a dedicated button.

Take your call anywhere

Sound your best where you work with 6 built-in microphones for clear transmit audio without the noise — in a boomless design.

Extended talk time

Say goodbye to battery anxiety. Talk all-day and stay charged up with our wireless charge stand ensuring up to 21 hours of talk time or up to 24 hours of listen time.

Ultimate listening bliss

Discover unparalleled comfort in our innovative lightweight carbon fiber design featuring an ergonomic headband for even pressure distribution, slanted audio drivers for comfort, and larger ear cushions for enhanced noise-cancellation.

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Audio	Microsoft Teams Open Office certified
Battery life	Up to 24 hours (music time); Up to 21 hours (talk time)
Battery type	Rechargeable Li-ion
Bluetooth version	5.3
Button user controls	Mute; Power on/off/pairing
Certified collaboration software	Microsoft Teams Open Office
Charge time	1 hour
Charging plug	USB Type-C® to USB Type-C®
Color	Black
Compatible Operating Systems	macOS; Android™; iOS; Windows
Connection type	Bluetooth® 5.3
Ear cushions	Artificial leather (surface material)
Indicator light	On call
Management Software	Poly Lens
Manufacturer Warranty	Poly standard two-year limited warranty
Microphone bandwidth	20 Hz to 16 kHz
Microphone type	Boomless
Minimum System Requirements	USB Type-A port; Bluetooth®; 3.5 mm audio; USB Type-C® port
Minimum dimensions (W x D x H)	7.52 x 3.03 x 7.13 in
Minimum dimensions (W x D x H)	191 x 77 x 181 mm
Number of microphones	10
Paired devices	Up to 2
Sensitivity (microphone)	-37 dB FS
Sensitivity (speaker)	132 dB SPL
Speaker size	40 mm
Supported bluetooth profiles	A2DP; AVRCP; HFP; HSP; AVDTP
Touch user controls	Volume +/-; Play/pause; Track forward/back; Programmable touch control
UNSPSC code	43191638
Weight	0.6 lb
Weight	275 g
What's in the box	Carrying case; User guide; Wireless headset; USB charging cable; BT700 Bluetooth® Type-C® adapter; USB Type-C® to USB Type-A adapter; USB Type-C® to 3.5 mm audio cable

Wireless range	Up to 30 m
-----------------------	------------

Wireless range (imperial)	Up to 98 ft
----------------------------------	-------------

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Dec 15, 2023 12:21 PM UTC+0000