

Product datasheet

Specifications



Galaxy VS UPS 60kW 400V with N+1 power module for external batteries, Start-up 5x8

GVSUPS60KRHS

Overview

Presentation	Highly efficient, easy-to-deploy 60kW, 400V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. Includes 5x8 start-up service and one additional power module for N+1 redundancy.
Lead time	Usually Ships within 2 Weeks

Main

Main Input Voltage	400 V 3 phases
Other Input Voltage	380 V 415 V
Main Output Voltage	400 V 3 phases
Rated power in W	60 kW
Rated power in VA	60 kVA
Battery type	External battery system Li-Ion (Lithium-Ion) VRLA
Provided equipment	Dust filter EcoStruxure IT ready (UPS) Installation guide Integrated network management Power modules ship installed Start-up service

Batteries & Runtime

Max current discharge	163 A
------------------------------	-------

General

Bypass voltage tolerance	+/- 10 %
Redundant	Yes

Physical

Colour	White
Height	148.5 cm
Width	52.1 cm
Depth	84.7 cm
Net weight	290 kg

Input

Network frequency	40...70 Hz
Input voltage limits	340...460 V 400 V
Maximum input current	108 A
Max short time withstand current	65 kA
Input harmonic distortion	Less than 3 % for full load
Load power factor	From 0.7 leading to 0.7 lagging without any derating

Output

Maximum configurable power in W	60 kW
Output frequency	50 Hz sync to mains 60 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised
Crest factor	2.5
Wave type	Sine wave
Output voltage tolerance	+/-1% after 50ms
Output harmonic distortion	< 1% linear load and < 5% non-linear load
Output overload operation	10 minutes at 125% and 60 seconds at 150%
Bypass type	Built-in static bypass
Maximum configurable power in VA	60 kVA

Conformance

Standards	EN/IEC 62040-1 EN/IEC 62040-2 FCC part 15 class A IEC 60721-4-2 level 2M2 UL 1778 5th edition
-----------	---

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3300 ft
Ambient air temperature for storage	-25...55 °C
Storage Relative Humidity	10...80 % non-condensing
Acoustic level	68 dBA
Heat dissipation	6150 Btu/h
IP degree of protection	IP21

Communications & Management

Control panel	Touch screen LCD user interface
---------------	---------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	168 cm
Package 1 Width	99 cm
Package 1 Length	64 cm
Package 1 Weight	315 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Recommended replacement(s)