

ThinkVision P27pz-30

PSREF

Product Specifications Reference

PERFORMANCE

Display Size

27"

View Area

596.7x335.6 mm

Panel

In-Plane Switching

Backlight

Mini-LED

Aspect Ratio

16:9

Resolution

3840x2160

Pixel Pitch

0.155x0.155 mm

Dot / Pixel Per Inch

163 dpi

View Angle (H / V)

178° / 178°

Response Time

4ms (Extreme mode) / 6ms (Normal mode)

Color Support

1.07 Billion

Refresh Rate

60Hz

Brightness

650 cd/m² (Typical) / 1200 cd/m² (Peak)

Contrast Ratio

1000:1

Color Gamut

99% DCI-P3, 99% Adobe® RGB, 100% sRGB, 100% BT.709, 81% BT2020

Screen Surface Treatment

Anti-glare

Curvature

Flat Panel

Camera

Modular Camera Support

Microphone

None

Speakers

Modular Speaker Support

Power Consumption (Typical / Maximum)

26W / 315W

Power Adapter

Integrated

Touchscreen

None

Smart System

None

DESIGN

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Case Color

Raven Black

Side Bezel Width

2 mm

Mounting

Supports VESA mount 100 x 100 mm

ThinkCentre® M Series Support

Tiny, Nano Support

Pen

None

Dimensions (WxDxH)

- Head Only | 613.5 x 76.4 x 372.9 mm (24.15 x 3.01 x 14.68 inches)
- Highest Position | 613.5 x 220.4 x 549.8 mm (24.15 x 8.68 x 21.65 inches)
- Lowest Position | 613.5 x 220.4 x 397.8 mm (24.15 x 8.68 x 15.66 inches)

Packaging Dimensions (WxDxH)

706 x 163 x 504 mm (27.8 x 6.41 x 19.84 inches)

Weight

- Monitor With Stand | 8.8 kg (19.4 lbs)
- Monitor Head Only | 6.2 kg (13.7 lbs)

Packaging Weight

12 kg (26.5 lbs)

CONNECTIVITY

USB Port

1x USB-C® 3.2 Gen 2 (USB upstream), 1x USB4® (DP 1.4 Alt Mode, up to 140W PD, USB upstream), 4x USB 3.2 Gen 2 (1x BC1.2), 1x USB-C® 3.2 Gen 2 (Up to 15W)

Video Connector

2x HDMI® 2.1 TMDs, 1x DP 1.4, 1x DP 1.4 Out, 1x USB 4 (40Gbps, DP 1.4 Alt Mode)

Network Connectivity

1x RJ45, Ethernet (10M/100M/1000M)

SERVICE

Base Warranty

3-year

CERTIFICATIONS

Environmental Certification

ENERGY STAR® Certified, RoHS, EU Energy Efficiency Level (Level-F), EPEAT™ Gold

Ergonomic Certification

TÜV Low Blue Light, TÜV Rheinland® Eye Comfort, TÜV Rheinland® Flicker Free

Sync Technology

None

Special Features

- HDR10 Compliance
- DisplayHDR™ 1000
- Factory Calibration: Avg. Delta E<1.5
- Picture In Picture (PIP) / Picture By Picture (PBP) Support
- Lenovo® ThinkColour (Lenovo® Accessories and Display Manager) Support
Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems).
Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
- HLG
- KVM Switch
- Smart Power
The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device
- Smart Sensor (Ambient Light Sensor, Human Detection Sensor)

SOFTWARE

Operating System

Support Windows® 10, Windows® 11

ACCESSORIES

Video Cables

USB-C® to USB-A Gen 2 Cable, USB 4 Cable

MODEL

Announce Date	: 2023-09-06	EAN	/	UPC	: 0196804350646 / 196804350646 / None
			/		
				JAN	

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

Kensington MicroSaver 2.0 Cable Lock from Lenovo

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

Lenovo HDMI to VGA Monitor Adapter

Go Do. Connect. The 20 cm Lenovo HDMI to VGA Monitor Adapter provides the best sleek compatibility experience as it seamlessly enables interoperability of ThinkPad systems with commercial analog projectors and displa...

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

PSREF
Product Specifications
Reference