


NX Series

Unparalleled visual experience.



Ultra-thin and lightweight



16:9
Aspect ratio

43.5mm 1.71"
Ultra-thin design

20kg/m² 44lbs/m²
Ultra-lightweight

Items	NX1.5	NX1.8	NX2.5	NX3.7
Panel resolution	640*360	512*288	384*216	256*144
4K display	6*6pcs	8*8pcs	10*10pcs	15*15pcs
8K display	12*12pcs	15*15pcs	20*20pcs	30*30pcs


Ultimate display performance



- 800nits normal brightness version
- 1500nits high brightness version(optional)
- A5C+ color calibration technology
- High grayscale at low brightness
- TÜV Rheinland low blue light certification

• Corporate, mall, chain store, transportation hub, etc

◀ Creative splicing with 45° edge-cutting small panel



240 (W)*540 (H)* 43.5 (D) mm
9.45 (W)*21.26 (H)* 1.71 (D) "
Default 45° angle on both sides

◀ Installation and maintenance



- Rotary clamshell design for easy rear maintenance
- Front/rear maintenance of module, PSU, receiving card, etc.
- Supports hanging, wall-mounting and stacking installation
- Precise floating connector for bright and dark lines adjustment
- X/Y/Z axis alignment for flatness adjustment between panels



- Flat screen with large panels + curve splicing with small panels



- Artistic wavy splicing with small panels



- 90° seamless L-shape splicing



- Cube

◀ Product specification

Parameters	NX1.5	NX1.8 (Normal)	NX1.8 (High brightness)	NNX2.5 (Normal)	NX2.5 (High brightness)	NX3.7 (Normal)	NX3.7 (High brightness)
LED type	Black SMD1212	Black SMD1515	Black SMD1515	Black SMD1515	Black SMD1515	Black SMD1515	Black SMD1515
Pixel pitch (mm)	1.5	1.87	1.87	2.5	2.5	3.75	3.75
Panel dimensions (W*H*D, mm)	960x540x43.5mm(37.80x21.26x1.71") / 240x540x43.5(9.45x21.26x1.71")						
Brightness (nit)	800	800	1500	800	1500	800	1500
Refresh rate (Hz)	3840						
Grayscale (bit)	16 (Internal processing 16bit)						
Contrast ratio	4000:1	4000:1	6000:1	4500:1	7600:1	5200:1	7400:1
Color temperature (K)	6500	6500	6500	6500	6500	6500	6500
Viewing angle (H/V, °)	150/150	160/160	160/160	160/160	160/160	160/160	160/160
Drive mode	1/45	1/36	1/36	1/27	1/27	1/18	1/18
AC operating voltage (V)	100~240	100~240	100~240	100~240	100~240	100~240	100~240
Power consumption (max./avg., W/m ²)	480/160	420/140	606/202	450/150	534/178	480/160	609/203
IP Rating (Front/Rear)	IP40/IP21	IP40/IP21	IP40/IP21	IP40/IP21	IP40/IP21	IP40/IP21	IP40/IP21
Certification	FCC, ETL, CE, RoHS						

Note:

1. NX1.5 only has 800nits normal brightness version.
2. Provides optional dual backup version to ensure continuous transmission of signal and power supply.
3. Small panel adopts rotary clamshell design as well and support rear maintenance of PSU and receiving card.
4. Z-axis alignment function is only available for ground stacking installation.

Abjen

HQ Office
7120 Lake Ellenor Dr Orlando, FL 32809
407.203.8870 info@usabsen.com
www.usabsen.com

East Service Center&Warehouse
7307 Presidents Drive, Orlando, FL 32809
West Service Center & Showroom
20311 Valley Blvd Suite J, Walnut, CA 91789

Twitter: @Absen_Inc
Facebook: @AbsenInc
LinkedIn: @AbsenInc
IG: @absen_inc