


HPE G2 Metered Modular 4.9kVA/L6-30P 24A/208V Outlets (6) IEC C19/1U Horizontal NA/JP PDU (P9R51A)



What's new

- HPE G2 Metered Power Distribution Units (PDU) are rated for operating temperatures of up to 60°C (or 140°F).
- Color-coded receptacles on single and three phase models to easily distinguish between the different load segments/phases.
- A hot swappable Network Management Card (NMC) allowing for power to remain distributed with the removal of the management card thus creating zero down time.

Overview

Do you need rack level power monitoring over the network?

With billing grade accuracy, HPE G2 Metered Power Distribution Units (PDU) are an excellent choice for data centers wanting to make the most of circuit capacity or for co-location facilities needing to precisely track power usage for billing purposes.

The G2 Metered PDUs offer load segment power metering and have a low profile single piece design with multiple mounting options and ease of access to rear devices for maintenance. Designed for HPE racks but also work in a large variety of third party racks as well using standard button and keyhole

- Enhanced environmental sensor options on the G2 Metered PDUs for monitoring temperature, humidity, intrusion, and water leakage within the rack.
- Choose the optional Locking Power Cord for secure cable retention to both the PDU and target device.

mounting. They can be installed on either side of the rack with outlets facing the back of the rack for easy access and improved clearance. Also for higher power density they can be installed side by side on both sides of the rack with the outlets facing in towards the center of the rack. HPE G2 Metered PDUs are backed by HPE's limited 3-year warranty.

Features

Powerfully Built Power Distribution, Because No Two Environments Are the Same

HPE G2 Metered Power Distribution Units (PDU) include a 3-year warranty.

Premium materials and robust construction guarantee power continuity and maintained performance at elevated temperatures.

Power distribution where you need it in the rack with Load segment metering for added management and security.

Get Power Where You Need It To Go – and Keep It There

HPE G2 Metered Power Distribution Units (PDU) are compatible with HPE IEC Locking Power Cords a new supported option available for most HPE G2 PDUs. HPE's IEC Locking Power Cords provide a safe and secure solution against the common issues that lead to power-related downtime.

Integrated cord retention to connect the right cord to the right outlet, quickly and easily.

Daisy-chain up to four units to share the same network connection and IP address.

Load segment metering capabilities keep you in the loop at all times – and let you shut things down if something's amiss, from wherever you are.

Enhanced environmental sensor options on HPE G2 Metered PDUs for monitoring temperature, humidity, intrusion, and water leakage within the rack.

Getting Power In the Right Place Has Never Been Easier, From Purchase To Prime Time

HPE G2 Metered Power Distribution Units (PDU) are available in four form factors for a variety of rack configurations and environments.

Hot swappable network management provides enables serviceability without any downtime.

Dual network access provides redundancy to protect data continuity and enable informed management decisions.

Highest-density PDUs on market means more power and less headache for even the most demanding compute applications.

ASHRAE-certified 60-degree centigrade operating temperature (10 degrees above industry standard) means more performance and less cooling costs.



Technical specifications

HPE G2 Metered Modular 4.9kVA/L6-30P 24A/208V Outlets (6) IEC C19/1U Horizontal NA/JP PDU

Product Number	P9R51A
Mounting options	0U/Horizontal, and 1U/Horizontal
Outlet type	C-19
Power capacity	Less than 5kVA
Power distribution	Single Phase
Product dimensions	44.35 x 26.97 x 4.35 cm
Weight	7.03 kg
Warranty	Three-year limited warranty



For additional technical information, available models and options, please reference the [QuickSpecs](#)

HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

Consulting services

Experts can help you map out your path to hybrid cloud and optimize your operations.

Managed services

HPE runs your IT operations, giving you unified control, so can focus on innovation.

Operational services

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources.

- HPE Complete Care Service: a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.
- HPE Tech Care Service: the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.

Lifecycle Services

Address your specific IT deployment project needs with tailored project management and deployment services.

HPE Education Services

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options.

The [Defective Media Retention \(DMR\)](#) service feature option applies only to Disk or eligible SSD/Flash Drives replaced by Hewlett Packard Enterprise due to malfunction. [Comprehensive Defective Material Retention \(CDMR\)](#) allows you to keep all data retentive components.

HPE GreenLake

[HPE GreenLake edge-to-cloud platform](#) is HPE's market-leading as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model, on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please explore them [here](#).

Explore **HPE GreenLake**



Make the right purchase decision.
Contact our presales specialists.



Share now



Get updates

© Copyright 2024 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Image may differ from the actual product
[PSN1009830225WWEN](#), February, 2024.


**Hewlett Packard
Enterprise**