


30m (98.4ft) LC to LC (UPC) OS2 Single Mode Duplex Fiber Optic Cable, 9/125m, 100G, Bend Insensitive, Low Insertion Loss, LSZH Fiber Patch Cord

**Product ID:** SMDOS2LCLC30M



OS2 LC to LC Single Mode Duplex Fiber Optic Patch cable facilitates connectivity across 100G networks. It supports Coarse Wavelength Division Multiplexing (CWDM) across an extended wavelength range of 1260-1625nm, improving channel isolation for optimal signal strength over long distances.

This 9/125m Single Mode fiber cable supports 1260-1625nm laser-optimized sources and is ideal for critical connections between servers, switches, and data center equipment. It is backward compatible with OS1 networks, ensuring a reliable connection in legacy fiber environments.

Precision-manufactured ceramic ferrules ensure accurate fiber alignment for an insertion loss below 0.3dB. Ultra Physical Contact (UPC)-polished LC to LC fiber ends greatly improve return loss characteristics over older PC polishing techniques. The Bend Insensitive fiber core is surrounded by a layer of low refractive index material. This material reduces the amount of light that can escape the fiber cable by reflecting the light back into the fiber. The OS2 fiber patch cord is engineered for low attenuation and performance that exceeds ITU-T G652.D/G657.A1 and IEC60703-2-50 type B1.3/B6.a1 industry standards.

Housed in a Low-Smoke Zero-Halogen (LSZH) flame-retardant jacket, the OS2 fiber cable emits low smoke and toxic fumes when exposed to extreme heat or in the event of a fire. This enables safer cable installations in areas with poor ventilation including some industrial settings, self-contained environments such as trains and aircraft, as well as residential settings where compliance with building codes must be considered.

Each OS2 fiber cable is individually tested for insertion loss performance and includes a test report, for guaranteed compatibility and 100% reliability.

## Certifications, Reports and Compatibility



## Applications

- Use in 100 Gigabit Ethernet and fiber-channel applications
- For high-speed, low-latency connections between servers, switches, and storage devices
- Enable seamless data transmission with minimal signal loss

## Features

- **OS2 FIBER CABLE:** Single Mode OS2 Fiber Cable is immune to EMI and optimized for 100Gbps networks; Coarse Wavelength Division Multiplexing (CWDM) enables extended 1260-1625nm wavelength support for greater channel isolation over long distances
- **QUALITY CONSTRUCTION:** LC/LC-UPC ends for improved return loss over PC polish; Numbered and color-coded connectors to indicate polarity; Bend Insensitive fiber core housed in Aramid-reinforced jacket for a loaded bend radius of 10mm
- **SAFETY AND RELIABILITY:** Individually tested for guaranteed performance; Test report included; LSZH jacket emits low toxic fumes if combusted; Safe for enclosed/poorly ventilated spaces; Attenuation value under 0.35dB/km outperforms industry standards
- **COMPATIBILITY:** Single Mode Fiber Patch Cord supports 100G networks; Backward compatible with OS1; High micro-bend resistance facilitates tight bends in complex installations; Ideal for connecting between servers/switches and data center equipment
- **SPECS:** 30 meter (98.4 foot); OS2 Single Mode; LC/LC (UPC) Duplex; 100Gbps; 9/125um; 1260-1625nm Laser Optimized; Insertion Loss: 0.3dB; Return Loss: 55dB; Cable OD: 2mm; Bend Radius: 10mm (0.39in) loaded/unloaded

---

### Hardware

|                           |                                     |
|---------------------------|-------------------------------------|
| Warranty                  | Lifetime                            |
| Active or Passive Adapter | Passive                             |
| Cable Jacket Material     | Low Smoke Zero Halogen              |
| Fire Rating               | LSZH Rated (Low Smoke Zero Halogen) |
| Fiber Size                | 9/125                               |

---

### Performance

|                            |         |
|----------------------------|---------|
| Maximum Data Transfer Rate | 100Gbps |
|----------------------------|---------|

|                        |                                              |
|------------------------|----------------------------------------------|
| Cable Rating           | 10Gbps / 40Gbps / 100Gbps                    |
| Fiber Classification   | OS2                                          |
| Maximum Cable Length   | 3.3 ft [1 m]                                 |
| Type                   | Single Mode                                  |
| Wavelength             | 1260nm to 1625nm                             |
| General Specifications | Insertion Loss: 0.3dB<br>Return Loss: 55dB , |

#### Connector(s)

|             |                           |
|-------------|---------------------------|
| Connector A | 1 - Fiber Optic LC Duplex |
| Connector B | 1 - Fiber Optic LC Duplex |

#### Environmental

|                       |                         |
|-----------------------|-------------------------|
| Operating Temperature | -20C - 60C (-4F - 140F) |
| Storage Temperature   | -20C - 60C (-4F - 140F) |
| Humidity              | 40% - 70%               |

#### Physical Characteristics

|                   |                    |
|-------------------|--------------------|
| Color             | Yellow             |
| Connector Style   | Straight           |
| Material          | Polypropylene (PP) |
| Cable OD          | 0.1 in [2 mm]      |
| Product Length    | 98.4 ft [30.0 m]   |
| Product Width     | 0.5 in [1.2 cm]    |
| Product Height    | 0.4 in [1.0 cm]    |
| Weight of Product | 0.0 oz [0.0 g]     |

#### Packaging Information

|                |                   |
|----------------|-------------------|
| Package Length | 10.0 in [25.5 cm] |
| Package Width  | 13.0 in [33.0 cm] |

|                |                 |
|----------------|-----------------|
| Package Height | 0.6 in [1.5 cm] |
|----------------|-----------------|

|                              |                  |
|------------------------------|------------------|
| Shipping (Package)<br>Weight | 7.9 oz [224.0 g] |
|------------------------------|------------------|

---

**What's in the Box**

|                     |                                                      |
|---------------------|------------------------------------------------------|
| Included in Package | 1 - 30m OS2 Single Mode Fiber Optic Cable - LC to LC |
|                     | 1 - Test Report                                      |

---

***\*Product appearance and specifications are subject to change without notice.***