

MAXPRO® NVR SE

32/48/64-Channel NVR



OPERATIONAL	
MAXPRO NVR SOFTWARE - VERSION 7.5	
DATABASE	Microsoft® SQL Server® 2019 Express
OPERATING SYSTEM	Windows™ 10 IoT Enterprise for Embedded Systems
IMAGE COMPRESSIONS SUPPORTED	MJPEG, MPEG-4, H.264, H.265
SUPPORTED HONEYWELL IP CAMERAS AND ENCODERS	Supports Honeywell Performance IP, eIP® Series, 30/35/60/70 Series IP cameras
SUPPORTED THIRD PARTY IP CAMERAS AND ENCODERS	Refer to the MAXPRO® NVR Compatibility on our website for a comprehensive list of compatible products to which this device is integrated.
AUDIO SUPPORT	2-way audio for specific IP camera models.
MAXIMUM NUMBER OF DESKTOP CLIENT CONNECTIONS	Desktop Client - 38 per unit from 19 remote workstations + 2 local on NVR
SALVO LAYOUTS	Desktop Client - Full, 2x2, 1x5, 3x3, 2x8, 1x12, 4x4. Web Client - 2x2, 1x1, 1x2, 1x3. Mobile app (Phone) - 2x2, 2x4, 1x2, 1x1. Mobile app (Tablet) - 3x3, 2x2, 1x1.
PICTURE CONTROLS PER CAMERA	Sharpness, blur, brightness, contrast, hue, saturation, maintain aspect ratio, stretched, original size and picture mirror
OSD	Concealed text option
PLAYBACK CONTROLS PER CAMERA - DESKTOP CLIENT	FWD/REV Play x (1, 2, 4, 8, 16) Slow FWD/REV Play x (1/2, 1/4, 1/8)
SEARCH TYPES	Time/date timeline, time jump FWD/REV, bookmarks, calendar, preview, film strip, event search and SMART Motion Search
RECORDING SCHEDULE	Continuous and event based with H/M/D and holiday and exception days
RECORDING METHODS PER CAMERA	Continuous, event based and user activated
LIVE SETTINGS / CAMERA	Compression format, resolution and frame rate
RECORD SETTINGS PER CAMERA	Same as live or can be a separate stream configuration
CLIP FORMAT	Honeywell MPVC and SMPVC playable with standalone MAXPRO Clip Player for faster and secure exports. WMV with digital certificate for authentication playable with Windows media player. ASF for faster exporting of longer than an hour backup clips in native compression format.
VIDEO CLIP AUTHENTICATION	Digital signature, verification tool provided
MOTION DETECTION LOCATION	Camera-based for supported models or Server-based (SMART VMD) for all models (except 360 fisheye /panomorph views)
EVENT RECORDING	Pre and post duration setting
OPERATOR REPORTING	Per user, configurator, session and viewer
EVENT REPORT	Per camera or recorder events
OPERATORS	1024

OPERATIONAL	
MAXPRO NVR SE HARDWARE	
PROCESSOR	Intel® Core™ i7-8700, 3.2 GHz, Intel HD Graphics 630
MEMORY	16 GB DDR4
POWER SUPPLY	Single 500 W
OS PARTITION	250 GB M.2 SSD OS drive
STORAGE CAPACITIES	4 TB to 96 TB
STORAGE HARD DRIVE OPTIONS	6 bays - all field-upgradable, 4, 6, 8, 10, 12, or 16 TB SATA hard drives
OPTICAL	24x DVD-RW
NETWORK	Two 1 GB Ethernet included
CHASSIS WITH LOCKING BEZEL	2U 6 bay including rack mount kit
REAR PANEL CONNECTIONS	
MOUSE AND KEYBOARD	2x USB
USB	1x front, 4x back (including 4x USB 3.2)
NETWORK	2x RJ45
MONITOR OUTPUT	1 HDMI, 1 DVI, 1 VGA
ELECTRICAL	
INPUT VOLTAGE	100 V to 240 V - 50 Hz/60 Hz - max 500 W, auto switching
POWER DISSIPATION	Average BTU rating = 569 BTU/hour
MECHANICAL	
CONSTRUCTION	Housing: Steel chassis Finish: Black matte paint
DIMENSIONS (W X H X D)	17.2 in x 3.5 in x 26 in (437 mm x 88 mm x 660 mm)
WEIGHT	Unit: 43 lb (19.5 kg)
ENVIRONMENTAL	
TEMPERATURE	Operating: 5°C to 40°C (40°F to 104°F) Storage: -10°C to 65°C (14°F to 150°F)
RELATIVE HUMIDITY	0% to 90%, non-condensing
REGULATORY	
EMISSIONS	FCC Part 15, Subpart B, Class B
SAFETY	ANSI/UL 60950-1; CAN/CSA C22.2 No 60950-1
OTHER	
COUNTRY OF ORIGIN	United States
WARRANTY	3-year warranty, next business day on-site support (North America)
RECORDING AND REMOTE MONITORING PERFORMANCE	
1920 fps @ 4CIF/VGA or 1920 fps @ 720p HD or 1280 fps @ 1080p (4 Mbps bitrate) HD. One-way audio for up to 64 IP channels. Network bandwidth/throughput - Incoming: 160 Mbps, Outgoing: 280 Mbps, Total: 440 Mbps. Rendering performance using GPU of up to four 1080p HD @ 30 fps /two 4K @ 30fps on local client. Note: Oncam Grandeye 360 Cameras are not supported with GPU rendering and use CPU rendering by default.	

MAX VIDEO STREAMS SUPPORT	Desktop Client: Live - 256 streams, playback/video retrieval sessions - 32, Sync playback - 9 streams. 256 live streams limit excludes one stream used per camera if SMART VMD is enabled. Maximum live streams per camera is 15 with SMART VMD enabled. Mobile App: 16 streams of 1080p HD @ 5 fps each. Note: During archival operations, maximum no of playback streams recommended from Desktop Client and Web Client is 16 streams.
SERVER BASED VMD (SMART VMD) PERFORMANCE - CHANNELS SUPPORTED	Channels at max fps: 64 ch at 1920 fps @ 4CIF/VGA or 64 ch at 1920 fps @ 720p or 50 ch at 1280 fps @ 1080p or total 100 Megapixel. All channels at fps: 64 ch at 1920 fps @ 4CIF/VGA or 1920 fps @ 720p or 640 fps @ 1080p or total 128 Megapixel.
ARCHIVAL PERFORMANCE	16 channels @ 4 Mbps bitrate each/64 Mbps total archival throughput capacity. Outgoing archival storage throughput of 200 Mbps.
MULTI-STREAM PERFORMANCE	Support for maximum 128 streams. Support for configuring one preferred stream for continuous recording and one preferred stream for live video/motion based recording per camera.

Honeywell

MAXPRO® NVR SE (Standard Edition)


32/48/64-Channel Network Video Recorder (NVR)

HARDWARE FEATURES


- Provides the processor and storage enclosure in one chassis, resulting in both space and cost savings
- Rack mountable with six removable drives, SATA hard drives used for operating system partition and video storage
- Record and monitor up to 64 channels at 1920 fps @ 4CIF/VGA or 1920 fps @ 720p HD or 1280 fps @ 1080p (4 Mbps bitrate) HD per MAXPRO NVR SE. Network bandwidth/throughput supported per NVR with Incoming: 160 Mbps, Outgoing: 280 Mbps; Total: 440 Mbps.
- Archival support of 16 channels @ 4 Mbps bitrate each/64 Mbps total archival throughput capacity per MAXPRO NVR SE, with outgoing archival storage throughput of 200 Mbps
- Multi-stream support with maximum 128 streams per MAXPRO NVR SE. Support for configuring one preferred stream for continuous recording and one preferred stream for live video / motion based recording per camera
- Supports one-way audio (for specific IP cameras) with live, playback and clip export on desktop clients for up to 64 IP channels
- Includes HDMI, DVI-D and VGA ports for dual monitor support
- Supports displaying 16 cameras at one time on the NVR local monitor and rendering performance using GPU of up to 4 1080p HD @ 30 fps/2 4K @ 30 fps on local client
- 1 solid-state drive with operating system and six removable bays with storage hard drives (optional 4 TB, 6 TB, 8 TB, 10 TB, 12 TB or 16 TB SATA hard drives)
- Internal storage capacity from 4 TB to 96 TB
- Includes dual 1 GB Network ports optimized to separate record and viewing data to ensure 100% recording and smooth playback even with multiple client connections
- 2U rack mount form factor with locking front bezel. Rack rails included for use with four post racking systems

SPECIFICATIONS

Front View




Rear View



- 1 COM (RS-232)
- 2 HDMI 1.4
- 3 VGA
- 4 DVI-D
- 5 RJ45 LAN (Intel I219V)
- 6 RJ45 LAN (Realtek RTL8111HS)
- 7 USB 3.2 Gen 1 (3x)
- 8 USB 3.2 Gen 1 (1x)
- 9 Audio Line-in
- 10 Audio Line-out
- 11 Microphone In

Side View



MAXPRO® NVR SE (Standard Edition)

32/48/64-Channel Network Video Recorder (NVR)


ORDERING

MAXPRO NVR SE	
HNMSE32D04T	4 TB, 32 Channel, 1 x 4 TB
HNMSE48D04T	4 TB, 48 Channel, 1 x 4 TB
HNMSE64D04T	4 TB, 64 Channel, 1 x 4 TB
HNMSE32D08T	8 TB, 32 Channel, 2 x 4 TB
HNMSE48D08T	8 TB, 48 Channel, 2 x 4 TB
HNMSE64D08T	8 TB, 64 Channel, 2 x 4 TB
HNMSE32D16T	16 TB, 32 Channel, 4 x 4 TB
HNMSE48D16T	16 TB, 48 Channel, 4 x 4 TB
HNMSE64D16T	16 TB, 64 Channel, 4 x 4 TB
HNMSE32D24T	24 TB, 32 Channel, 6 x 4 TB
HNMSE48D24T	24 TB, 48 Channel, 6 x 4 TB
HNMSE64D24T	24 TB, 64 Channel, 6 x 4 TB
HNMSE32D36T	36 TB, 32 Channel, 6 x 6 TB
HNMSE48D36T	36 TB, 48 Channel, 6 x 6 TB
HNMSE64D36T	36 TB, 64 Channel, 6 x 6 TB
HNMSE32D48T	48 TB, 32 Channel, 6 x 8 TB
HNMSE48D48T	48 TB, 48 Channel, 6 x 8 TB
HNMSE64D48T	48 TB, 64 Channel, 6 x 8 TB
HNMSE32D60T	60 TB, 32 Channel, 6 x 10 TB
HNMSE48D60T	60 TB, 48 Channel, 6 x 10 TB
HNMSE64D60T	60 TB, 64 Channel, 6 x 10 TB

Refer to the storage calculator on buildings.honeywell.com to help determine what size unit to order.

MAXPRO NVR SE – CHANNEL UPGRADE LICENSES	
HNM01UP	MAXPRO NVR – 1 channel license upgrade to add support for up to 64 channels per NVR
HNM04UP	MAXPRO NVR – 4 channel license upgrade to add support for up to 64 channels per NVR
HNM08UP	MAXPRO NVR – 8 channel license upgrade to add support for up to 64 channels per NVR
HNM16UP	MAXPRO NVR – 16 channel license upgrade to add support for up to 64 channels per NVR
HNM32UP	MAXPRO NVR – 32 channel license upgrade to add support for up to 64 channels per NVR
UPGRADE KITS FOR MAXPRO NVR SE/XE REV D	
HNMSXDHD2T	2 TB HDD upgrade kit
HNMSXDHD4T	4 TB HDD upgrade kit
HNMSXDHD6T	6 TB HDD upgrade kit
HNMSXDHD8T	8 TB HDD upgrade kit
HNMSXDHD10T	10 TB HDD upgrade kit
3RD PARTY I/O MODULE INTEGRATION	
HNMNVR3PIO	Network I/O module
SOFTWARE MAINTENANCE & UPGRADES AGREEMENTS FOR MAXPRO NVR	
SSAMPNVRCH	Annual Software Support Agreement – MAXPRO NVR System with VMS support included, Per Channel
SSA24MPNVRCH	Annual 24/7 Software Support Agreement – MAXPRO NVR System with VMS support included, Per Channel
SSAEUMPNVRCH	Annual End User 24/7 Software Support Agreement – MAXPRO NVR System with VMS support included, Per Channel

MAXPRO NVR SE – PART NUMBER LOOKUP



For more information

buildings.honeywell.com/security

Honeywell Commercial Security

715 Peachtree St. NE
 Atlanta, GA 30308
 1.800.323.4576
www.honeywell.com

Intel® and Core™ are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries.

Microsoft®, Windows™, and SQL Server® are trademarks or registered trademarks of Microsoft Corporation in the United States and other countries.

MAXPRO is a trademark or registered trademark of Honeywell International Inc in the United States and other countries

Honeywell reserves the right, without notification, to make changes in product design or specifications.

HSV-MPSE-13-US(1122)DS-ZD
 © 2022 Honeywell International Inc.

