

M/Flex for M2.1 M8.1 and M10

Model Number: X2NTNCESTBCTB---18-----

List Price (As of 10/15/24): US\$1,049.00



FEATURES

- Scalable solution accommodates future additions of up to 6 monitors
- Compatible with Humanscale's M2.1, M8.1 and M10 monitor arms
- Reduces future installation costs by allowing for simple reconfigurations
- Available with accessories such as Notebook Holders, Crossbars, Thin Client Holders, UFEAs, Coloured VESA Covers and Sliders
- Patent-pending Smart Stop allows the user to customise the rotation of the arm, preventing overhang and protecting surrounding equipment
- Patent-pending Quick Release Joints instantly snap together for a secure and robust fit, simplifying installation
- Compatible with M/Connect, M/Connect 2 and M/Power, the first-ever integrated monitor arm bases and docking stations of their kind

SPECIFICATIONS

Weight Capacity: Supports up to 40 kg (90 lbs.)

Maximum Arm Reach: Up to 710 mm (28")

Maximum Height Adjustment: Up to 255 mm (10") dynamic 760 mm (30") static

Monitor Capacity: Up to 6 monitors

Colour Options:

- Polished Aluminium with White Trim
- Silver with Grey Trim
- Black with Black Trim

Product Material: Recycled Aluminium

Warranty: 15 years

CONFIGURATION DETAILS

CODE DESCRIPTION

X2	- M/Flex for M2.1 Monitor Arm
NT	- Base Without Technology
N	- No Technology
C	- Clamp
E	- Two Single Monitor Brackets for 2 Monitors
S	- Silver with Grey Trim
C	- 100mm (4") Straight Link/Dynamic Link
T	- Standard Monitor Tilt (one per monitor)
B	- Standard 100mm x 100mm, black
C	- 100mm (4") Straight Link/Dynamic Link
T	- Standard Monitor Tilt (one per monitor)
B	- Standard 100mm x 100mm, black
18	- 455mm (18") High Post

SUSTAINABILITY

A selection of sustainability highlights for the M/Flex:

- Recycled content: 12% post-consumer, 5% pre-consumer
- Made predominantly of steel and aluminum, which are highly recyclable
- Shipped in packaging that contains recycled content

FIND OUT MORE

[Humanscale.com](https://www.humanscale.com)

Per visualizzare tutti i Termini e condizioni Humanscale, visita:

www.humanscale.com/terms-conditions