



Redefining the Large-Format Printer.

imagePROGRAF™ Series

Up to 2.4 D
Prints/Minute

Vivid, Eye-Catching Prints,
with New Magenta Ink

Scan-to-Copy/File/
Share Solution



imagePROGRAF

TM-240 MFP Lm24

Specifications

imagePROGRAF

TM-240 MFP Lm24

Print Head PF-06	Power Consumption Max: Approx. 59W Standby: Approx. 1.6W Power Off: Approx. 0.1W	Maximum Media Width 26"
Number of Nozzles Matte Black: 5,120 Nozzles Other Colors: 2,560 Nozzles per Color	Certifications Environmental Certifications ENERGY STAR® (Worldwide), EPEAT Gold	Maximum Scan Length 109"
Droplet Size 5 Picoliter	Operational Environment Temperature: 59 – 86 °F (15 – 30 °C) Relative Humidity: 10 – 80% (Non Condensation)	Maximum Media Thickness 0.003" - 0.03" (0.07 mm - 0.8 mm)
Ink Type Pigment: Matte Black (MBK), Cyan (C), Magenta (M), Yellow (Y), Black (BK)	TM-240 MFP Lm24 Dimensions (H x W x D) and Weight (with stand and basket) 50.24" x 38.5" x 34.1"; 125.7 lbs.	Digital Imaging Technology Contact Image Sensor (CIS) Technology (SingleSensor Assembly) • 24-bit RGB digital color image capture • 16-bit grayscale image capture • Panchromatic monochrome and black-and-white • Bi-directional extra long-life LED light system for optimum object illumination and instant-on scanning capability
Ink Tank Shipped with printer: MBK (80 ml), BK, C, M, Y (55 ml) Replacement: MBK, BK, C, Y: PFI-030 (55 ml) and M: PFI-031 (55 ml)	Package Dimensions (H x W x D) and Weight (Printer only with pallet) 26.7" x 45.3" x 35.9"; 156.5 lbs	Included Software ScanAppL
Printer RAM 2 GB	Options • 2"/3" Roll Holder Set (RH2-28) User-Replaceable Items • Ink Tank (PFI-030/PFI-031) • Print Head (PF-06) • Maintenance Cartridge (MC-31) • Cutter Blade (CT-08)	Operating Environment 10 - 35 °C, 10 - 90% RH
Media Feed Roll Feed: One Roll, Top-loading, Front Output	What's In The Printer Box Printer, Starter Ink Tanks BK/C/M/Y (55ml) MBK (80ml), 1 Print Head, Maintenance Cartridge (Installed), 2" Roll Holder, Installation Guide, User Registration Card, One Year Printer Warranty Statement, Print Head Warranty Statement, Call Center Notice, Media Compatibility Flyer, PosterArtist Web Notice Flyer, Safety and Environmental Information, iWR Service Terms Leaflet, USB port (High Speed), Power Cable & Screw, Gigabit Ethernet (Built-in)	External Power Supply 100-240V, 50-60 Hz
Media Width Roll Feed: 8"-24" (203.2 mm - 610 mm) Cut Sheet: 8.2"-24" (210 mm - 610 mm)		Scanner Power Consumption Sleep/Idle: 0.6W/11.7W Scanning Color/Grayscale @ 200 dpi: 17.5W
Media Cutter Automatic horizontal cutting (Rotary cutter): standard		Compliance ENERGY STAR®, UL, FCC
Media Thickness 0" - 0.03" (0.07 mm - 0.8 mm)		Scanner Dimensions (H x W x D) (With Doc Return Guide - Paper Tray flat) 5.1" x 36.8" x 9.9"
Media Core Sizes 2" Core Standard. 2"/3" Core Roll Holder Set (RH2-28) Optional.		Scanner Weight 11.6 lb. (Approx.)
Maximum Roll Outer Diameter 5.9" (150 mm)		What's In The Scanner Box • Lm24 Scanner • Printer mounting brackets, fixings, and 3mm tool • 2 paper edge guides • Document return guides (1 for Lm24 scanner) • Calibration target • Lm24 Lm36 Scanner Quick Start Guide • Ethernet cable (2 meter) • Power Supply Regional - Mains power cord(s) (2 meter)
Media Output Catch Basket (included)	What's In The Stand Box SD-24 Stand with Catch Basket	■ Wireless printing requires a working network with wireless 802.11b/g or 802.11n capability. Wireless performance may vary based on terrain and distance between the printer and wireless network clients. ■ The scan rate is proportional across the full range of resolutions supported by the scanner. Actual scan times will depend on the host system performance. Quoted top speeds may be limited by the effective bandwidth of the USB 2 and is not guaranteed for all media types. ▲ The quoted scan accuracy may vary depending on the operating environment and the thickness of the media. Note: The imagePROGRAF TM Series MFP Lm24 systems contain multiple components, some of which are manufactured by third parties. To the extent that such third-party offerings come with limited warranties, such limited warranties are hereby passed to the purchaser, and Canon shall have no obligation or any liability with respect to such third-party offerings.
Printing Software Utilities Accounting Manager, Device Management Console, Direct Print Plus, Free Layout Plus, imagePROGRAF Printer Driver for Windows®/Mac®, Media Configuration Tool, PosterArtist Lite, Canon PRINT Inkjet Selphy	Lm24 SCANNER	
Operating System Windows 7 (32/64-bit), Windows 8.1 (32/64-bit), Windows 10 (32/64-bit), Windows 11 (64-bit), Windows Server 2008R2, 2012, 2012R2, 2016, 2019, 2022 (64-bit), Macintosh OS v10.12.6- v13x	Scan Speed ■■ • Color: 1" per second at 200dpi • Mono or B/W: 3" per second at 200dpi	
Print Language Printer: SGRaster, HP-GL/2, HP RTL, JPEG, CALS G4	Scan Modes • 16.7 Million Color RGB (24-bit) • 256-level Grayscale (8-bit) • Black-and-white (1-bit)	
Interface Standard (Built-in): USB 2.0 Hi-Speed, 10/100/1000Base-T/TX, Wireless LAN (IEEE 802.11 b/g/n)■	Color Space sRGB	
Power Supply AC 100 – 240V (50 – 60 Hz)	Maximum Resolution 600 dpi (Optical)	
	Scan Accuracy ▲ +/- 0.2% : +/- 1 pixel	
	Maximum Scan Width 24"	

Canon

Canon products offer certain security features, yet many variables can impact the security of your devices and data. Canon does not warrant that use of its features will prevent security issues.

Nothing herein should be construed as legal or regulatory advice concerning applicable laws; customers must have their own qualified counsel determine the feasibility of a solution as it relates to regulatory and statutory compliance. Some security features may impact functionality/performance; you may want to test these settings in your environment.

As an ENERGY STAR® Partner, Canon U.S.A., Inc. has qualified these models as meeting the ENERGY STAR energy efficiency criteria through an EPA recognized certification body. ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. Canon and imagePROGRAF are registered trademarks of Canon Inc. in the United States and may also be registered trademarks or trademarks in other countries. Wi-Fi is a registered trademark of the Wi-Fi alliance. All other referenced product names and marks are trademarks of their respective owners. All printer output and screen images are simulated. Specifications and availability subject to change without notice. Not responsible for typographical errors.

©2023 Canon U.S.A., Inc. All rights reserved.

9/23-1917-9311

usa.canon.com/imagePROGRAF

