



Environmental Certificates



[Newland](#)

**NL48243QHT
NEWLAND | 48"X24" RECTANGULAR TABLE - 3-STAGE, 2
LEGS**

Newland - simple and modular components combining classic design, quality and value to support a wide range of workspace applications. From private offices, open plan, meeting and training spaces, Newland offers functional and practical desking solutions that will stand the test of time.

- Quick assembly electric height adjustable bases with leg columns preassembled to telescopic cross bar assembly including electric motors. Unfold leg columns, attach feet and worksurface support to base; fasten assembly to top; plug in connections and start to use.
- 3-stage base. range of adjustability with 1" thick top is 22.6" to 48.2"H.
- Easy to use up-down controller with digital read-out and four memory programmable positions.
- May be specified as complete tables or may order tops and bases separately.
- Dual motor with 265 lbs. lift capacity.
- Anti-collision sensor.
- Standby power consumption 0.1W. Active power consumption 220W.
- Operates at 1.2" per second.
- 8' long power cord.
- Meets applicable ANSI/BIFMA x5.5 standards.
- Laminate tops covered by Global's lifetime warranty.
Five-year warranty on base components including electrical components and motorized parts.
- ETL/CETL and Greenguard Certified.
- Shipped easy to assemble in 2 cartons.
- Worksurface is dimensioned to allow 1" gap around perimeter in a nominal footprint

Finish Options:

Laminate finish: Available in all Newland finishes

Base finish: Tungsten finish only



Specifications

Dimensions: 46"W x 23"D x 22.6"-48.2"H

Weight: 108 lbs / 48.99 kg

Volume: 5 ft³ / 0.14 m³
