

PERFORMANCE**Processor**

Intel® Celeron® N4500 (2C / 2T, 1.1 / 2.8GHz, 4MB L3)

Graphics

Integrated Intel® UHD Graphics

Chipset

Intel® SoC Platform

Memory

4GB Soldered LPDDR4x-2933

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

4GB soldered memory, not upgradable

Storage

32GB eMMC 5.1

Storage Support^[1]

32GB eMMC 5.1 on systemboard

Storage Slot

eMMC on systemboard, no slots

Card Reader

MicroSD Card Reader

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® 5682I-CGT codec

Speakers

Stereo speakers, 2W x2

Camera

Front HD 720p with Privacy Shutter

Microphone

Mono

Battery

Integrated 42Wh

Power Adapter

65W USB-C® (2-pin)

DESIGN**Display^[2]**

11.6" HD (1366x768) IPS 250nits Glossy, 50% NTSC, Corning® Gorilla® Glass, Touch

Touchscreen

10-point Multi-touch

Keyboard

Non-backlit, French / English

Touchpad

One-piece multi-touch touchpad

Case Color

Grey

Surface Treatment

Texture

Case Material

PC + ABS with Rubber Bumper (Top), PC + ABS (Bottom)

Pen

No Support

Dimensions (WxDxH)^[3]

289.6 x 202.4 x 19.9 mm (11.4 x 7.97 x 0.78 inches)

Weight^[4]

Starting at 1.33 kg (2.93 lbs)

Others

Buttons: power key, volume key

SOFTWARE**Operating System**

ChromeOS

Bundled Software

None

CONNECTIVITY**Ethernet**

No Onboard Ethernet

WLAN + Bluetooth^[5]

Intel® Wi-Fi® 6 AX201, 11ax 2x2 + BT5.1

WWAN

None

SIM Card

None

Standard Ports

- 2x USB 3.2 Gen 1
- 1x USB-C® 3.2 Gen 1 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.2)
- 1x HDMI® 1.4b
- 1x Headphone / microphone combo jack (3.5mm)
- 1x microSD card reader

Optional Ports (configured)

None

SECURITY & PRIVACY**Security Chip**

Google Security Chip H1

Fingerprint Reader

None

Physical Locks

Kensington® Nano Security Slot™

Other Security

Camera privacy shutter

SERVICE**Base Warranty**

1-year, Mail-in

Included Upgrade

None

ACCESSORIES**Bundled Accessories^[6]**

None

CERTIFICATIONS**Green Certifications^[7]**

- ENERGY STAR® 8.0
- EPEAT™ Silver Registered
- ErP Lot 3
- RoHS compliant
- TCO Certified 8.0

Mil-Spec Test

MIL-STD-810H military test passed

MODEL**TopSeller** : Yes**Announce Date** : 2023-03-14**EAN / UPC / JAN** : 196804987989**End of Support** : N/A**Note:**

^[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.

^[2] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

^[3] The system dimensions may vary depending on configurations.

^[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

^[5] Wi-Fi 6 full features might be limited by country-level restrictions. Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitations.

^[6] For more compatible accessory solutions, please visit [Accessories for Lenovo 500e Chromebook Gen 3 \(Intel\)](#)

^[7] EPEAT is registered where applicable, please see epeat.net for registration status by country.

Lenovo reserves the right to change specifications without notice.

To see more note information, please link to <https://psref.lenovo.com/Detail/1648?M=82JB003XCF>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

Lenovo 65W Standard AC Adapter (USB Type-C)- US/Can/Mex

4X20M26268

This Lenovo 65W Standard AC Adapter (USB Type-C) Power Adapter offers fast, efficient charging at home, in the office, or on the go. This power adapter is compatible with ThinkPad USB-C enabled Notebook and Tablet.

Recommended Services

GOOD

3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0Q81869)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference